## Merck

# Empower your Lao

EMSURE<sup>®</sup> | EMPARTA<sup>®</sup> | EMPLURA<sup>®</sup> Inorganics & Solvents for classical analysis

The life science business of Merck operates as MilliporeSigma in the U.S. and Canada.



Supelco<sup>®</sup> Analytical Products

## precision Made simple

Our goal is to make your daily lab work more secure, more efficient and more reliable. With one word: smarter! Close partnerships with our customers have been at the heart of our progress throughout our long history. They have allowed us to clearly understand your challenges. Our Supelco® Inorganics and Solvents are developed from analytical experts for analytical experts. They stand for precision, accuracy and consistency. And even more, they constantly push the boundaries of innovation.

We provide scientists with best-in-class portfolio particularly for lab applications. Our Life Science portfolio comprises more than 300,000 products, served to you in 66 countries around the world. So whether in your quality control lab, pilot plant or production facility, you'll have the most suitable products, packaging and documentation to conduct your application more easily, efficiently and economically. **Discover how our world-class Inorganics and Solvents can empower your work.** 



The Supelco<sup>®</sup> portfolio of analytical solutions is developed by analytical chemists for analytical chemists to ensure your results are accurate, precise and reproducible. Every product is meticulously quality controlled to maintain the integrity of your testing protocols and, with our dedicated scientists, the expertise you need is always on hand.

... it's so simple to find the right reagent for your application!

> Demanding or regulated analytical applications

## Routine analytical applications


Preparative lab work, cleaning and production

## Just choose your grade

Analytical chemistry is a vast field. It can mean anything from complex analysis to routine or preparative lab work. Each poses unique demands, requires distinct solutions, and is governed by different regulations. When looking for products, you have to consider your application, your target and, of course, your budget.




To simplify your search, our extensive Supelco<sup>®</sup> portfolio of Inorganics and Solvents is divided into three grades: EMSURE<sup>®</sup>, EMPARTA<sup>®</sup> and EMPLURA<sup>®</sup>. Each quality grade is offered in a variety of volumes, packaging materials, and with different documentation packages. Now, you won't have to search for the right solution for your application. All you have to do is choose.



## contents

Compliance and Documentation	Page $8$
Pharmaceutical Analysis	Page 12
Specification and Purity	Page $14$
Safety and Packaging	Page 18
Smart Label	Page 20






Packaging and Safe Handling Page 42

### .g .ege .\_

## Inorganics & Solvents



Safety Products & Essentials Page 120

## compliance and bocumentation

Whether you manufacture products nationally or internationally, you need to comply with a host of regulations. It can be challenging to maintain an overview of requirements – especially when they change. This is where a capable partner can help.

Our Inorganics and Solvents are produced and tested according to multiple international guidelines. This means they can be used worldwide for almost all applications. It also allows our global customers to work with the same standard operating procedures (SOPs), and export to countries with different regulations.

By combining multi-standard compliance with comprehensive documentation, our products make your work both simpler and safer.

### **Regulatory environment**

Our analytical reagents are available in different grades, which are specified in accordance with various international regulations.

#### **American Chemical Society (ACS)**

EMPARTA<sup>®</sup> and EMSURE<sup>®</sup> products are specified according to the monographs published in the "Reagent Chemicals" guidelines of the American Chemical Society (ACS). We follow the most recent online version as the version of record, and regularly check for updates. Our in-depth approach to ACS specifications includes comparison with our own stringent quality control standards.

#### **United States Pharmacopeia (USP)**

The "Reagents" chapter of the U.S. Pharmacopeia and National Formulary defines the quality of reagents required for testing according to USP-NF. In most cases, the USP recommends to "use ACS reagent grade", which is described as a grade meeting the corresponding specifications of the online version of ACS Reagent Chemicals. Since EMPARTA® and EMSURE® products are ACS-compliant, they are also ideal for quality control according to USP-NF.

#### **Reagents section of the European Pharmacopoeia (Reag. Ph Eur)**

Currently in its 10th edition, the European Pharmacopoeia (Ph Eur) is published by the European Directorate for the Quality of Medicines & Health Care (EDQM), and defines requirements for the "qualitative and quantitative composition of medicines, the tests to be carried out on medicines and on substances and materials used in their production". It contains a detailed section describing reagents to be used for analysis in accordance with the European Pharmacopoeia. EMSURE<sup>®</sup> products fulfill these requirements, and bear the designation, "Reag. Ph Eur".

## International Organization for Standardization (ISO)


Besides pharmacopoeia regulations, the International Organization for Standardization (ISO) also sets guidelines for analytical reagents. Specifically, ISO 6353 defines the requirements for reagents used in analytical chemistry. All EMSURE® products with the designation "ISO" are compliant with ISO 6353.

### Multi-standard compliance and support

We offer a choice of product grades to suit the regulatory environment you work in. EMPARTA<sup>®</sup> products are specified according to ACS. Most EMSURE<sup>®</sup> product specifications not only fulfill ACS, Reag. Ph Eur, and ISO guidelines – but exceed them. That's because we are regularly adding new parameters required by our customers. This is essential as it enables the use of new, more sensitive technologies.

#### The most parameters

The following graph demonstrates the number of parameters specified for an EMSURE® product versus those required by regulatory organizations (ACS, Reag. Ph Eur and ISO). Clearly, EMSURE® products not only fulfill international guidelines, but surpass them by far. Brand comparisons confirm the advantages of EMSURE® reagents. In this example, the number of specified parameters clearly demonstrates the superior quality of an EMSURE® product.




(Cat. No. 106404)

#### **Documentation**

Complete, correct documentation is vital when working with analytical reagents. That's why we offer product specifications, Certificates of Analysis, and Material Safety Data Sheets (MSDS) for all EMSURE<sup>®</sup>, EMPARTA<sup>®</sup> and EMPLURA<sup>®</sup> products. Available 24/7 on our website, the specifications and Certificates of Analysis prove the superior quality of the chemicals, while the MSDS provides product-specific safety information. The availability of further documentation is connected to the new M-Clarity<sup>™</sup> program.

#### **M-Clarity<sup>™</sup> program**

With the M-Clarity<sup>™</sup> program products from Merck Life Science are allocated to 6 MQ levels from MQ100 to MQ600 defining the quality attributes, documentation and services offered with our products in each level. EMSURE<sup>®</sup> products are minimum classified into MQ300, while EMPARTA<sup>®</sup> and EMPLURA<sup>®</sup> are in MQ200. This means more support and transparency for our EMSURE<sup>®</sup> products than ever before.



For more information see page 36

\* For more information on MQ levels and the M-Clarity<sup>™</sup> program see page 30

# pharmaceutical analysis

### with suitable, specified reagents

We supply several hundred Inorganics and Solvents perfectly fitted for pharmaceutical analysis – the most extensive range offered by any manufacturer. Comprising solvents, acids, salts, caustics, bases, indicators and special reagents, our pharmacopoeia portfolio ensures that you work with the most suitable products for your particular needs and that they meet all quality guidelines.

For pharmaceutical analysis, you have the choice of two grades: EMSURE<sup>®</sup> or EMPARTA<sup>®</sup>. While both grades comply with ACS standards, EMSURE<sup>®</sup> products also fulfill the Reagents requirements of the European Pharmacopoeia.

#### **Fulfill global requirements**

Through compliance with these comprehensive global standards, our analytical reagents offer a new level of quality and reliability in pharmaceutical applications. Whether for research and development or routine quality control, they allow you to fulfill the fundamental prerequisites of your scientific work and successfully pass audits.

#### **Ensure reliable analyses**

Reagent quality is decisive in pharmaceutical analysis. The greater and more consistent the quality, the more reproducible the results, and the lower the need for repeat analyses. Due to their exceptional quality and purity, our analytical reagents provide you with greater accuracy, efficiency and economy from the start.

#### Soar with our high standards

Our product quality not only complies with international regulations, but also fulfills the Merck KGaA, Darmstadt, Germany rigorous pharmaceutical guidelines – which are even more stringent for most products. Due to our unique, superior quality standards and additional parameters, our reagents offer maximum purity and security.

#### Regulations



For more information see page 32

#### Specification

Reag. Ph Eur	= Reagents section of the European Pharmacopoeia
ACS	= American Chemical Society
USP	= United States Pharmacopoeia (refers to ACS for reagents)

## specifications and purity

## Reliable quality for trusted results

Our reagents and chemicals are renowned for their outstanding quality and purity. We achieve and maintain this reputation through three important measures: validation, accreditation, and compliance with regulations. Every step in our supply chain is subject to the most stringent controls and fully documented to give you complete confidence in your analysis.

#### **Purity**

Decades of experience with highly pure chemicals combined with cutting-edge production and filling plants ensure that what you order is what you receive. We only use high-quality raw materials and manufacture under strictly controlled conditions using our advanced methodology. This results in outstanding chemical purity and extremely low limiting values, which makes our products the ideal choice for reliable qualitative and quantitative analyses.


#### **Quality control**

All our Inorganics and Solvents are tested and certified in our own state-of-the-art laboratories under the guidance of highly qualified specialists. We have quality control labs at every production site, which work closely together to ensure comparable test procedures and results. During testing, we always adhere to international standards and legal requirements, and integrate the latest developments in technology and methods. So you can trust on our analytical competence. EMPARTA® and EMPLURA® grade products are tested at one of our own labs close to its production site. EMSURE® grade products are quality controlled at our Merck KGaA, Darmstadt, Germany site.

#### Consistency

Due to their outstanding batch-to-batch consistency, each time you use our products, you can expect the same excellent quality. This not only ensures reproducible results, but also avoids the costs and complications of repeat analyses. The graphs on the right demonstrate the superior batch-to-batch consistency of some of our products.

Every step in our supply chain is subject to the most stringent controls and fully documented to give you **complete confidence** in your analysis.




#### Acetone for analysis EMSURE® ACS, ISO, Reag. Ph Eur

Assay specification Assay effective values

#### Hydrochloric acid fuming 37% for analysis EMSURE® ACS, ISO, Reag. Ph Eur









## Our promise of exceptional quality

#### **Unrivalled specifications**

Our reagents and solvents often offer additional specifications beyond those required by international guidelines, such as ISO, ACS and Reag. Ph Eur. Many are measured for up to 70 parameters! Furthermore, thanks to our proven Quality Management System, we are able to continuously improve our specifications.

#### **Application-optimized**

The differences in our quality grades are clearly shown in their individual specifications. Regardless of the grade you choose, you will always receive a product of excellent quality that's perfectly suited to your application.

#### **Dedicated service**

For us, quality encompasses more than product purity and consistency. It also means service that exceeds expectations. Whether you require regulatory support, application advice, or a specific product, our experienced team is always at hand to work closely with you and deliver swift, innovative solutions.

_	Regulatory support	Purity	Number of specified parameters
EMSURE®	The most extensive specifications worldwide!	99.7–99.9%	< 70
<b>EMPARTA®</b>	All ACS requirements	99.0-99.5%	< 10
<b>EMPLURA</b> ®	All basic parameters	~ 99%	4–5



#### Certificate of Analysis

#### 1.04933.0500 Potassium chloride for analysis (<= 0.005% Br) EMSURE® ACS,ISO, Reag. Ph Eur A1554533

Batch

	Spec. Values		Batch Values	
Assay (argentometric)	99.5 - 100.5	%	99.6	%
Assay (argentometric; calculated on dried substance)	99.0 - 100.5	%	99.6	%
Identity	passes test		passes test	
Appearance of solution	passes test		passes test	
Insoluble matter	≤ 0.005	%	≤ 0.005	%
pH-value (5 %; water)	5.5 - 8.0		6.1	
Acidity or alkalinity	passes test		passes test	
Bromide (Br)	≤ 0.005	%	≤ 0.005	%
Chlorate and Nitrate (as NO <sub>3</sub> )	≤ 0.003	%	≤ 0.003	%
lodide (I)	≤ 0.002	%	≤ 0.002	%
lodide (I)	passes test		passes test	
Phosphate (PO <sub>4</sub> )	≤ 0.0005	%	≤ 0.0005	%
Sulfate (SO <sub>4</sub> )	≤ 0.001	%	≤ 0.001	%
Total nitrogen (N)	≤ 0.001	%	≤ 0.001	%
Heavy metals (as Pb)	≤ 0.0005	%	≤ 0.0005	%
Ba (Barium)	passes test		passes test	
Ca (Calcium)	≤ 0.001	%	≤ 0.001	%
Fe (Iron)	≤ 0.0002	%	≤ 0.0002	%
Mg (Magnesium)	≤ 0.0005	%	≤ 0.0005	%
Na (Sodium)	≤ 0.005	%	≤ 0.005	%
Magnesium and alkaline-earth metals (as Ca)	≤ 0.02	%	≤ 0.02	%
Loss on Drying (105 °C)	≤ 1.0	%	< 0.2	%

Corresponds to ACS, ISO, Reag. Ph Eur

Date of release (DD.MM.YYYY) 02.04.2020 Minimum shelf life (DD.MM.YYYY) 31.12.2024

> Claudia Wiegand Responsible laboratory manager quality control

This document has been produced electronically and is valid without a signature

EMSURE® products combine maximum specifications with minimum

impurities. Their Certificates of Analysis provide an extended impurity profile for each batch, and detailed batch values for each specification parameter. This avoids misinterpretation of results, and gives you greater control of your analysis, especially when developing new methods.

# safety and packaging

## Protecting people, products and the planet

Besides offering premium chemicals and reagents, we have invested decades into developing the most advanced packaging concepts in the field of chemistry. Our innovative packaging and withdrawal systems are precisely tailored to the contents, and based on sustainable principles. So they not only protect your personnel and products, but also the environment.



#### Handy, unbreakable HDPE bottles for reagents

- Safe and unbreakable
- High pressure stability
- Convenient handling with integrated handle
- Eco-friendly
- Cost-efficient

#### **Robust, PE-coated Safebreak bottles for acids**

- Safe handling of acids
- Long shelf-life as with conventional glass bottles
- Easy, eco-friendly disposal (with glass)

## Environmentally friendly, returnable stainless steel drums for solvents

- Safe, easy and convenient handling of solvents
- Ecological, returnable container
- Cost effective solution
- Suitable withdrawal systems available



#### **Development and testing**

Our internal packaging department is exclusively responsible for testing, developing and approving packaging materials. Our package testing facility is accredited by the German Federal Institute for Materials Research and Testing (BAM – Bundesanstalt für Materialforschung und -prüfung), the authority responsible for the packaging of dangerous goods.

#### **Grades and options**

All our products are delivered in sophisticated and suitable packaging. The choice of packaging, however, varies from grade to grade. EMSURE<sup>®</sup> products are available in a large variety of packaging sizes and materials to suit your particular application and requirements. EMPARTA<sup>®</sup> and EMPLURA<sup>®</sup> products are offered in standard pack sizes, for example, 1 kg or 25 kg for solids, and 2.5 l, 4 l, or 25 l for liquids.

### Packaging advantages

- Packaging is always compatible with the product
- Safe and convenient handling, storage and transportation
- Optimal protection of chemicals and reagents from contamination
- Application-oriented packaging
- Wide choice of packaging materials and sizes
- For more details about our packaging, please see "Packaging and Safe Handling" on page 42

#### Well protected

All our products come with a tamper evident seal – e.g. our bottles with S40, S60, S85 thread have an improved tamper evident seal with a ring remaining on the bottle neck.



## **Smart Label** Easier, faster, better data handling

Enjoy the simplest, quickest way to access data with our new smart label which is equipped with a 2D data matrix barcode. It contains all the essential product information you require, such as item code, batch number, shelf life, country of origin and links to documentation like CoA, and SDS – all in digitalized form.

No need to manually search for and enter data into your system. No more typos, repetitions, or lost time. The 2D barcode is programed using Global Standard One (GS1) specifications, so it can be processed directly in your LIMS or ERP system. For even greater convenience, use one of our innovative, intuitive web and mobile apps.

The new smart label with a real 2D barcode. It's precision made simple – for analytical chemists by analytical chemists.

#### **Features and benefits**

- Easy, quick and convenient
- Digitalized, up-to-date product data
- Minimized errors, greater security
- · Seamless access to safety data
- 2 mobile apps for smartphones and tablets
- Scan Now web app for use with barcode scanner
- Direct processing in LIMS or ERP system

## 3 smart ways to easy data access

#### 1. My M Safety mobile app for safety data and tags

Use your smartphone and our My M Safety app to access product safety data and print safety tags – all in accordance with your local regulations, and in your local language. Discover safety data as easy and convenient as never before. The app is available for iOS and Android systems.

#### 2. Scan Now web or mobile app for product info and documents

Access documents, like CoA, MSDS and product related literature, with our Scan Now web app. Simply connect a standard barcode scanner to your PC or laptop, visit MerckMillipore.com/ScanNow and scan the 2D barcode.

For even easier data handling without a barcode scanner, use our new Scan Now mobile app and your smartphone camera. The app is available for iOS and Android systems.

#### 3. LIMS or ERP system for direct scanning of 2D barcode


Thanks to the universal GS1 data encoding of our 2D barcode, you can insert all product data straight into your application via your LIMS or ERP system.



## **EMSURE®** Premium Grade Products

### Inorganics and Solvents – for demanding or regulated analytical applications

The EMSURE<sup>®</sup> brand designates our premium grade Inorganics and Solvents, which are optimized for regulated analyses and highly demanding lab applications. These products offer the highest quality and an unmatched scope of specifications to give you complete control of test conditions and eliminate uncertainties. What's more, EMSURE<sup>®</sup> Inorganics and Solvents are fully compliant with international regulations, and are suitable for an extraordinarily wide range of applications. So when you want to be more than sure: choose EMSURE<sup>®</sup> products.





▶ Page 26



Obtain more accurate and reliable results

▶ Page 24



Fulfill regulatory requirements

▶ Page 27



Know your impurity profile

▶ Page 22



Worldwide availability Page 27



Enhanced documentation and support

▶ Page 28

## **EMSURE**<sup>®</sup> Premium Grade Products

23

## **EMSURE**<sup>®</sup> Premium Grade Inorganics and Solvents



#### Extended impurity profile – Superior purity and clarity

New analytical methods have lower detection limits and higher sensitivity. Hence, reagents of greater purity are required. EMSURE® products are the perfect choice. They not only offer superior quality, but also more extensive product information to prepare you for any analytical challenge.

All EMSURE<sup>®</sup> products are made from high-quality raw materials in our state-of-the-art production facilities, then tested for up to 70 parameters at our stringent quality control labs in Darmstadt, Germany. This results in outstanding chemical purity and extremely low limiting values. Every EMSURE<sup>®</sup> product comes with a comprehensive Certificate of Analysis, which includes an extended impurity profile for each batch. This gives you absolute analytical security, and prevents misinterpretation of results caused by impurities.


#### **Your benefits**

- Most extensive specifications worldwide
  - Tested for up to 70 parameters
  - Extraordinary purity
  - Very low limiting values
- Greater accuracy and control of analyses
- Optimized for highly critical and demanding analyses
- Ideal for method development
- No interference or contamination due to unknown impurities

Acetic acid (glacial) 100% anhydrous for

analysis EMSURE® Premium Grade Inorganics

and Solvents, ACS, ISO, Reag. Ph Eur



Additional parameters for EMSURE® products \_

Additional parameters for ISO 6353

Additional parameters for Reag. Ph Eur \_\_\_\_

ACS —

#### Acetic acid (glacial) 100% anhydrous for analysis EMSURE®

Water	≤ 0.2%
Zr (Zirconium)	≤ 0.050 ppm
Zn (Zinc)	≤ 0.030 ppm
V (Vanadium)	≤ 0.010 ppm
Tl (Thallium)	≤ 0.020 ppm
Ti (Titanium)	≤ 0.050 ppm
Sr (Strontium)	≤ 0.010 ppm
Sn (Tin)	≤ 0.050 ppm
Pt (Platinum)	≤ 0.100 ppm
Phosphate (PO₄)	≤ 0.4 ppm
Ni (Nickel)	≤ 0.020 ppm
Na (Sodium)	≤ 0.200 ppm
Mo (Molybdenum)	≤ 0.010 ppm
Mn (Manganese) Mg (Magnesium)	≤ 0.010 ppm ≤ 0.050 ppm
	≤ 0.030 ppm ≤ 0.010 ppm
Li (Lithium) K (Potassium)	≤ 0.010 ppm ≤ 0.100 ppm
In (Indium)	≤ 0.100 ppm ≤ 0.050 ppm
Hg (Mercury)	≤ 0.005 ppm ≤ 0.005 ppm
Ge (Germanium)	≤ 0.020 ppm
Ga (Gallium)	≤ 0.050 ppm
Cr (Chromium)	≤ 0.020 ppm
Co (Cobalt)	≤ 0.010 ppm
Cd (Cadmium)	≤ 0.020 ppm
Ca (Calcium)	≤ 0.100 ppm
Bi (Bismuth)	≤ 0.050 ppm
Be (Beryllium)	≤ 0.005 ppm
Ba (Barium)	≤ 0.010 ppm
B (Boron)	≤ 0.100 ppm
Au (Gold)	≤ 0.010 ppm
As (Arsenic)	≤ 0.010 ppm
Al (Aluminium)	≤ 0.020 ppm
Ag (Silver)	≤ 0.005 ppm
Acetaldehyde	≤ 2 ppm
Pb (Lead)	≤ 0.010 ppm
Cu (Copper)	≤ 0.010 ppm
Solidification temp.	≥ 16.3 °C
Identity	passes test
Titratable base	≤ 0.0004 meq/g
Substances reducing KMnO <sub>4</sub>	≤ 20 ppm
Substances reducing K <sub>2</sub> Cr <sub>2</sub> O <sub>7</sub>	passes test
Fe (Iron)	≤ 0.050 ppm
Heavy metals (as Pb)	≤ 0.5 ppm
Sulphate (SO₄)	≤ 0.4 ppm
Chloride (Cl)	≤ 0.4 ppm
Acetic anhydride	≤ 100 ppm
Evaporation residue	≤ 5 ppm
Dilution test	passes test
Color	≤ 10 Hazen
Assav (alkalimetric)	≥ 99.8%

## **EMSURE**<sup>®</sup> Premium Grade Inorganics and Solvents



#### Accuracy and reliability – Absolute trust – every time


Thanks to their outstanding batch-to-batch consistency, each time you use EMSURE<sup>®</sup> products, you can expect the same excellent quality. This not only ensures reproducible results, but also reduces your analytical costs. Now, you can avoid repeat analyses, and won't need to stock up on specific product batches.

- Unmatched batch-to-batch consistency
- Reliable and reproducible results
- Lower analytical costs
- No repeat analyses


Lab technician Tom is scanning the new 2D barcode with his mobile phone using the ScanNow app


K123456785 2018/12/05 2.51

#### Chloroform for analysis EMSURE® ACS, ISO, Reag. Ph Eur



#### Sodium chloride for analysis EMSURE® ACS, ISO, Reag. Ph Eur





#### Perchloric acid 70-72% for analysis EMSURE® ACS, ISO, Reag. Ph Eur

## **EMSURE**<sup>®</sup> Premium Grade Inorganics and Solvents



#### Convenience and safety – Packed with innovation

Most EMSURE<sup>®</sup> products offer top quality both inside and out. Through continuous innovation, we have developed various packaging and withdrawal systems, which are precisely tailored to the contents. Our solutions offer secure and convenient usage for lab personnel, while being safer for the planet.

- Packaging is always compatible with the product
- Safe and convenient handling, storage and transportation
- Optimal protection of chemicals and reagents from contamination
- Application-oriented packaging
- Wide choice of packaging materials and sizes





#### **Regulatory compliance – Specified beyond standards**

Most EMSURE<sup>®</sup> product specifications not only fulfill ACS, Reag. Ph Eur and ISO guidelines – but surpass them. That's because we are regularly adding new parameters required by our customers. As a result, EMSURE<sup>®</sup> products can be used around the world for almost all applications, including pharmacopoeia analysis. Due to their extensive specifications, EMSURE<sup>®</sup> products are also suitable for use with the latest technologies, such as detecting concentrations of metals via atomic absorption spectroscopy (AAS).

- Compliance with ACS, ISO and / or Reag. Ph Eur (Please see "Compliance and Documentation")
- Most products' specifications exceed international standards
- Suitable for pharmacopoeia analysis
- Can be used internationally



#### Global availability - One excellent quality - worldwide

Whenever or wherever you require EMSURE® Inorganics and Solvents, we serve you the same excellent quality from 154 locations in 67 countries around the world. This, combined with multi-standard compliance, means that our multinational customers can work with the same standard operating procedures (SOPs), and export to countries with different regulations.

- Identical quality worldwide
- Comparable results
- Work with one global SOP
- Suitable for global export



## **EMSURE**<sup>®</sup> Premium Grade Inorganics and Solvents



#### **EMSURE® Documents & Support**

Highly demanding applications often require enhanced support regarding supplier quality. For EMSURE<sup>®</sup> products, we offer comprehensive documents that go far beyond CoA or MSDS, and include important change agreements for critical product modifications.

#### Your advantages:

- Streamlined lab work
- Time and cost savings
- Superior comparability of results
- Certainty during product use
- Accuracy regarding impurities
- Confidence in analysis and production
- Transparency & security in demanding processes

#### The M-Clarity<sup>™</sup> Program

The M-Clarity<sup>™</sup> Program includes the majority of our Life Science products classified into 6 MQ levels (MQ100 to MQ600).

- Each level provides specific documentation and services.
- The levels have increasing attributes to meet your application and regulatory requirements.
- Transparency allows you to select the right product for your needs regarding change control notifications and documentation support.

All EMSURE<sup>®</sup> products are part of the M-Clarity<sup>™</sup> program and are classified to a minimum level of MQ300, while EMPARTA<sup>®</sup> and EMPLURA<sup>®</sup> are at level MQ200. This means you enjoy even greater support and transparency with EMSURE<sup>®</sup> products.

#### MQ300 – Enhanced Control

EMSURE® products at the MQ300 level offer:

#### **1. Documentation support**

- Specification/Certificate of analysis
- MSDS
- ISO certificate
- Site self-assessment
- Country of origin statement
- BSE/TSE or AO certificate
- Test methods\*
- RoHS certificate\*
- \* Optional purchase

#### 2. Enhanced change control notification support

- Discontinuation of product
- Change of product specification (excluding compendial changes)
- MQ level downgrade
- Change of general shelf life
- Change in test method (non-compendial)
- Change of primary packaging material

#### Please contact your customer service for further details.



## **EMPARTA®** Standard Grade Products

### Inorganics and Solvents – for routine analytical applications

With EMPARTA® products, we offer a range of high-quality, cost-efficient Inorganics and Solvents for routine analytical applications. These standard-grade products offer fewer test parameters than EMSURE® products. Still, EMPARTA® product sepecifications are fully compliant with ACS requirements and cover all important parameters, thus ensuring reliable and reproducible results.







ACS





Convenient lab-sized packaging

▶ Page 35



Reliable results
Page 35



Efficient and cost-effective solution

Page 35

## **EMPARTA®** Standard Grade Products

## **EMPARTA®** Standard Grade Inorganics and Solvents



#### **Compliant with ACS**

The quality of EMPARTA<sup>®</sup> Inorganics and Solvents is tested according to the specifications of the monographs published in the "Reagent Chemicals" guidelines of the American Chemical Society (ACS). We follow the most recent online version as the version of record, and regularly check for updates. Our in-depth approach to ACS specifications includes comparison with our own stringent quality control standards.

#### **Reagents for analysis according to USP**

The "Reagents" chapter of the U.S. Pharmacopeia and National Formulary defines the quality of reagents required for testing according to USP-NF. In most cases, the USP recommends to "use ACS reagent grade", which is described as a grade meeting the corresponding specifications of the current edition of "Reagent Chemicals" published by the ACS. Since EMPARTA® products are fully compliant with ACS guidelines, they are ideal for quality control according to USP-NF.



#### Standard quality for routine lab applications

EMPARTA<sup>®</sup> products offer just the parameters you really need – including all those required by the ACS. Hence, they are the perfect choice for reliable quality control and routine analytical applications in less regulated industries.





#### **Reliable results**

EMPARTA<sup>®</sup> Inorganics and Solvents feature a high analytical purity of 99.0–99.5%. Thanks to our sophisticated production chain, particulate impurities and cross-contamination from other products are completely ruled out.

#### **Efficient and cost-effective solution**

From raw materials to specifications, packaging and documentation, every aspect of EMPARTA® products is designed to make your analytical lab applications as cost-effective as possible – without sacrificing quality.





#### **Convenient lab-sized packaging**

EMPARTA<sup>®</sup> Inorganics and Solvents typically come in HDPE or amber glass bottles, which are the perfect size for working in the lab. Our tailor-made packaging offers multiple safety features.

Learn about them in the chapter "Packaging and Safe Handling" (page 42).

## **EMPLURA®** Basic Grade Products

## Inorganics and Solvents for preparative lab work, cleaning and production

For many basic applications, you don't need chemicals of the highest purity – you need a cost-effective solution with reliable quality that is available in large quantities. The EMPLURA® product range is ideal for basic lab work and production applications. These economical Solvents and Inorganics offer adequate specifications with the most common parameters, and are available in small pack sizes as well as in bulk quantities.





Economical solution

Page 38



Adequate specifications with most common parameters

► Page 38



Suitable for numerous basic applications

► Page 38



Completely flexible pack sizes Page 38



Page 39

# **EMPLURA®** Basic Grade Products

# **EMPLURA®** Basic Grade Inorganics and Solvents

#### Suitable for numerous basic applications

The EMPLURA® product range includes a broad selection of the most important Inorganics and Solvents. So you will easily find the most suitable solutions for numerous basic applications, such as preparative lab work, cleaning or standard production processes.





#### **Economical solution**

Why pay for high purity when your application only requires basic quality? EMPLURA<sup>®</sup> Inorganics and Solvents are your economical answer. It gives you reliable results at a reasonable price.

#### **Completely flexible pack sizes**

Our standard packaging options vary from 1 l glass bottles to 190 l drums. However, we are completely flexible and can offer even larger quantities, such as intermediate bulk containers (IBCs) or tank containers, on request.





#### **Adequate specifications**

EMPLURA<sup>®</sup> products are mainly tested for preparative lab applications and standard production processes. Hence, we only monitor the basic parameters that are important in these applications, such as purity, identity, density, evaporation residue and water content. In most cases, the purity exceeds 98%.

#### Sustainable and safer solvent alternatives

The products we create help our customers improve people's lives every day, but we recognize that every product we make also has an environmental impact. That's why we are committed to continually enhancing the sustainability performance of our products and adopting environmentally friendly chemical processes.

Our advances include bio-based solvents that avoid the use of non-renewable resources, as well as safer substitutes for commonly used solvents that pose health or environmental concerns.





# **EMPLURA®** Basic Grade Inorganics and Solvents



### **Bio-Based Solvents**

One of the sustainable initiatives we actively pursue is the change from solvents based on synthetic chemicals to those from renewable raw materials. Whenever possible, we favor chemical products which preserve functional efficacy while reducing toxicity and environmental impact. Since their supply risk is independent of petrochemical production, bio-based solvents are also reliably available. Furthermore, production processes are safer for the environment than with fossil-based solvents.

#### **Bio-Based Ethanol\***

Instead of synthetic ethanol, we use bioethanol produced from grain or sugar cane. High quality, affordability, and ready availability make our bioethanol an obvious choice for a sustainable future.

#### **Benefits**

- Produced from grain or sugar cane, a renewable source
- Less toxic than synthetic ethanol (no toxic by-products)
- Reliable availability
- Production method is safer for the Environment

#### Ethyl(-)-L-Lactate

Ethyl lactate is a safer and more sustainable alternative to ethyl acetate and acetone. It is an ester of natural L-lactic acid, which is produced by fermentation of sugar.

#### **Benefits**

- Increased user safety due to less toxicity (non-carcinogenic)
- No waste due to 100% biodegradability
- Non-corrosive in contact with metals

#### 2-Methyltetrahydrofuran (Methyl THF)

2-Methyltetrahydrofuran is a safer and more sustainable alternative to dichloromethane and tetrahydrofuran. It is derived from renewable resources, such as corncobs and sugarcane bagasse.

#### **Benefits**

- Less solvent consumption due to more efficient extraction and higher reaction yields
- Lower volatility and higher flash point increase user safety
- Limited miscibility in water reduces waste stream
- Reliable availability (independent of petrochemical production)

### Synthetic-Based Sustainable and Safer Alternatives

#### 1-Butylpyrrolidin-2-One

NEW

1-Butylpyrrolidin-2-one is a safer alternative to N-Methyl-2-pyrrolidone (NMP), N,N-Dimethylacetamide (DMA), Dimethyl sulfoxide (DMSO) and N,N-Dimethylformamide (DMF), which face increasing regulatory pressure. As opposed to NMP, DMF and DMA, 1-Butylpyrrolidin-2-one is not classified as developmentally reprotoxic.

#### **Benefits**

- Excellent solvency power and water miscibility
- High boiling point
- High chemical and thermal stability
- Not classified as a developmental or geno-toxin
- Inherently bio-degradable
- Lower volatility compared to NMP
- Reliable alternative for REACH-restricted DMA, DMF, NMP

#### **Cyclopentyl Methyl Ether (CPME)**

Cyclopentyl methyl ether is a safer substitute for tetrahydrofuran, tert-butyl methyl ether, 1,4 dioxane and other ether solvents. It is produced by a 100% atomic catalytic reaction without any formation of by-products.

#### **Benefits**

- Resistance to peroxide formation improves laboratory safety
- One-step reaction saves energy and reduces wastewater
- More stable than tetrahydrofuran
- Higher hydrophobicity increases yields and selectivity
- Limited miscibility in water reduces waste stream

# packaging and safe Handling

### Perfected to protect



For us, packaging is not just an empty vessel for products. It is a fundamental aspect of safety, sustainability and reliability. Hence, we pay as much attention to the quality of our outer materials as to their inner contents. This commitment has led to an exceptional range of packaging options that ensure safe transport, storage and handling, while minimizing environmental impact.



### Every detail - optimized and tested


All our packing materials are tailored to their contents and meticulously tested for quality and permeability to preserve the purity of our products. Not only the container, but also the closure, transportation box and withdrawal systems (for solvents, acids and bases) are optimized as a complete packaging concept. Thanks to our high standards, our package testing facility is accredited by the German Institute for Materials Research and Testing (Bundesanstalt für Materialforschung und -prüfung), the authority responsible for the packaging of dangerous goods.



#### Your advantages

- Application-oriented packaging materials and volumes
- Convenient, safe and contamination-free handling
- Maximum safety through an extensive portfolio of accessories
- Ecological and economical use of returnable containers where suitable
- Individual user installation or other customized solutions possible

### Product label



Content of one package

#### **Labeling of Hazardous Chemicals**

The Merck label for chemical products includes the hazard communication elements according to CLP. Standardized signal words, hazard pictograms and hazard and precautionary statements are a fundamental step towards a worldwide harmonized high safety level. In the European Union the Globally Harmonized System (GHS) has been adopted by the Regulation on classification, labelling and packaging of substances and mixtures (CLP).

Hazard pictograms including the signal word provide a first visual impression for estimating potential risks. H statements describe the type and severity of the hazards posed by a substance or mixture. P statements recommend measures to be taken in order to reduce or avoid negative effects caused by a hazardous substance or mixture.

#### Labels that last

Our labels provide essential information for our customers. So their durability is a top priority. We use varnished paper labels that are resistant to most chemicals, or apply PE labels wherever necessary. All labels are resistant to abrasion, forgery proof, and adhered with glue that is specially developed for use in the chemicals sector.

## Packaging overview from bottles to tanks



#### Glass bottles for acids, bases and solvents

- Safe and convenient handling, storage and transportation
- Special shape of the opening allows optimum pouring
- Secure S40 screw cap with tamperproof seal
- Premium amber blank glass remains inert even to aggressive chemicals
- High pressure resistance
- Pulp packaging for safe transport of glass bottles Strong yet light in weight, our molded fiber trays ensure that chemical bottles are optimally protected during transportation and storage. All our pulp packaging is made from recyclable materials, so it also protects the environment.











#### HDPE bottles for acids, bases and solvents

- Made from high-density polyethylene (HDPE)
- Convenient handling and dosage with integrated handle for 2.5 I and 5 I bottles
- Narrow base for efficient use of lab space
- Low tare weight facilitates handling and reduces transport costs
- Secure S40 screw cap with tamperproof seal
- High pressure resistance (particularly for 2.5 I bottle with special base geometry)



#### HDPE bottles for caustic alkalis and salts

- Made from high-density polyethylene (HDPE)
- Wide opening for easy withdrawal
- Square base allows efficient use of storage space in labs and during transportation
- Compatible with S38 to S85 closure systems







25 kg / 50 kg



25 kg / 50 kg

#### Large packaging for caustic alkalis and salts

- Special packaging for higher volume requirements
- PE inliner is produced in clean room conditions to protect contents
- Corrugated board boxes are glued in a water-resistant manner acc. to DIN 53133 to remain stable even under damp conditions
- Robust construction allows stacking
- PE bucket and boxes for moisture-sensitive and hygroscopic products



### Packaging overview from bottles to tanks





#### Stainless steel drums for solvents

- Optimum material characteristics avoid interactions with solvents
- Returnable drums reduce costs and environmental waste
- Compatible with a variety of withdrawal systems and level sensors
- Optimum emptying characteristics
- Stackable for efficient use of space





#### Steel drums and and combi drums for solvents and acids

• Steel drums (10, 25 or 180 / 190 l) with option of PE inliner and special coating depending on contents



#### **Other drums and containers**

- Special packaging for higher volume requirements
- PE drums (up to 200 l)
- PE canisters
- 1,000 l intermediate bulk containers (IBCs)
- Larger sizes (up to tank containers or tank trucks) also available

Exemplary packaging. Offering depends on suitability with content.



### Quantity Guide Safety comes in many sizes

Our extensive variety of packaging types and sizes is unrivaled in the industry. With volumes from 0.05 I to 20,000 I, and materials from glass and HDPE to metal and stainless steel, we can easily cater to your individual requirements. The guide below will help you select the size and material that best suits your application. Whichever you choose, extraordinary safety comes standard.

#### Metal drums

#### PE drums, canisters etc.







Pack sizes	0.5   - 5	10 I – 200 I
Annual consumption	0.5 I – 100 I	> 100 l
	Standard packaging	Standard packaging range one-way packaging

Stainless steel drums optional returnable packaging in Europe

- Advantage: no rinsing / cleaning / disposing
- Return unrinsed with original labels and tightly closed

#### Tank trucks



#### Intermediate bulk containers (IBC)

#### Stainless steel drums





### > 200 I - 20,000 I

### > 1,000 l

- Customized products and containers
- Individual processes with rental agreements

### Amber glass bottles for acids, bases and solvents


Pack sizes: 0.5 | to 4 |





1.40140.0001

1.78178.0001



Safety carrier for 4 I bottles

Withdrawal system for solvents with manual pressure build-up in S40 bottles

### **HDPE bottles for liquids** for acids, bases and solvents

Pack sizes: 0.25 | to 5 |

Specially developed

Specially formed, sharp thread lip

withstands higher contact

for safe drip free pouring

Specially treated high

safety and product quality

Reduced packaging waste \_

(no additional protection

inside cardboard boxes)

to protect the environment and to benefit from economical advan-

material necessary

tages

quality HDPE

pressure and ensures tighter seals

with extreme durability, inertness

and shock resistance for highest

S40 thread





handling Special base geometry

of 2.5 | bottles prevents bulging

### Technical data

Material: HDPE Available packaging size:

0.25 l, 0.5 l, 1 l, 2.5 l and 5 l

Height, diameter and net weight (bottle size): 206 mm, ø 101 mm, ~ 66 g (1 l) 322 mm, ø 125 mm, ~ 145 g (2.5 l) 330 mm, ø 178 mm, ~ 335 g (5 l)

#### Safety accessories

2.51

Adapter with integrated level sensor for our bottles with S40 thread (supply)	9.67100.2001
Adapter with integrated level sensor for our bottles with S40 thread (solvent disposal)	9.67100.2002
Bottle opening key S40 / S28	1.08801.0001
Display for level sensor	9.67100.2004
Label set for self-labeling lab-mixtures according to GHS, DIN EN ISO & GLP	1.00801.0001
Safety stand for 2.5 I HDPE bottles	9.67213.0001
Withdrawal system for solvents with manual pressure build-up in S40 bottles	1.78178.0001

# **Safety accessories for bottles**

To further protect you during daily lab work, we offer several safety accessories specially designed for Merck KGaA, Darmstadt, Germany bottles.

#### Withdrawal system for solvents (1.78178.0001)

- Manual pump system for safe and easy withdrawal of solvents (!) from glass bottles
- Specially designed to fit bottles with S40 neck
- Conductive dip tube (included) can be easily adjusted to the size of the bottle
- Conductive dip tubes are also available separately in packs of 5 (1.78179.0001)
- Grounding cable can be easily connected to avoid the risks of static electricity
- Withdrawal system can also be used for 2.5 I HDPE bottles when combined with the safety stand (9.67213.0001)





#### Safety carrier for glass bottles up to 2.5 | (9.20078.0001) and up to 4 | (1.40140.0001)

- Secure transport of broken glass bottles and contents
- High-quality PE foam buffer ensures optimal protection
- Additional time for disposal due to chemical resistant materials
- Robust material avoids risk of cuts by glass splinters
- Leak-proof top cover prevents exposure to liquids and vapors
- Stable, broad handle for convenient handling

#### Bottle key (1.08801.0001)

- Convenient opening and closing of bottles with S40 and S28 screw caps
- Perfectly tailored to our bottles
- Maximum safety when working with hazardous liquids



#### Pouring aid for 1 I and 2.5 I glass bottles with S40 thread for single-use (1.02547.0005)

- Can be clipped on the bottle neck
- Convenient handling of 1 I and 2.5 I glass bottles
- Suitable for all liquids like acids, bases and solvents
- Is only for single-use and is disposed of with the bottle





### Label set acc. to GHS, DIN EN ISO and GLP (1.00801.0001)

- Comprehensive label compliant with GHS, DIN EN ISO and GLP standards
- Complete safety information at a glance with adhesive pictograms and signal words
- Non-permanent adhesive for easy, residuefree removal
- Robust plastic label, resistant to chemicals

#### Adapter with integrated level sensor for Merck bottles with S40 thread for solvent supply (9.67100.2001) and for solvent disposal (9.67100.2002)

- Suitable for solvents (!) in all S40 bottles
- The level sensor is pre-assembled in a S40 screw cap
- Equipped with a clamping screw, the sensor can be adjusted to several bottle sizes or also to the desired level
- Needs to be connected to an alarm display for optical and acoustic signalling (9.67100.2004)



# **Specials for acids**



### Safebreak bottles for acids – Just in case

#### When accidents happen

As containers for many types of reagents, glass bottles offer numerous advantages. They are inert to most chemicals, highly impermeable, easy to sterilize, and reusable. There's just one problem: glass can break. Depending on the contents, this could pose serious health risks for lab personnel.

#### We have you covered

Fortunately, we have developed an effective and protective solution: the Safebreak bottle. This unique glass bottle is coated with polyethylene (PE), and can withstand considerable impact force. But should the bottle break, all liquid acid (!) and glass splinters are reliably contained within the PE coating, thereby protecting users from cuts or exposure to harmful chemicals.

#### **Additional protective features**

Every Safebreak bottle is fitted with a S40 screw cap made of polypropylene that has an integrated PTFE component. Even after frequent opening and closing, the cap keeps the bottle absolutely airtight so that no liquid or vapor can escape. Our Safebreak bottle also protects the planet. It can be reused and ecologically disposed of, just as conventional glass. During incineration, the PE is burnt off without affecting the environment.





### SafetyCap for reagents that build pressure

Certain reagents, such as sodium hypochlorite solution or hydrogen peroxide, are capable of generating excess pressure through chemical reactions. To help avoid contamination, we supply all such reagents in bottles fitted with the SafetyCap.



This innovative cap has a valve that allows excess gas to be released, hence preventing the build-up of pressure. It is also absolutely leak-proof – even if the bottle is tipped.

Furthermore, the PTFE membrane incorporated in the SafetyCap allows neither gas nor liquid to enter the bottle, thus protecting the contents from contamination. For additional safety, all bottles with such reagents are packed in PE bags.

- Allows gas to be released, thereby reducing internal pressure
- Absolutely leak-proof, protects users and the environment from contamination
- Prevents gas and liquid from entering bottle, protects contents from contamination



## HDPE bottles for solids

Pack sizes: 0.1 kg to 5 kg





1.25 |

1.80 I

2.50 |

6.00 I

207 mm

219 mm

281 mm

170.5 mm

90 mm

121 mm

121 mm

180 mm

90 mm

121 mm

121 mm

180 mm

min. 65 g

min. 103 g

min. 103 g

min. 237 g

### **Corrugated board box** with PE inliner for solids



Pack sizes: 25 kg and 50 kg




for convenient and secure packing

#### Technical data

Material: Corrug	gated cardboard, PE bag		
Available package	ging size: 25 kg and 50 k	g (volume dependent on	bulk density of the product)
Volume	Height	Width	Depth
26 I	310 mm	370 mm	275 mm
36 I	420 mm	370 mm	275 mm
40 I	330 mm	379 mm	379 mm
44	500 mm	370 mm	275 mm
50 I	413 mm	374 mm	374 mm
57 l	640 mm	370 mm	275 mm
60 I	488 mm	374 mm	374 mm
80	648 mm	369 mm	369 mm

# **PE buckets & square boxes** for solids



Pack sizes: 12 kg, 25 kg and 50 kg



#### Technical data

Parameter	PE bucket 12 kg	Square box 25 kg	Square box 50 kg
Height	29.2 cm	32.9 cm	47.0 cm
Diameter / Width	33.8 cm	37.8 cm	37.8 cm
Depth	-	37.8 cm	37.8 cm
Volume	15	35 I	52 I
Filling quantity	12 kg	25 kg	50 kg
Weight (empty)	0.86 kg	1.39 kg	2.06 kg
Number per pallet	21	18	12
Material	HDPE (Lid: PE)	HDPE (Lid: PP)	HDPE (Lid: PP)

### **PE canisters & Fassetts®** for acids and bases

Pack sizes: 5 | and 25 |

Number per pallet

Openings

Material

72 (4 / cardboard)

S 60 x 6

PE

11

PE

KS 60 x 6



8

PF

CCS 60 x 6

### Steel drums and combi drums for acids and solvents

Pack sizes: 10 | to 190 |



#### Technical data

#### Withdrawal systems for acids see page 67; for solvents see page 68

Parameter	10 I	25 I	25 I with PE	180 / 190 l	180 / 190 l with PE
Height	34 cm	52 cm	52 cm	88 cm	88.5 cm
Diameter	24.5 cm	29 cm	29 cm	59.5 cm	58.8 cm
Volume	13.5 l	28	28 I	216.5	203
Filling quantity	10 I	25	25 I	180 / 190 l	180 / 190 l
Weight (empty)	1.8 kg	3.6 kg	3.4 kg	22 kg	22 kg
Number per pallet	13	11	11	2	2
Openings	2" decentrally located	2" centrally and 3/4" decentrally located	S56 x 4 (PP)	2" centrally and 3/4" decentrally located (steel, galvanized)	2 x S56x4 (PP)
Material	steel	steel	steel with PE	steel	steel with PE

### Stainless steel drums for solvents



Pack sizes: 10 | to 190 |



			N/the descent such sectors.
Technical data	Withdrawal systems for solvents see page 68		
Parameter	10	25 I	190 I
Height	35 cm	52 cm	88 cm
Diameter	24 cm	29 cm	59.5 cm
Volume	12	28	215
Filling quantity	10	25	190
Weight (empty)	1.9 kg	3.8 kg	18 kg
Number per pallet	15	11	2
Openings	2" decentrally located	2" decentrally located	2" decentrally located 3/4" decentrally located
Material	stainless steel	stainless steel	stainless steel

## **Important information** for safety and returnable system for solvents



#### The returnable system and process

In Europe Merck KGaA, Darmstadt, Germany stainless steel drums for solvents are part of a returnable process. Their use means that the user no longer has to cope with the topics of complete emptying, rinsing, disposing of the rinsing liquid and even disposing of the packaging itself in the proper manner. After consumption of the solvents on user site the empty drums are returned to us, unrinsed and with their original labels still attached. On their return, we will ensure that they are properly cleaned, checked and refilled. Clear advantages for a time saving and cost effective way of daily solvent handling.



#### Measures to discharge static electricity

If flammable liquids (e.g. solvents) are used, the container (10 l or more) must be properly earthed according to **valid local safety regulations** to avoid the risk of explosion and fire.

- General warnings and safety instructions must be observed
- All components (e.g. container and withdrawal system) must be grounded separately
- Grounding clamps must have metallic contact with both the container and the withdrawal system, and a safe ground connection
- · The grounding must be installed before opening the container
- The user must always wear conductive personal protective equipment (e.g. shoes and gloves)
- The floor must be conductive
- Use sampling vessels made of insulating material with a volume not greater than 1 liter
- Ensure that there are no additional ignition hazards caused by process-specific parameters, such as increased ignitability of the substances due to changed environmental conditions or when sampling in combination with highly charge-generating processes

#### Suitable withdrawal systems for improved safety

To further significantly increase personnel safety when handling hazardous chemicals, we offer tailor-made withdrawal systems. Our broad range of withdrawal systems and accessories includes everything you need to ensure safe and easy handling and contamination-free withdrawal of inorganics and solvents. All recommended applications are tested in accordance to the properties and specifications of the chemical.

Our products provide essential safety features required by safety regulations – from self-closing nozzles to safety accessories with pressure relief mechanisms and anti-static devices. Systems for manual pressure build-up and inert gas pressurizing are supplemented by a comprehensive selection of reducers, adapters and couplings that allow easy interconnection of all components. This way you can precisely manage your individual chemical flow and thus optimize your processes – and at the same time minimize risks for your employees and the environment.



#### Important safety advice

Our withdrawal systems have been developed and optimized for the use with containers and chemicals from us. We therefore disclaim any warranty or liability for the operability of our withdrawal systems in connection with containers or chemicals from other manufacturers.

We reserve the right to refrain from the delivery of withdrawal systems if the respective order does not indicate that each withdrawal system will be used in combination with appropriate chemicals and containers from us.

We inform and advise our customers to the best of our knowledge and ability but without any engagement or liability on our part. Our customers must obey all existing laws and regulations. This also applies in respect of any protected rights of third parties. Our information and advice does not eliminate the need for our customers to check, on their own responsibility, that our products are suitable for the purpose envisaged.

## Manual withdrawal systems for acids and bases NEW

The need for greater volumes of acids or bases may require a switch from bottles to larger containers, which increases the risk of spills and accidents. The best way to protect yourself from unintended contact with harmful and often corrosive liquids is through the use of suitable withdrawal systems. Our unique solutions allow you to safely and easily dispense harmful chemicals from large containers into other, typically smaller, reaction vessels, thereby minimizing risks.

- Unique concept allows safe and easy withdrawal of chemicals, preventing accidental contact with contents and vapors
- Flexible, lightweight withdrawal systems with integrated outlet valve and individual pressurizing options
- Integrated check valve protects the pump ball from chemical vapors
- Integrated venting system avoids vacuum development
- No operating supplies required: manual pressure buildup by hand or foot pump ball
- Lower costs through use of larger volumes of 10 l or more


#### Manual withdrawal system for acids and bases (PE)

- Made of specially tested high purity polyethylene (PE)
- Suitable for use with all acids and bases (except HNO<sub>3</sub> and H<sub>2</sub>SO<sub>4</sub>)



Examples for individual compilations						
25   Fassett <sup>®</sup> e.g. 25   Hydrochloric acid 37% EMSURE <sup>®</sup> (1.00317.9026)		25   PE canisters e.g. 25   Sodium hydroxide solution about 32% EMSURE® (1.05590.9025)				
Dispense head (PE) for acids and bases, manual pressure build-up	1.67500.0001	Dispense head (PE) for acids and bases, manual pressure build-up	1.67500.0001			
Hand pump ball for withdrawal systems	9.67114.0000	Hand pump ball for withdrawal systems	9.67114.0000			
Dip tube (PE) for acids and bases in 25 I fassetts	1.67526.0001	Dip tube (PE) for acids and bases in 25 I canisters	1.67525.0001			





#### Manual withdrawal system especially for Nitric acid and Sulfuric acid (PVDF)

- Made of specially tested high purity polyvinylidene fluoride (PVDF)
- Developed specifically for use with aggressive acids, e.g.  $\mathsf{HNO}_3$  and  $\mathsf{H}_2\mathsf{SO}_4$



Examples for individual compilati		r system compilations		
25 l combi containers e.g. 25 l Nitric acid 65% EMSURE® (1.0045	56.9026)	180 l combi containers e.g. 180 l Nitric acid 65% EMSURE® (1.00456.9180)		
Dispense head (PVDF) for Nitric acid and Sulfuric acid, manual pressure build-up	1.67501.0001	Dispense head (PVDF) for Nitric acid and Sulfuric acid, manual pressure build-up	1.67501.0001	
Hand pump ball for withdrawal systems	9.67114.0000	Foot pump ball for dispense heads	1.67502.0001	
Dip tube (PVDF) for Nitric acid and Sulfuric acid in 25 I combi containers	1.67527.0001	Dip tube (PVDF) for Nitric acid in 180 l combi containers	1.67585.0001	


#### 67

### Withdrawal Systems for solvent drums



#### Manual pressure build-up

- Safe, easy and convenient solvent handling
- Usage of tested high quality materials to ensure a reliable, contamination free and safe handling of our solvents
- High flexibility due to independence on gas supply
- Suitable for solvents in 10 I and 25 I metal and stainless steel drums



#### System at a glance

Order number	1.01114.0001	Necessary completive products	9.67100.1026 Dip tube for 25   (steel/PE)	composite drum
Suitability	10 I and 25 I metal and stainless steel drums	<ul> <li>Recommended safety</li> </ul>	Antistatic set (3 cables)	1.07070.0001
Operation mode Manual pressure build-up by pump ball		products	Drum opening key	1.08803.0001
Set components	Withdrawal system body with 2" clamp, Hand pump ball with rapid action connector, 10   dip tube, 25   dip tube	Spare parts	Dip tube for 10 l drums Dip tube for 25 l drums Hand pump ball	9.67100.1012 9.67100.1028 9.67114.0000



9.67100.9051

Spiral gas

feeding tube

#### Pressurizing with inert gas [only for stainless steel drums]

- Safe, easy and convenient solvent handling
- Usage of tested high quality materials to ensure a reliable, contamination free and safe handling of our solvents
- Construction of a central supply system, direct connection to instruments or individual installations as options

### Self closing tear off connections

for quick connection and disconnection

#### 9.67100.9002

Threaded adapter with vertical connections

Two different connectors for avoiding mismatch of gas and product



### 9.67106.0001

Stainless steel clamp

Nozzle can be hanged directly on the drum with the clamp



#### Safety hook

to avoid unintended solvent supply (push safety hook first to unblock the supply handle)

#### 9.67100.9090

Filling nozzle with stainless steel coated PTFE-tube

#### Integrated swivel joints

to avoid tube tensions

#### System at a glance

Order number	1.06710.0001			Dip tube for 10 I stainless steel drums	9.67100.1010
Suitability	bility 10 l, 25 l and 190 l stainless steel drums		Necessary completive	Dip tube for 25 l stainless steel drums Dip tube for 190 l stainless steel drums	9.67100.1025 9.67100.1190 9.67106.0001
Operation mode	Pressurizing with inert gas		products	Stainless steel clamp for filling nozzle attachment to drums	5.07100.0001
	(house gas / gas bottle) Filling nozzle with stainless	Recommended safety products	Antistatic set (3 cables) Drum opening key	1.07070.0001 1.08803.0001	
Set components	steel coated, flexible PTFE-9.67100.9090tube (80 cm)9.67100.9051Gas feeding tube9.67100.9051Threaded adapter with9.67100.9002vertical connections9.67100.902	9.67100.9090	90	Filling nozzle with stainless steel coated, flexible PTFE-tube (80 cm)	9.67100.9090
		Spare parts	Gas feeding tube Threaded adapter with horizontal connections	9.67100.9051 9.67100.9003 9.67100.9002	

### Withdrawal Systems for solvent drums



#### Manual pressure build-up for high volumes


- Safe, easy and convenient solvent handling
- Usage of tested high quality materials to ensure a reliable, contamination free and safe handling of our solvents
- High flexibility due to independence on gas supply



#### System at a glance

Order number	1.19171.0001	Necessary completive products	Reducer (PE) from S56 x 4 to 2" thread (for combi drum)	9.67202.0000
Suitability	180 I / 190 I / 200 I metal and stainless steel drums	Recommended safety	Antistatic set (3 cables)	1.07070.0001
Operation mode Manual pressure build-up by foot pump ball		products	Drum opening key	1.08803.0001
Set components	Withdrawal system body with 2" thread Foot pump ball with flexible tube and rapid action connector Adjustable dip tube	Spare parts	-	

### Ordering information Inorganics & Solvents







**EMSURE**<sup>®</sup> | **EMPARTA**<sup>®</sup> | **EMPLURA**<sup>®</sup> acids offer the highest possible quality, greatest safety and optimized packaging – for a multitude of analytical applications. Every product undergoes strict quality checks using the most sensitive instruments and methods.

EMSURE <sup>®</sup> Acids	Premium Grade
For more information please have a look at page 22	
	Standard Grade
For more information please have a look at page 32	
	Basic Grade
For more information please have a look at page 36	

# Ordering information Acids

Α	ci	ds	: A	-B

Product	CAS No.	Chemical formula	Content	Packaging	Ord. I
Acetic acid 30% for analysis EMSURE <sup>®</sup> Reag. Ph Eur			500 ml	Glass bottle	1.59166.05
Acetic acid 60% EMPLURA®			25 I	PE canister	4.80362.90
			1	Glass bottle	1.00062.10
			1	HDPE bottle	1.00062.10
			2.5 I	Glass bottle	1.00062.2
Acetic acid 96% for analysis EMSURE®			2.5 I	HDPE bottle	1.00062.2
			25 I	PE canister	1.00062.9
			200 I	PE drum	1.00062.9
			500 ml	Safebreak bottle	1.00063.0
			1	Glass bottle	1.00063.1
			1	Safebreak bottle	1.00063.1
			1	HDPE bottle	1.00063.1
Acetic acid (glacial) 100% anhydrous for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	64-19-7	CH₃COOH	2.5 I	Glass bottle	1.00063.2
			2.5 I	Safebreak bottle	1.00063.2
			2.5 I	HDPE bottle	1.00063.2
			25 I	PE canister	1.00063.9
			200 I	PE drum	1.00062.9
Acetic acid (glacial) 100% for analysis EMPARTA® ACS	64-19-7	CH₃COOH	2.5 l	HDPE bottle	1.01830.2
			25 I	PE canister	1.01830.9
Acetic anhydride for analysis EMSURE® ACS, ISO, Reag. Ph Eur			1	Glass bottle	1.00042.1
	108-24-7	(CH <sub>3</sub> CO) <sub>2</sub> O	2.5 l	Glass bottle	1.00042.2
			25 I	PE canister	1.00042.9
	5220 14 6		100 g	HDPE bottle	1.00103.0
Amidosulfuric acid for analysis EMSURE®	5329-14-6	$H_2NSO_3H$	250 g	HDPE bottle	1.00103.0
	5000 44 6		2.5 kg	HDPE bottle	1.00219.2
Amidosulfuric acid EMPLURA®	5329-14-6	$H_2NSO_3H$	25 kg	Fibre carton	1.00219.9
			100 g	HDPE bottle	1.00468.0
L(+)-Ascorbic acid for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	50-81-7	$C_6H_8O_6$	500 g	HDPE bottle	1.00468.0
			1 kg	HDPE bottle	1.00468.1
		C U N O	25 g	HDPE bottle	1.00132.0
Barbituric acid for analysis EMSURE®	67-52-7	$C_4H_4N_2O_3$	100 g	HDPE bottle	1.00132.0
			100 g	HDPE bottle	1.00136.0
	65.05.0		250 g	HDPE bottle	1.00136.0
Benzoic acid for analysis EMSURE® Reag. Ph Eur	65-85-0	C₀H₅COOH	1 kg	HDPE bottle	1.00136.1
			25 kg	Fibre carton	1.00136.9
			100 g	HDPE bottle	1.00165.0
			500 g	HDPE bottle	1.00165.0
Boric acid for analysis EMSURE® ACS, ISO, Reag. Ph Eur			1 kg	HDPE bottle	1.00165.1
	10043-35-3	H <sub>3</sub> BO <sub>3</sub>	5 kg	HDPE bottle	1.00165.5
			12 kg	PE bucket	1.00165.9
			25 kg	Fibre carton	1.00165.9

	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
С				500 g	HDPE bottle	1.00244.0500
				1 kg	HDPE bottle	1.00244.1000
	Citric acid monohydrate for analysis EMSURE® ACS, ISO, Reag. Ph Eur	5949-29-1	$C_6H_8O_7 * H_2O$	5 kg	HDPE bottle	1.00244.5000
	·····			12 kg	PE bucket	1.00244.9012
				25 kg	Fibre carton	1.00244.9026
F	Formic acid 89-91% for analysis EMSURE® ACS			1	Glass bottle	1.00253.1000
	Formic acid 90% for determination of viscosity acc. to DIN EN ISO 307			2.5 I	Glass bottle	1.10854.2500
				100 ml	Glass bottle	1.00264.0100
				1	Glass bottle	1.00264.1000
	Formic acid 98–100% for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	64-18-6	НСООН	2.5 l	Glass bottle	1.00264.2500
	,			25 I	PE canister	1.00264.9026
				200 I	PE drum	1.00264.9200
G	Glycolic acid for analysis EMSURE®	79-14-1	HOCH <sub>2</sub> COOH	100 g	HDPE bottle	1.04106.0100
н	Hydrobromic acid 47% for analysis EMSURE® ACS, ISO			1	Glass bottle	1.00307.1000
				500 ml	Glass bottle	1.00304.0500
	Hydrobromic acid 47% EMPLURA®			2.5 I	Glass bottle	1.00304.2500
				20 I	Carboy	1.00304.9020
				1	Glass bottle	1.00316.1000
				1	HDPE bottle	1.00316.1011
	Hydrochloric acid 25% for analysis EMSURE®			2.5 I	Glass bottle	1.00316.2500
				2.5 I	HDPE bottle	1.00316.2511
				25 I	PE canister	1.00316.9025
				1	Glass bottle	1.00319.1000
				1	HDPE bottle	1.00319.1011
	Hudroshlaris asid 270% for analysis EMCUDE®			2.5 I	Glass bottle	1.00319.2500
	Hydrochloric acid 32% for analysis EMSURE®			2.5 I	HDPE bottle	1.00319.2511
				25 I	PE canister	1.00319.9025
				200 I	PE drum	1.00319.9200
				2.5 I	Glass bottle	1.00313.2500
	Hydrochloric acid 32% EMPLURA®			25 I	PE canister	1.00313.9025
				180 I	PE drum	1.00313.9180
	Hydrochloric acid fuming 37% for analysis max. 0.001 ppm Hg EMSURE®			2.5 I	Glass bottle	1.13386.2500
				500 ml	Safebreak bottle	1.00317.0510
				1	Glass bottle	1.00317.1000
				1	Safebreak bottle	1.00317.1010
				1	HDPE bottle	1.00317.1011
	Hydrochloric acid fuming 37% for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur			2	HDPE bottle	1.00317.2011
	·····, ····, ·····			2.5 I	Glass bottle	1.00317.2500
				2.5 I	Safebreak bottle	1.00317.2510
				25 I	PE canister	1.00317.9026

200 I

PE drum

Acids C-H

1.00317.9200

# Ordering information Acids

Acids H-N

	Acids H-N					
	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
н	Under shirt of the forming 270/ for an electron			2	HDPE bottle	1.01834.2011
	Hydrochloric acid fuming 37% for analysis EMPARTA <sup>®</sup> ACS			2.5 I	Glass bottle	1.01834.2502
				25 I	PE canister	1.01834.9025
	Hydrofluoric acid 38-40% EMPLURA®			1	HDPE bottle	1.00337.1000
				2.5	HDPE bottle	1.00337.2500
				500 ml	HDPE bottle	1.00338.0500
	Hydrofluoric acid 40% for analysis EMSURE <sup>®</sup> ISO, Reag. Ph Eur			1	HDPE bottle	1.00338.1000
				2.5 I	HDPE bottle	1.00338.2500
				500 ml	HDPE bottle	1.00334.0500
	Hydrofluoric acid 48%			1	HDPE bottle	1.00334.1000
	for analysis EMSURE® ACS, ISO, Reag. Ph Eur			2.5 l	HDPE bottle	1.00334.2500
				5 I	PE canister	1.00334.5000
				250 ml	HDPE bottle	1.07210.0250
	Hydrogen peroxide 30% (Perhydrol™)			1	HDPE bottle	1.07210.1000
	(stabilized for higher storage temp.) for analysis EMSURE® ISO			2.5 I	HDPE bottle	1.07210.2500
				25 I	PE canister	1.07210.9025
				250 ml	HDPE bottle	1.07209.0250
	Hydrogen peroxide 30% (Perhydrol™)			500 ml	HDPE bottle	1.07209.0500
	for analysis EMSURE® ISO			1	HDPE bottle	1.07209.1000
				2.5	HDPE bottle	1.07209.2500
	Hydrogen peroxide 35% EMPLURA®			25 I	PE canister	1.08556.9025
				250 ml	Glass bottle	1.00344.0250
	Hydroiodic acid 57% for analysis EMSURE®			1	Glass bottle	1.00344.1000
				250 ml	Glass bottle	1.00341.0250
	Hydroiodic acid 57% EMPLURA®			22	Carboy	1.00341.9022
	Hydroiodic acid 67% for analysis EMSURE®			250 ml	Glass bottle	1.00345.0250
	Hypophosphorous acid 50% for analysis EMSURE®			500 ml	Glass bottle	1.04633.0500
м	Molybdatophosphoric acid hydrate			25 g	Glass bottle	1.00532.0025
	for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	51429-74-4	$H_3[P(Mo_3O_{10})_4] * x H_2O$	100 g	Glass bottle	1.00532.0100
	Molybdic acid about 85% MoO <sub>3</sub> (containing ammonium molybdate) EMPLURA®	7782-91-4	H <sub>2</sub> MoO <sub>4</sub>	1 kg	HDPE bottle	1.00400.1000
N				1	Glass bottle	1.00452.1000
	Nitric acid 65% for analysis (max. 0.005 ppm Hg) EMSURE <sup>®</sup> Reag. Ph Eur, ISO			2.5	Glass bottle	1.00452.2500
	(max. 0.005 ppin rig) EnSOKE Reay. Fil Eul, ISU			180 I	PE / Metal drum	1.00452.9180
				500 ml	Safebreak bottle	1.00456.0510
				1	Glass bottle	1.00456.1000
				1	Safebreak bottle	1.00456.1010
	Nitric acid 65% for analysis EMSURE® Reag. Ph Eur, ISO			2.5	Glass bottle	1.00456.2500
	TOT analysis LPISONL Nedy, FILEU, ISO			2.5	Safebreak bottle	1.00456.2510
				25 I	PE / Metal drum	1.00456.9026
				180 I	PE / Metal drum	1.00456.9180

Acids

#### Acids N-P

	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No
I.				1	Glass bottle	1.00443.1000
				2.5 I	Glass bottle	1.00443.2500
	Nitric acid 65% EMPLURA®			25 I	PE / Metal drum	1.00443.9025
				180 I	PE / Metal drum	1.00443.918
				500 ml	Safebreak bottle	1.01799.051
				1	Glass bottle	1.01799.100
	Nitric acid 69%			1	Safebreak bottle	1.01799.101
	for analysis EMSURE® ACS, Reag. Ph Eur			2.5 I	Glass bottle	1.01799.250
				2.5 I	Safebreak bottle	1.01799.251
				180 I	PE / Metal drum	1.01799.918
				2.5 l	Glass bottle	1.01832.250
	Nitric acid 69% for analysis EMPARTA® ACS			25 I	PE / Metal drum	1.01832.902
	Nitric acid fuming 100% for analysis EMSURE® Reag. Ph Eur	7697-37-2	HNO <sub>3</sub>	1	Glass btl. pl. coat.	1.00455.100
				100 g	HDPE bottle	1.00495.010
	Oxalic acid dihydrate			500 g	HDPE bottle	1.00495.050
	for analysis EMSURE® ACS, ISO, Reag. Ph Eur	6153-56-6	(COOH) <sub>2</sub> * 2 H <sub>2</sub> O	1 kg	HDPE bottle	1.00495.100
				 25 kg	Fibre carton	1.00495.902
	Oxalic acid dihydrate EMPLURA®				HDPE bottle	1.00492.100
		6153-56-6	(COOH) <sub>2</sub> * 2 H <sub>2</sub> O		HDPE bottle	1.00492.500
	·			50 kg	Fibre carton	1.00492.905
				11	Glass bottle	1.00518.100
	Perchloric acid 60%			6 x 1	Glass bottle	1.00518.101
	for analysis EMSURE® ACS			2.5 I	Glass bottle	1.00518.250
				4 x 2.5 l	Glass bottle	1.00518.251
	Perchloric acid 70% for analysis			1	Glass bottle	1.00514.100
	(max. 0.0000005% Hg) EMSURE® ACS, ISO, Reag. Ph Eur			6 x 1	Glass bottle	1.00514.100
					Safebreak bottle	1.00519.051
				11	Glass bottle	1.00519.100
				11	Safebreak bottle	1.00519.101
	Perchloric acid 70–72%			6 x 1	Glass bottle	1.00519.101
	for analysis EMSURE® ACS, ISO, Reag. Ph Eur			2.5	Glass bottle	1.00519.250
				4 x 2.5 l	Glass bottle	1.00519.251
				2.5	Safebreak bottle	1.00519.251
				25 g	Glass bottle	1.00524.002
	Periodic acid for analysis EMSURE®	10450-60-9	H <sub>5</sub> IO <sub>6</sub>	100 g	Glass bottle	1.00524.010
	maka Dhaankaria arid sissaa fay analysia			100 g	Metal can	1.00546.010
	meta-Phosphoric acid pieces for analysis (stabilized with sodium metaphosphate) EMSURE®			500 g	Metal can	1.00546.050
	· · · · ·				Safebreak bottle	1.00573.051
				1	HDPE bottle	1.00573.100
				2.5	HDPE bottle	1.00573.250
	ortho-Phosphoric acid 85% for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur			2.5	Safebreak bottle	
	,,					1.00573.251
				25	PE canister	1.00573.902
				200 I	PE drum	1.00573.920

# Ordering information Acids

Acids O-S

Product	CAS No.	Chemical formula	Content	Packaging	Ord. N
ortho-Phosphoric acid 99% cryst. for analysis EMSURE®	7664-38-2	H <sub>3</sub> PO <sub>4</sub>	500 g	HDPE bottle	1.00565.050
			250 g	HDPE bottle	1.00682.025
Succinic acid for analysis EMSURE® ACS	110-15-6	HOOCCH <sub>2</sub> CH <sub>2</sub> COOH	500 g	HDPE bottle	1.00682.050
			25 kg	Fibre carton	1.00682.902
Sulfuric acid 25% for analysic EMSUDE®			1	HDPE bottle	1.00716.100
Sulfuric acid 25% for analysis EMSURE®			25 I	PE canister	1.00716.902
Sulfuric acid 40% for determination of gas metabolism acc. to knipping			2.5 I	Glass bottle	1.09286.250
Sulfuric acid 62% for analysis EMSURE <sup>®</sup> ,			1	HDPE bottle	4.80531.10
for the determination of fat in cheese (d 1.52)			2.5 I	HDPE bottle	4.80531.25
			500 ml	Glass bottle	1.00729.05
Sulfuric acid 90–91% for gerber fat determination and determination of nitrates in milk			2.5 I	Glass bottle	1.00729.25
			25 I	PE canister	1.00729.90
			500 ml	Safebreak bottle	1.00732.05
Sulfuric acid 95–97% for analysis			1	Glass bottle	1.00732.10
(max. 0.005 ppm Hg) EMSURE® ACS, ISO,	7664-93-9	$H_2SO_4$	2.5 I	Glass bottle	1.00732.25
Reag. Ph Eur			2.5 I	Safebreak bottle	1.00732.25
			25 I	PE canister	1.00732.90
	7664-93-9	H <sub>2</sub> SO <sub>4</sub>	500 ml	Safebreak bottle	1.00731.05
			1	Glass bottle	1.00731.10
			1	Safebreak bottle	1.00731.10
			1	HDPE bottle	1.00731.10
Sulfuric acid 95-97% for analysis EMSURE® ISO			2.5 I	Glass bottle	1.00731.25
			2.5 I	Safebreak bottle	1.00731.25
			2.5	HDPE bottle	1.00731.25
			25 I	PE canister	1.00731.90
			200	PE drum	1.00731.92
			2.5	HDPE bottle	1.01833.25
Sulfuric acid 95–97% for analysis EMPARTA® ACS	7664-93-9	$H_2SO_4$	25 I	PE canister	1.01833.90
Sulfuric acid 96% for the determination of			1	HDPE bottle	1.08131.10
viscosity acc. to DIN EN ISO 307	7664-93-9	$H_2SO_4$	2.5	HDPE bottle	1.08131.25
			500 ml	Safebreak bottle	1.12080.05
			1	Glass bottle	1.12080.10
Sulfuric acid 98% for analysis EMSURE®	7664-93-9	$H_2SO_4$	2.5	Glass bottle	1.12080.25
			2.5	Safebreak bottle	1.12080.25
		NE	W 25 I	PE canister	1.12080.90
				Glass bottle	1.00748.05
Sulfuric acid 98% for the determination of nitrogen	7664-93-9	H₂SO₄	2.5	Glass bottle	1.00748.25
2		• •	25 I	PE canister	1.00748.90
Sulfuric acid fuming 65% SO $_{3}$ (Oleum) EMPLURA®	8014-95-7	H <sub>2</sub> SO <sub>4</sub> * SO <sub>3</sub> (1:2)	11	Glass btl. pl. coat.	1.00720.10
			1	Glass bottle	1.00761.10
Sulfurous acid 5–6% $SO_2$ for analysis EMSURE <sup>®</sup>			2.5	Glass bottle	1.00761.25

Aci	de	T-7	
ACI	us	1-2	

Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
			250 g	HDPE bottle	1.00804.0250
L(+)-Tartaric acid for analysis EMSURE® ACS, ISO,	97 60 4	HOOCCH(OH)CH(OH)	1 kg	HDPE bottle	1.00804.1000
Reag. Ph Eur	87-69-4	СООН	5 kg	HDPE bottle	1.00804.5000
			50 kg	Fibre carton	1.00804.9050
Toluene-4-sulfonic acid monohydrate for analysis EMSURE® ACS			100 g	HDPE bottle	1.09613.0100
	6192-52-5	$CH_3C_6H_4SO_3H * H_2O$	500 g	HDPE bottle	1.09613.0500
	76-03-9	CCI₃COOH	100 g	Glass bottle	1.00807.0100
Trichloroacetic acid for analysis EMSURE® ACS, Reag. Ph Eur			250 g	Glass bottle	1.00807.0250
			1 kg	Glass bottle	1.00807.1000
Tungstophosphoric acid hydrate for analysis	12501 22 4	$H_3[P(W_3O_{10})_4] * x H_2O$	100 g	HDPE bottle	1.00583.0100
EMSURE®	12501-23-4		250 g	HDPE bottle	1.00583.0250
	12501 22 4		100 g	HDPE bottle	1.00582.0100
Tungstophosphoric acid hydrate cryst. EMPLURA®	12501-23-4	$H_3[P(W_3O_{10})_4] * x H_2O$	25 kg	Fibre carton	1.00582.9025
Tungstosilicic acid hydrate for analysis EMSURE®	12027-43-9	H <sub>4</sub> [Si(W <sub>3</sub> O <sub>10</sub> ) <sub>4</sub> ] * x H <sub>2</sub> O	100 g	HDPE bottle	1.00659.0100



For more details about our packaging, please see "Packaging and Safe Handling" on page 42

# caustic alkalis and bases

### EMSURE® | EMPLURA®

Our high-quality caustic alkalis and bases are produced using specially selected raw materials. The range includes sodium and potassium hydroxide pellets and corresponding solutions, as well as ammonia solutions in various concentrations and grades. Simply choose the right product for your application.

**EMSURE**<sup>®</sup> Caustic alkalis and bases

Premium Grade

▶ For more information please have a look at page 22

EMPLURA<sup>®</sup> Caustic alkalis and bases

Basic Grade

▶ For more information please have a look at page 36

### Ordering information Caustic alkalis and bases

#### **Caustics and bases A-S**

	Product	CAS No.	Chemical formula	Content	Packaging	Ord.
1				1	Glass bottle	1.05432.1
				1	HDPE bottle	1.05432.1
	Ammonia solution 25% for analysis EMSURE®			2.5 I	Glass bottle	1.05432.2
	ISO, Reag. Ph Eur			5	HDPE bottle	1.05432.5
				25 I	PE canister	1.05432.9
			NE	N 180 I	PE / Metal drum	1.05432.9
				1	Glass bottle	1.05423.1
	Ammonia solution 28-30% for analysis			2.5 I	Glass bottle	1.05423.2
	EMSURE® ACS, Reag. Ph Eur			25 I	PE canister	1.05423.9
				180 I	PE / Metal drum	1.05423.9
	Ammonia colution 200/ EMDLUDA®			1	Glass bottle	1.05426.1
	Ammonia solution 32% EMPLURA®			2.5 I	Glass bottle	1.05426.2
Ρ				1 kg	HDPE bottle	1.05029.1
	Potassium hydroxide pellets for analysis max. 0.05% Na) EMSURE <sup>®</sup> ACS, Reag. Ph Eur	1310-58-3	КОН	12 kg	PE bucket	1.05029.9
	max. 0.05 /0 Na) EMSORE' ACS, Reag. FIT Eur			50 kg	HDPE box	1.05029.9
				500 g	HDPE bottle	1.05033.0
	Potassium hydroxide pellets for analysis EMSURE®			1 kg	HDPE bottle	1.05033.1
		1310-58-3	КОН	5 kg	HDPE bottle	1.05033.5
				25 kg	HDPE box	1.05033.9
				50 kg	Fibre carton	1.05033.9
	Potassium hydroxide pellets EMPLURA®			1 kg	HDPE bottle	1.05012.1
		1310-58-3	КОН	5 kg	HDPE bottle	1.05012.5
				50 kg	HDPE box	1.05012.9
	Potassium hydroxide solution 32%			1	HDPE bottle	1.05501.1
	(max. 0.005% Na) for analysis EMSURE®			2.5 I	HDPE bottle	1.05501.2
	Potassium hydroxide solution 47%			1	HDPE bottle	1.05545.1
	for analysis EMSURE®			25 I	PE canister	1.05545.9
5				1 kg	HDPE bottle	1.06469.1
	Sodium hydroxide pellets for analysis (max. 0.02% K) EMSURE <sup>®</sup> ACS, ISO, Reag.	1310-73-2	NaOH	5 kg	HDPE bottle	1.06469.5
	Ph Eur	1310-73-2	NaOH	12 kg	PE bucket	1.06469.9
				50 kg	HDPE box	1.06469.9
				500 g	HDPE bottle	1.06498.0
				1 kg	HDPE bottle	1.06498.1
	Sodium hydroxide pellets for analysis EMSURE®	1310-73-2	NaOH	5 kg	HDPE bottle	1.06498.5
				25 kg	HDPE box	1.06498.9
				50 kg	HDPE box	1.06498.9
				1 kg	HDPE bottle	1.06462.1
	Sodium hydroxide pellets EMPLURA®	1310-73-2	NaOH	5 kg	HDPE bottle	1.06462.5
				50 ka	HDPE box	1.06462.9

#### Caustics and bases S-Z

	Product	CAS No.	Chemical formula	Content	Packaging	Ord. N
Sodium hydroxide granulated EMPLURA®	1010 70 0	NEOL	10 kg	HDPE bottle	1.06467.901	
		1310-73-2	NaOH	50 kg	Fibre carton	1.06467.905
	Sodium hydroxide solution min. 10% (1.11)			1	HDPE bottle	1.05588.100
	for analysis EMSURE®			10	PE canister	1.05588.90
	Sodium hydroxide solution 21% for analysis EMSURE®			25	PE canister	1.05593.90
	Sodium hydroxide solution min. 27% (1.30)			2.5 I	HDPE bottle	1.05591.25
	for analysis (for the determination of nitrogen) EMSURE®			25 I	PE canister	1.05591.90
	Sodium hydroxide solution about 32%			1	HDPE bottle	1.05500.10
	(max. 0.002% K) for analysis EMSURE®			2.5 I	HDPE bottle	1.05500.25
	Sodium hydroxide solution about 32% (for the determination of nitrogen) for analysis EMSURE®			2.5 I	HDPE bottle	1.05590.25
				25 I	PE canister	1.05590.90
				200 I	PE drum	1.05590.92
				2.5 I	HDPE bottle	1.05587.25
	Codium hydrovido colution shout 220/ EMDLUDA®			5	HDPE bottle	1.05587.50
	Sodium hydroxide solution about 32% EMPLURA®			25 I	PE canister	1.05587.90
				200 I	PE drum	1.05587.92
	Sodium hydroxide solution about 36% for analysis EMSURE®			5	HDPE bottle	1.05596.50
	Sodium hydroxide solution min. 45%			2.5 I	HDPE bottle	1.11360.25
	for analysis EMSURE®			25 I	PE canister	1.11360.90
				1	HDPE bottle	1.58793.10
	Sodium hydroxide solution 50% for analysis			5	HDPE bottle	1.58793.50
	EMSURE®			25 I	PE canister	1.58793.90
				200 I	PE drum	1.58793.92



For more details about our packaging, please see "Packaging and Safe Handling" on page 42

# metals and metal oxides



**EMSURE**<sup>®</sup> | **EMPLURA**<sup>®</sup> metal salts, metals and noble metals are renowned for their high quality and purity. We offer a diverse range of products suitable for a multitude of applications in R&D, production and quality control.

**EMSURE**<sup>®</sup> Metals and metal oxides

Premium Grade

▶ For more information please have a look at page 22

**EMPLURA®** Metals and metal oxides

Basic Grade

▶ For more information please have a look at page 36

## Ordering information Metals and metal oxides

#### Metals and metal oxides A-H

	Metals and metal oxides A-H					
	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
A	Aluminium fine powder, stabilized about 2% fat	7429-90-5	Al	250 g	Metal can	1.01056.0250
				1 kg	Metal can	1.01056.1000
	Aluminium (foil) for analysis 0.3 mm thickness,	7429-90-5	Al	250 g	Fibre case	1.01057.0250
	30 mm width EMSURE®	7425 50 5		1 kg	Fibre case	1.01057.1000
	Antimony(III) chloride for analysis EMSURE <sup>®</sup> ACS	10025-91-9	SbCl <sub>3</sub>	250 g	Glass bottle	1.07838.0250
	Antimoliy(III) chloride for analysis EMSORE® ACS	10025-91-9	SDCI3	1 kg	Glass bottle	1.07838.1000
	Antimony(III) oxide for analysis EMSURE <sup>®</sup>	1200 64 4	Sh O	100 g	HDPE bottle	1.07836.0100
	Antimony(III) oxide for analysis EMSORE®	1309-64-4	Sb <sub>2</sub> O <sub>3</sub>	1 kg	HDPE bottle	1.07836.1000
		1200 64 4	Sh O	2.5 kg	HDPE bottle	1.07835.2500
	Antimony(III) oxide EMPLURA®	1309-64-4	Sb <sub>2</sub> O <sub>3</sub>	50 kg	Fibre carton	1.07835.9050
в		1004 76 0	5: 0	1 kg	HDPE bottle	1.01862.1000
	Bismuth(III) oxide EMPLURA®	1304-76-3	Bi <sub>2</sub> O <sub>3</sub>	25 kg	Fibre carton	1.01862.9025
				50 ml	Glass btl. pl.coat.	1.01948.0050
	Bromine for analysis EMSURE® ACS, ISO, Reag. Ph Eur	7726-95-6	Br <sub>2</sub>	250 ml	Glass bottle	1.01948.0250
	Reag. Fil Eul			1	Glass btl. pl.coat.	1.01948.1000
				250 ml	Glass bottle	1.01945.0250
	Bromine EMPLURA®	7726-95-6	Br <sub>2</sub>	1	Glass btl. pl.coat.	1.01945.1000
с	Cadmium coarse powder, for analysis and for filling reductors particle size about 0.3-1.6 mm EMSURE®	7440-43-9		250 g	Metal can	1.02001.0250
			Cd	1 kg	Metal can	1.02001.1000
	Cadmium granular, for analysis particle size about		Cd	250 g	Metal can	1.02004.0250
		7647-17-8		25 g	Glass bottle	1.02038.0025
	Cesium chloride for analysis EMSURE®		CsCl	100 g	HDPE bottle	1.02038.0100
	Cesium chloride EMPLURA®	7647-17-8	CsCl	1 kg	HDPE bottle	1.02041.1000
				25 g	Glass bottle	1.02856.0025
	Cesium nitrate 99+ for analysis EMSURE®	7789-18-6	CsNO <sub>3</sub>	1 kg	HDPE bottle	1.02856.1000
	Chromium(VI) oxide for analysis EMSURE®	1333-82-0	CrO <sub>3</sub>	250 g	Glass bottle	1.00229.0250
	Copper fine powder particle size < 63 MYm			250 g	HDPE bottle	1.02703.0250
	(> 230 mesh ASTM) EMSURE®	7440-50-8	Cu	1 kg	HDPE bottle	1.02703.1000
	Copper foil about 0.1 mm thickness for analysis EMSURE®	7440-50-8	Cu	250 g	Fibre case	1.02700.0250
	Copper(II) oxide granular for analysis EMSURE®	1317-38-0	CuO	500 g	HDPE bottle	1.02768.0500
				100 g	HDPE bottle	1.02766.0100
	Copper(II) oxide powder	1317-38-0	CuO	500 g	HDPE bottle	1.02766.0500
	for analysis EMSURE® ACS			25 kg	Fibre carton	1.02766.9025
				500 g	HDPE bottle	1.02761.0500
	Copper(II) oxide powder EMPLURA®	1317-38-0	CuO		PE bucket	1.02761.9025
D				250 g	HDPE bottle	1.05341.0250
-	Devarda's alloy for analysis EMSURE®	8049-11-4	Cu / Al / Zn		HDPE bottle	1.05341.1000

#### Metals and metal oxides I-R

	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
	Iron for analysis reduced, particle size 10 µm		_	100 g	HDPE bottle	1.03819.0100
	EMSURE®	7439-89-6	Fe	500 g	HDPE bottle	1.03819.0500
	di-Iodine pentoxide for analysis granular 0.5-2.5 mm EMSURE®	12029-98-0	$I_2O_5$	100 g	Glass bottle	1.00358.0100
	Iodine sublimated for analysis EMSURE® ACS,	7553-56-2	I <sub>2</sub>	100 g	Glass bottle	1.04761.0100
	ISO, Reag. Ph Eur.	7555-50-2	12	500 g	Glass bottle	1.04761.0500
	Lanthanum(III) oxide EMPLURA®	1312-81-8	La <sub>2</sub> O <sub>3</sub>	100 g	HDPE bottle	1.12220.0100
		1512 01 0	Lu <sub>2</sub> O <sub>3</sub>	500 g	HDPE bottle	1.12220.0500
	Lead foil for analysis about 0.25 mm thick $EMSURE^{\circledast}$	7439-92-1	Pb	500 g	Fibre case	1.07365.0500
		xide for analysis EMSURE® 1317-36-8 PbO	DF O	250 g	HDPE bottle	1.07401.0250
	Lead(11) oxide for analysis EMSURE®		PDU	1 kg	HDPE bottle	1.07401.1000
		LURA® 1317-36-8 PbO	DI- O	5 kg	HDPE bottle	1.05658.5000
	Lead(II) oxide EMPLURA®	1317-36-8		50 kg	PE drum	1.05658.9050
	Lithium hydroxide 98% + for analysis EMSURE®	1310-65-2	LiOH	100 g	HDPE bottle	1.05691.0100
		1310-05-2	LION	1 kg	HDPE bottle	1.05691.1000
1	Magnesium foil 0.15-0.30 mm thickness, 3 mm wide	7439-95-4	Mg	1 rol (~ 25 g)		1.05812.0001
	Magnesium powder particle size about 0.06–0.3 mm	7439-95-4	Mg	1 kg	Metal can	1.05815.1000
	Magnesium oxide for analysis	1200 40 4		100 g	HDPE bottle	1.05866.0100
	(max. 0.001% SO₄) EMSURE® ACS	1309-48-4	MgO	500 g	HDPE bottle	1.05866.0500
		1309-48-4	M-O	100 g	HDPE bottle	1.05865.0100
	Magnesium oxide for analysis EMSURE®	1309-48-4	MgO	500 g	HDPE bottle	1.05865.0500
	Manganese(IV) oxide powder EMPLURA®	1313-13-9	MpO	1 kg	Glass bottle	1.05957.1000
		1313-13-9	MnO <sub>2</sub>	25 kg	Fibre carton	1.05957.9025
	Malyhdanum()/I) ayida far analysia EMCUDE®	1313-27-5	MaQ	100 g	HDPE bottle	1.00403.0100
	Molybdenum(VI) oxide for analysis EMSURE®	1313-27-5	MoO <sub>3</sub>	500 g	HDPE bottle	1.00403.0500
	Palladium powdered 99+ for analysis EMSURE®	7440-05-3	Pd	1 g	Glass bottle	1.19225.0001
		7440-05-5	ru	5 g	Glass bottle	1.19225.0005
	Platinum black 98+ for analysis EMSURE®	7440-06-4	Pt	5 g	Glass bottle	1.19233.0005
		/++0-00-4	і с.	50 g	HDPE bottle	1.19233.0050
ł	Rubidium chloride for analysis EMSURE®	7791-11-9	RbCl	25 g	Glass bottle	1.07615.0025
	Ruthenium(III) chloride hydrate for analysis	14898-67-0	RuCl <sub>3</sub> * x H <sub>2</sub> O	5 g	Glass bottle	1.19247.0005
	EMSURE®	14090-07-0		25 g	Glass bottle	1.19247.0025

## Ordering information Metals and metal oxides

#### Metals and metal oxides S-Y

	Metals and metal oxides 5-1					
	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
S				50 g	HDPE bottle	1.07714.0050
	Selenium black 99+ for analysis EMSURE®	7782-49-2	Se	250 g	HDPE bottle	1.07714.0250
				1 kg	HDPE bottle	1.07714.1000
				25 g	HDPE bottle	1.19203.0025
	Silver chloride 99+ for analysis EMSURE®	7783-90-6	AgCl	100 g	HDPE bottle	1.19203.0100
				1 kg	HDPE bottle	1.19203.1000
	Silver diethyldithiocarbamate for analysis EMSURE <sup>®</sup> Reag. Ph Eur	1470-61-7	$C_5H_{10}AgNS_2$	5 g	Glass bottle	1.01515.0005
		20007 12 2	A= 0	25 g	HDPE bottle	1.19208.0025
	Silver oxide 99+ for analysis EMSURE®	20667-12-3	Ag <sub>2</sub> O	100 g	HDPE bottle	1.19208.0100
	Sodium rod diameter 2.5 cm (protective liquid: paraffin oil)	7440-23-5	Na	250 g	Glass bottle	1.06260.0250
т	Tetrachloroauric(III) acid trihydrate 99%	16961-25-4	AuCl <sub>4</sub> H*3H <sub>2</sub> O	1 g	Glass ampoule	1.01582.0001
	for analysis EMSURE®	10901-25-4	AuCl <sub>4</sub> H <sup>•</sup> 5H <sub>2</sub> O	5 g	Glass ampoule	1.01582.0005
	Tin fine powder EMPLURA <sup>®</sup> (particle size < 71 $\mu$ m)	7440-31-5	Sn	250 g	HDPE bottle	1.07807.0250
	Tin foil about 0.04 mm thick	7440-31-5	Sn	200 strips	Plastic box	1.07826.0001
	Tin granulated for analysis (particle size about	7440-31-5	Sn	250 g	HDPE bottle	1.07806.0250
	4 mm) EMSURE <sup>®</sup> Reag. Ph Eur	7440-31-3	511	1 kg	HDPE bottle	1.07806.1000
	Tin(IV) oxide EMPLURA®	18282-10-5	SnO <sub>2</sub>	250 g	HDPE bottle	1.07818.0250
		10202-10-5	31102	25 kg	Fibre carton	1.07818.9025
				1 kg	HDPE bottle	1.00808.1000
	Titanium(IV) oxide for analysis EMSURE <sup>®</sup> Reag. Ph Eur	13463-67-7	TiO <sub>2</sub>	25 kg	Fibre carton	1.00808.9025
				50 kg	Fibre carton	1.00808.9050
v	Vanadium(V) oxide EMPLURA®	1314-62-1	V <sub>2</sub> O <sub>5</sub>	250 g	HDPE bottle	1.00824.0250
		1314-02-1	<b>v</b> <sub>2</sub> <b>v</b> <sub>5</sub>	1 kg	HDPE bottle	1.00824.1000
Y	Yttrium oxide 99+ for analysis EMSURE®	1314-36-9	Y <sub>2</sub> O <sub>3</sub>	25 g	HDPE bottle	1.12412.0025

#### Metals and metal oxides Z

	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
z	Zinc coarse powder for analysis suitable for filling of reductors, particle size about 0.3 – 1.5 mm	7440-66-6	Zn	250 g	Metal can	1.08756.0250
	(14–50 mesh ASTM) EMSURE® Reag. Ph Eur	7440-00-0	211	1 kg	Metal can	1.08756.1000
	Zinc dust particle size < 63 µm EMPLURA®	7440-66-6	Zn	1 kg	HDPE bottle	1.08774.1000
		7440-00-0	211	50 kg	Steel drum	1.08774.9050
	Zinc granular for analysis, particle size	7440-66-6	Zn	500 g	HDPE bottle	1.08780.0500
	about 3-8 mm EMSURE® ISO	7440-00-0 Z	211	1 kg	HDPE bottle	1.08780.1000
	Zinc powder for analysis particle size < 45 $\mu$ m	7440-66-6 Z	Zn	500 g	Metal can	1.08789.0500
	EMSURE®		Zn	1 kg	Metal can	1.08789.1000
	Zinc sticks, triangular cross section about 8 mm for analysis EMSURE®	7440-66-6	Zn	500 g	Fibre case	1.08782.0500
				500 g	HDPE bottle	1.08849.0500
	Zinc oxide for analysis EMSURE® ACS, Reag. Ph Eur	1314-13-2	ZnO	1 kg	HDPE bottle	1.08849.1000
			-	25 kg	Fibre carton	1.08849.9025
	Zirconium(IV) oxide chloride octahydrate for analysis EMSURE®	13520-92-8	ZrOCl <sub>2</sub> * 8 H <sub>2</sub> O	100 g	HDPE bottle	1.08917.0100

For more details about our packaging, please see "Packaging and Safe Handling" on page 42





### EMSURE® | EMPLURA® Salts.

We offer an extensive range of inorganic salts for qualitative and quantitative analysis. At our facilities in Darmstadt, our salts are manufactured under strictly controlled conditions with state-of-theart production technologies and equipment, to ensure outstanding analytical purity.

EMSURE<sup>®</sup> Salts

Premium Grade

▶ For more information please have a look at page 22

**EMPLURA®** Salts

**Basic Grade** 

▶ For more information please have a look at page 36

## Ordering information Salts

Calt	~ ^
Saits	<b>A</b>

Product	CAS No.	Chemical formula	Content	Packaging	Ord. I
Aluminium ammonium sulfate dodecahydrate for analysis EMSURE® ACS	7784-26-1	NH <sub>4</sub> Al(SO <sub>4</sub> ) <sub>2</sub> * 12 H <sub>2</sub> O	500 g	HDPE bottle	1.01031.05
Aluminium hydroxide powder EMPLURA®			1 kg	HDPE bottle	1.01091.10
hydrargillite	21645-51-2	$AI(OH)_3 * x H_2O$	50 kg	Fibre carton	1.01091.90
Aluminium nitrata nanahudrata far analusia EMCUDE®			500 g	HDPE bottle	1.01063.05
Aluminium nitrate nonahydrate for analysis EMSURE®	7784-27-2	$AI(NO_3)_3 * 9 H_2O$	50 kg	Fibre carton	1.01063.90
Aluminium nitrata nanahudrata EMDUUDA®	7784-27-2		1 kg	HDPE bottle	1.01086.10
Aluminium nitrate nonahydrate EMPLURA®	//04-2/-2	$AI(NO_3)_3 * 9 H_2O$	50 kg	PE canister	1.01086.9
Aluminium potassium sulfate dodecahydrate	te 7784-24-9		1 kg	HDPE bottle	1.01047.10
for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	7704-24-9	KAI(SO <sub>4</sub> ) <sub>2</sub> * 12 H <sub>2</sub> O	25 kg	Fibre carton	1.01047.9
			500 g	HDPE bottle	1.01116.0
			1 kg	HDPE bottle	1.01116.1
Ammonium acetate for analysis EMSURE® ACS, Reag. Ph Eur	631-61-8	$CH_3COONH_4$	5 kg	HDPE bottle	1.01116.5
			12 kg	PE bucket	1.01116.9
			25 kg	Fibre carton	1.01116.9
	CO1 C1 0		1 kg	HDPE bottle	1.01115.1
Ammonium acetate EMPLURA®	631-61-8	CH <sub>3</sub> COONH <sub>4</sub>	5 kg	HDPE bottle	1.01115.5
Ammonium amidosulfonate for analysis (for detection of sulfonamide in blood) EMSURE <sup>®</sup> ACS, Reag. Ph Eur	7773-06-0	$H_2NSO_3NH_4$	100 g	HDPE bottle	1.01220.0
Ammonium honzosta EMDI LIDA®	1962 62 4		1 kg	HDPE bottle	1.01118.1
Ammonium benzoate EMPLURA®	1863-63-4	C <sub>6</sub> H₅COONH₄	50 kg	Fibre carton	1.01118.9
Ammonium bromide for analysis EMSURE® ACS	12124-97-9	NH₄Br	1 kg	HDPE bottle	1.01125.1
	12124-97-9	NH4DI	25 kg	Fibre carton	1.01125.9
Ammonium carbamate for analysis EMSURE®	1111-78-0	H <sub>2</sub> NCOONH <sub>4</sub>	500 g	HDPE bottle	1.01134.0
			250 g	HDPE bottle	1.59504.0
Ammonium carbonate for analysis EMSURE® ACS, Reag. Ph Eur	10361-29-2		1 kg	HDPE bottle	1.59504.1
		NEW	25 kg	Fibre carton	1.59504.9
Ammonium cerium(IV) nitrate	16774 21 2		100 g	HDPE bottle	1.02276.0
for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	16774-21-3	$(NH_4)_2[Ce(NO_3)_6]$	1 kg	HDPE bottle	1.02276.1
Ammonium cerium(IV) sulfate dihydrate for analysis EMSURE® ACS	10378-47-9	(NH <sub>4</sub> ) <sub>4</sub> Ce(SO <sub>4</sub> ) <sub>4</sub> * 2 H <sub>2</sub> O	100 g	HDPE bottle	1.02273.0
			500 g	HDPE bottle	1.01145.0
			1 kg	HDPE bottle	1.01145.1
Ammonium chloride for analysis EMSURE® ACS, ISO, Reag. Ph Eur	12125-02-9	NH₄CI	5 kg	HDPE bottle	1.01145.5
			25 kg	Fibre carton	1.01145.9
			50 kg	Fibre carton	1.01145.9
			500 g	HDPE bottle	1.01126.0
Ammonium dihydrogen phosphate for analysis EMSURE® ACS, Reag. Ph Eur	7722-76-1	(NH <sub>4</sub> )H <sub>2</sub> PO <sub>4</sub>	5 kg	HDPE bottle	1.01126.5
iui anaiysis Emoure- ACo, Kedy. Mi Eui			50 kg	Fibre carton	1.01126.9
			250 g	HDPE bottle	1.01164.0
Ammonium fluoride for analysis EMSURE® ACS	12125-01-8	NH₄F		HDPE bottle	1.01164.1
ATTITIONIUTI HUOTIGE FOF ANALYSIS EMSUKE <sup>∞</sup> ACS	12125-01-8	••••4		Fibre carton	1.01164.9

#### Salts A-B

Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
			500 g	HDPE bottle	1.01154.0500
di-Ammonium hydrogen citrate for analysis EMSURE® ACS, Reag. Ph Eur	3012-65-5	C <sub>6</sub> H <sub>8</sub> O <sub>7</sub> * 2 NH <sub>3</sub>	2.5 kg	HDPE bottle	1.01154.2500
			25 kg	Fibre carton	1.01154.9025
			500 g	HDPE bottle	1.01207.0500
di-Ammonium hydrogen phosphate for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	7783-28-0	$(NH_4)_2HPO_4$	25 kg	Fibre carton	1.01207.9025
			50 kg	Fibre carton	1.01207.9050
			500 g	HDPE bottle	1.03776.0500
			1 kg	HDPE bottle	1.03776.1000
Ammonium iron(III) sulfate dodecahydrate for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	7783-83-7	(NH <sub>4</sub> )Fe(SO <sub>4</sub> ) <sub>2</sub> * 12 H <sub>2</sub> O	5 kg	HDPE bottle	1.03776.5000
			12 kg	PE bucket	1.03776.9012
			50 kg	Fibre carton	1.03776.9050
			500 g	HDPE bottle	1.03792.0500
mmonium iron(II) sulfate hexahydrate	7783-85-9		1 kg	HDPE bottle	1.03792.1000
for analysis EMSURE® ISO	//03-05-9	$(NH_4)_2Fe(SO_4)_2 * 6 H_2O$	5 kg	HDPE bottle	1.03792.5000
			50 kg	Fibre carton	1.03792.9050
			500 g	HDPE bottle	1.01188.0500
Ammonium nitrate for analysis EMSURE® ACS	6484-52-2	$NH_4NO_3$	1 kg	HDPE bottle	1.01188.1000
			5 kg	HDPE bottle	1.01188.5000
Ammonium nitrate EMPLURA®	6484-52-2	$NH_4NO_3$	1 kg	HDPE bottle	1.01187.1000
	0404-52-2	N114NO3	5 kg	HDPE bottle	1.01187.5000
di-Ammonium oxalate monohydrate	6009-70-7	(NH <sub>4</sub> ) <sub>2</sub> C <sub>2</sub> O <sub>4</sub> * H <sub>2</sub> O	250 g	HDPE bottle	1.01192.0250
for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	0009-70-7	$(111_4)_2 C_2 O_4 = 11_2 O_4$	1 kg	HDPE bottle	1.01192.1000
di-Ammonium oxalate monohydrate EMPLURA®	6009-70-7	(NH <sub>4</sub> ) <sub>2</sub> C <sub>2</sub> O <sub>4</sub> * H <sub>2</sub> O	1 kg	HDPE bottle	1.01190.1000
	0009-70-7	$(1014)_2C_2O_4 = 11_2O_4$	50 kg	Fibre carton	1.01190.9050
			500 g	HDPE bottle	1.01201.0500
Ammonium peroxodisulfate	7727-54-0	$(NH_4)_2S_2O_8$	1 kg	HDPE bottle	1.01201.1000
for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	//2/-54-0		5 kg	HDPE bottle	1.01201.5000
			12 kg	PE bucket	1.01201.9012
			1 kg	HDPE bottle	1.01200.1000
Ammonium peroxodisulfate EMPLURA®	7727-54-0	(NH <sub>4</sub> ) <sub>2</sub> S <sub>2</sub> O <sub>8</sub>	5 kg	HDPE bottle	1.01200.5000
			25 kg	PE bucket	1.01200.9025
			100 g	HDPE bottle	1.01217.0100
Ammonium sulfate	7783-20-2	(NH <sub>4</sub> ) <sub>2</sub> SO <sub>4</sub>	1 kg	HDPE bottle	1.01217.1000
for analysis EMSURE $^{\circ}$ ACS, ISO, Reag. Ph Eur	//85-20-2	(NH <sub>4</sub> ) <sub>2</sub> 50 <sub>4</sub>	5 kg	HDPE bottle	1.01217.5000
			25 kg	Fibre carton	1.01217.9025
Ammonium thiocyanate	1762 05 4		500 g	HDPE bottle	1.01213.0500
for analysis EMSURE® ACS, ISO, Reag. Ph Eur	1762-95-4	NH₄SCN	25 kg	Fibre carton	1.01213.9025
Barium acetate for analysis EMSURE® ACS	543-80-6	Ba(CH <sub>3</sub> COO) <sub>2</sub>	500 g	HDPE bottle	1.01704.0500
			250 g	HDPE bottle	1.01714.0250
Barium carbonate for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	513-77-9	BaCO <sub>3</sub>	1 kg	HDPE bottle	1.01714.1000
			25 kg	Fibre carton	1.01714.9025

## Ordering information Salts

#### Salts B-C

Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
			500 g	HDPE bottle	1.01719.0500
Barium chloride dihydrate			1 kg	HDPE bottle	1.01719.1000
for analysis EMSURE® ACS, ISO, Reag. Ph Eur	10326-27-9	BaCl <sub>2</sub> * 2 H <sub>2</sub> O	5 kg	HDPE bottle	1.01719.5000
			50 kg	Fibre carton	1.01719.9050
Barium chloride dihydrate EMPLURA®	10326-27-9	BaCl <sub>2</sub> * 2 H <sub>2</sub> O	1 kg	HDPE bottle	1.01717.1000
Barium hydroxide octahydrate for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	12230-71-6	$Ba(OH)_2 * 8 H_2O$	500 g	HDPE bottle	1.01737.0500
Barium hydroxide octahydrate EMPLURA®	12230-71-6	Ba(OH) <sub>2</sub> * 8 H <sub>2</sub> O	1 kg	HDPE bottle	1.01735.1000
	10000 01 0		500 g	HDPE bottle	1.01729.0500
Barium nitrate for analysis EMSURE® ACS	10022-31-8	$Ba(NO_3)_2$	50 kg	Fibre carton	1.01729.9050
Barium perchlorate anhydrous	12465 05 7		250 g	Metal can	1.01738.0250
for analysis EMSURE®	13465-95-7	Ba(ClO <sub>4</sub> ) <sub>2</sub>	1 kg	Metal can	1.01738.1000
Bismuth(III) nitrate alkaline for analysis EMSURE <sup>®</sup> Reag. Ph Eur	1304-85-4	Bi <sub>5</sub> O(OH) <sub>9</sub> (NO <sub>3</sub> ) <sub>4</sub>	100 g	HDPE bottle	1.01878.0100
Cadmium acetate dihydrate for analysis EMSURE®	5743-04-4	(CH <sub>3</sub> COO) <sub>2</sub> Cd * 2 H <sub>2</sub> O	500 g	HDPE bottle	1.02003.0500
Cadmium oxide fine powder EMPLURA®	1306-19-0	CdO	5 kg	Metal can	1.02015.5000
Cadmium sulfate hydrate for analysis EMSURE® ACS	7790-84-3	3 CdSO <sub>4</sub> * 8 H <sub>2</sub> O	100 g	HDPE bottle	1.02027.0100
			250 g	HDPE bottle	1.02066.0250
Calcium carbonate precipitated for analysis EMSURE <sup>®</sup> Reag. Ph Eur	471-34-1	CaCO <sub>3</sub>	1 kg	HDPE bottle	1.02066.1000
LHOOKE' Kedy. I'l Eul			50 kg	Fibre carton	1.02066.9050
Calcium carbonate precipitated for analysis of silicates EMSURE®	471-34-1	CaCO <sub>3</sub>	500 g	HDPE bottle	1.02067.0500
			250 g	HDPE bottle	1.02382.0250
		CaCl <sub>2</sub> * 2 H <sub>2</sub> O	500 g	HDPE bottle	1.02382.0500
Calcium chloride dihydrate for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	10035-04-8		1 kg	HDPE bottle	1.02382.1000
Tor analysis Erisoite Acs, heag. In Ear			5 kg	HDPE bottle	1.02382.5000
			25 kg	Fibre carton	1.02382.9025
			500 g	HDPE bottle	1.02047.0500
Calcium hydroxide for analysis EMSURE® ACS, Reag. Ph Eur	1305-62-0	Ca(OH) <sub>2</sub>	1 kg	HDPE bottle	1.02047.1000
			50 kg	Fibre carton	1.02047.9050
			500 g	HDPE bottle	1.02121.0500
Calcium nitrate tetrahydrate for analysis EMSURE <sup>®</sup> ACS	13477-34-4	$Ca(NO_3)_2 * 4 H_2O$	5 kg	HDPE bottle	1.02121.5000
			50 kg	Fibre carton	1.02121.9050
Calcium nitrata tatrahudrata EMDI UDA®	12477 24 4	C2(NO) * 4 H O	5 kg	HDPE bottle	1.02120.5000
Calcium nitrate tetrahydrate EMPLURA®	13477-34-4	$Ca(NO_3)_2 * 4 H_2O$	50 kg	Fibre carton	1.02120.9050
Calcium sulfate dihydrate precipitated	10101 41 4		500 g	HDPE bottle	1.02161.0500
for analysis EMSURE®	10101-41-4	$CaSO_4 * 2 H_2O$	25 kg	Fibre carton	1.02161.9025
			25 g	HDPE bottle	1.02274.0025
Cerium(IV) sulfate tetrahydrate for analysis EMSURE <sup>®</sup>	10294-42-5	Ce(SO <sub>4</sub> ) <sub>2</sub> * 4 H <sub>2</sub> O	100 g	HDPE bottle	1.02274.0100
			250 g	HDPE bottle	1.02274.0250
Chromium(III) nitrate nonahydrate for analysis EMSURE®	7789-02-8	Cr(NO <sub>3</sub> ) <sub>3</sub> * 9 H <sub>2</sub> O	250 g	HDPE bottle	1.02481.0250

#### Salts C-I

	Saits C-1					
	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
С	Chromium(III) potassium sulfate dodecahydrate for analysis EMSURE® ACS, Reag. Ph Eur	7788-99-0	KCr(SO <sub>4</sub> ) <sub>2</sub> * 12 H <sub>2</sub> O	250 g	HDPE bottle	1.01036.0250
	Cobalt(II) acetate tetrahydrate for analysis EMSURE <sup>®</sup> ACS	6147-53-1	(CH <sub>3</sub> COO) <sub>2</sub> Co * 4 H <sub>2</sub> O	100 g	HDPE bottle	1.02529.0100
	Cobalt(II) chloride hexahydrate	7701 12 1		100 g	HDPE bottle	1.02539.0100
	for analysis EMSURE® ACS, Reag. Ph Eur	7791-13-1	$CoCl_2 * 6 H_2O$	250 g	HDPE bottle	1.02539.0250
	Cobalt(II) nitrate hexahydrate for analysis	10026-22-9	$Co(NO_3)_2 * 6 H_2O$	50 g	HDPE bottle	1.02554.0050
	(max. 0.001% Ni) EMSURE® ACS, Reag. Ph Eur	10020-22-9	$CO(NO_3)_2 = 0 = 0_2O$	250 g	HDPE bottle	1.02554.0250
	Cobalt(II) nitrate hexahydrate	10026-22-9	$Co(NO_3)_2 * 6 H_2O$	100 g	HDPE bottle	1.02536.0100
	for analysis EMSURE®	10020-22-9	CO(NO <sub>3</sub> ) <sub>2</sub> O H <sub>2</sub> O	250 g	HDPE bottle	1.02536.0250
	Cobalt(II) sulfate heptahydrate	10026-24-1		100 g	HDPE bottle	1.02556.0100
	for analysis EMSURE®	10020-24-1		250 g	HDPE bottle	1.02556.0250
	Copper(II) acetate monohydrate	10026-24-1       CoSO <sub>4</sub> * 7 H <sub>2</sub> O         6046-93-1       (CH <sub>3</sub> COO) <sub>2</sub> Cu * H <sub>2</sub> O         6046-93-1       (CH <sub>3</sub> COO) <sub>2</sub> Cu * H <sub>2</sub> O         7758-89-6       CuCl         10125-13-0       CuCl <sub>2</sub> * 2 H <sub>2</sub> O	250 g	HDPE bottle	1.02711.0250	
	for analysis EMSURE <sup>®</sup> ACS	0040-95-1		25 kg	Fibre carton	1.02711.9025
	Copper(II) acetate monohydrate cryst.	6046-93-1		500 g	HDPE bottle	1.02710.0500
	EMPLURA®	0040 55 1		50 kg	Fibre carton	1.02710.9050
	Copper(I) chloride for analysis EMSURE® ACS	7758-89-6	CuCl	250 g	HDPE bottle	1.02739.0250
		//30 05 0		25 kg	Fibre carton	1.02739.9025
	Copper(II) chloride dihydrate	10125-13-0		250 g	HDPE bottle	1.02733.0250
	for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	10125 15 0		1 kg	HDPE bottle	1.02733.1000
				250 g	HDPE bottle	1.02753.0250
	Copper(II) nitrate trihydrate for analysis EMSURE <sup>®</sup>	10031-43-3	$Cu(NO_3)_2 * 3 H_2O$	1 kg	HDPE bottle	1.02753.1000
				25 kg	Fibre carton	1.02753.9025
	Copper(II) sulfate anhydrous	7758-98-7	758-98-7 CuSO₄ -	250 g	HDPE bottle	1.02791.0250
	for analysis EMSURE®			1 kg	HDPE bottle	1.02791.1000
				250 g	HDPE bottle	1.02790.0250
	Copper(II) sulfate pentahydrate	7758-99-8	CuSO <sub>4</sub> * 5 H <sub>2</sub> O	1 kg	HDPE bottle	1.02790.1000
	for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur			5 kg	HDPE bottle	1.02790.5000
				50 kg	Fibre carton	1.02790.9050
	Copper(II) sulfate pentahydrate	7758-99-8	$CuSO_4 * 5 H_2O$	5 kg	HDPE bottle	1.02780.5000
	very fine crystals EMPLURA®			50 kg	Fibre carton	1.02780.9050
I	Iven(III) chloride hevelvidrate			250 g	HDPE bottle	1.03943.0250
	Iron(III) chloride hexahydrate for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	10025-77-1	$FeCl_3 * 6 H_2O$	1 kg	HDPE bottle	1.03943.1000
				25 kg	PE drum	1.03943.9025
	Iron(III) chloride solution (10% Fe) for analysis EMSURE $^{\odot}$			250 ml	HDPE bottle	1.05512.0250
				250 g	HDPE bottle	1.03861.0250
	on(II) chloride tetrahydrate 13478-10-9	FeCl <sub>2</sub> * 4 H <sub>2</sub> O	1 kg	HDPE bottle	1.03861.1000	
	tor analysis Encone			50 kg	PE drum	1.03861.9050
	Iron(III) nitrate nonahydrate	7702 61 0		250 g	HDPE bottle	1.03883.0250
	for analysis EMSURE® ACS, Reag. Ph Eur	7782-61-8	$Fe(NO_3)_3 * 9 H_2O$	1 kg	HDPE bottle	1.03883.1000
	Iron(III) phosphate for analysis calcined (max. $0.001\%$ SO <sub>4</sub> ) EMSURE <sup>®</sup>	10045-86-0	FePO <sub>4</sub>	500 g	HDPE bottle	1.03935.0500

## Ordering information Salts

#### Salts I-M

_	Salts 1-M					
	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
I				100 g	HDPE bottle	1.03965.0100
				500 g	HDPE bottle	1.03965.0500
	Iron(II) sulfate heptahydrate for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	7782-63-0	FeSO <sub>4</sub> * 7 H <sub>2</sub> O	1 kg	HDPE bottle	1.03965.1000
	, , , ,		_	5 kg	HDPE bottle	1.03965.5000
				25 kg	PE drum	1.03965.9025
L	Lead(II) acetate trihydrate	6080-56-4	(CH <sub>3</sub> COO) <sub>2</sub> Pb * 3 H <sub>2</sub> O	250 g	HDPE bottle	1.07375.0250
	for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	0080-50-4	$(CH_3COO)_2PD + 5 H_2O$	1 kg	HDPE bottle	1.07375.1000
	Lead(II) carbonate for analysis EMSURE® ACS	598-63-0	PbCO <sub>3</sub>	250 g	HDPE bottle	1.07381.0250
	Lead(II) hydroxide acetate anhydrous	51404-69-4	(CH <sub>3</sub> COO) <sub>2</sub> Pb * Pb(OH) <sub>2</sub>		HDPE bottle	1.07414.1000
	for the analysis of sugar acc. to Horne EMSURE®	51404-05-4			Fibre carton	1.07414.9030
	Lead(II) hydroxide acetate anhydrous or the analysis of sugar acc. to Horne EMSURE® Lead(II) nitrate or analysis EMSURE® ACS, Reag. Ph Eur Lithium carbonate or analysis EMSURE® ACS, Reag. Ph Eur Lithium carbonate EMPLURA® Lithium chloride or analysis EMSURE® ACS, Reag. Ph Eur Lithium sulfate monohydrate or analysis EMSURE® ACS, Reag. Ph Eur	10099-74-8	Pb(NO <sub>3</sub> ) <sub>2</sub>	100 g	HDPE bottle	1.07398.0100
	for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	10099-74-8	$PD(NO_3)_2$	1 kg	HDPE bottle	1.07398.1000
	Lithium carbonate for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	554-13-2	Li <sub>2</sub> CO <sub>3</sub>	250 g	HDPE bottle	1.05680.0250
			NEW	1 kg	HDPE bottle	1.05670.1000
	Lithium carbonate EMPLURA®	554-13-2	Li <sub>2</sub> CO <sub>3</sub>		Fibre carton	1.05670.9050
				100 g	HDPE bottle	1.05679.0100
	Lithium chloride	7447-41-8	LiCl	250 g	HDPE bottle	1.05679.0250
	Tor analysis ENSORE ACS, Reag. The Eur	EMSURE® ACS, Reag. PILEUI	12 kg	PE bucket	1.05679.9012	
	Lithium sulfate monohydrate for analysis EMSURE® ACS, Reag. Ph Eur	10102-25-7	Li <sub>2</sub> SO <sub>4</sub> * H <sub>2</sub> O	250 g	HDPE bottle	1.05694.0250
М		16674-78-5	(CH <sub>3</sub> COO) <sub>2</sub> Mg * 4 H <sub>2</sub> O	250 g	HDPE bottle	1.05819.0250
	Magnesium acetate tetrahydrate			1 kg	HDPE bottle	1.05819.1000
	Tor analysis ENSORE ACS, Reag. The Eur			50 kg	Fibre carton	1.05819.9050
			MgCl <sub>2</sub> * 6 H <sub>2</sub> O	250 g	HDPE bottle	1.05833.0250
	Magnesium chloride hexahydrate			1 kg	HDPE bottle	1.05833.1000
	for analysis EMSURE® ACS, ISO, Reag. Ph Eur	7791-18-6		5 kg	HDPE bottle	1.05833.5000
				25 kg	Fibre carton	1.05833.9025
	Magnesium hydroxide carbonate	12125 20.0	~ 4 MgCO <sub>3</sub> * Mg(OH) *	250 g	HDPE bottle	1.05827.0250
	for analysis EMSURE®	12125-28-9	5 H <sub>2</sub> O	25 kg	Fibre carton	1.05827.9025
	Magnesium nitrate hexahydrate	12446 10 0		500 g	HDPE bottle	1.05853.0500
	for analysis EMSURE® ACS, Reag. Ph Eur	13446-18-9	$Mg(NO_3)_2 * 6 H_2O$	25 kg	PE drum	1.05853.9025
	Magnesium perchlorate hydrate	C 4010 42 0		100 g	Metal can	1.05874.0100
	[about 83% Mg(ClO <sub>4</sub> ) <sub>2</sub> ] for analysis EMSURE <sup>®</sup>	64010-42-0	$Mg(CIO_4)_2 * x H_2O$	500 g	Metal can	1.05874.0500
	Magnesium sulfate anhydrous	7407 00 0	M-60	1 kg	Glass bottle	1.06067.1000
	for analysis EMSURE®	7487-88-9	MgSO₄	25 kg	PE drum	1.06067.9025
				500 g	HDPE bottle	1.05886.0500
	Magnesium sulfate heptahydrate			1 kg	HDPE bottle	1.05886.1000
	for analysis EMSURE® ACS, Reag. Ph Eur	10034-99-8	$MgSO_4 * 7 H_2O$	5 kg	HDPE bottle	1.05886.5000
				50 kg	Fibre carton	1.05886.9050
	Manganese(II) chloride dihydrate	20603-88-7	MnCl <sub>2</sub> * 2 H <sub>2</sub> O	100 g	HDPE bottle	1.05934.0100

#### Salts M-N

Product	CAS No.	Chemical formula	Content	Packaging	Ord. No
Manganese(II) chloride tetrahydrate	12446 24.0		100 g	HDPE bottle	1.05927.010
for analysis EMSURE® ACS	13446-34-9	$MnCl_2 * 4 H_2O$	1 kg	HDPE bottle	1.05927.100
			500 g	HDPE bottle	1.05940.050
Manganese(II) nitrate tetrahydrate for analysis EMSURE <sup>®</sup>	20694-39-7	$Mn(NO_3)_2 * 4 H_2O$	1 kg	HDPE bottle	1.05940.100
			25 kg	Metal drum	1.05940.902
Manganese(II) sulfate monohydrate spray-dried for analysis EMSURE® ACS, Reag. Ph Eur	10034-96-5	MnSO₄ * H₂O	250 g	HDPE bottle	1.05941.025
	10034-96-5		25 kg	Fibre carton	1.05941.902
Manganese(II) sulfate tetrahydrate	10101-68-5	M=50 * 4 H 0	1 kg	HDPE bottle	1.02786.100
for analysis EMSURE®	10101-08-5	$MnSO_4 * 4 H_2O$	25 kg	Fibre carton	1.02786.902
Mercury for analysis and for polarography	7439-97-6	На	250 g	HDPE bottle	1.04403.025
EMSURE®	7439-97-0	Hg	1 kg	HDPE bottle	1.04403.100
Mercury EMPLURA®	7439-97-6	Hg	250 g	HDPE bottle	1.04401.025
Mercury(II) acetate	1600-27-7		50 g	HDPE bottle	1.04410.005
for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	1600-27-7	Hg(CH <sub>3</sub> COO) <sub>2</sub>	250 g	HDPE bottle	1.04410.025
Mercury(II) bromide	7789-47-1	HaBr	50 g	HDPE bottle	1.04421.005
for analysis EMSURE® ACS	//89-4/-1	HgBr <sub>2</sub>	250 g	HDPE bottle	1.04421.025
		HgCl <sub>2</sub>	50 g	HDPE bottle	1.04419.005
Mercury(II) chloride for analysis EMSURE <sup>®</sup> Reag. Ph Eur, ACS	7487-94-7		250 g	HDPE bottle	1.04419.025
			1 kg	1 kg HDPE bottle	1.04419.100
Mercury(II) chloride fine cryst. EMPLURA®	7487-94-7	HgCl <sub>2</sub>	100 g	HDPE bottle	1.04417.010
Mercury(II) iodide red,	7774-29-0	HgI <sub>2</sub>	50 g	HDPE bottle	1.04428.005
for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	7774-29-0		250 g	HDPE bottle	1.04428.025
Mercury(II) iodide red EMPLURA®	7774-29-0	Hat	100 g	HDPE bottle	1.04420.010
	7774-29-0	HgI <sub>2</sub>	1 kg	HDPE bottle	1.04420.100
Mercury(II) nitrate monohydrate	7783-34-8	Hg(NO <sub>3</sub> ) <sub>2</sub> * H <sub>2</sub> O	50 g	HDPE bottle	1.04439.005
for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	7783-34-8	$Hg(HO_3)_2 + H_2O$	250 g	HDPE bottle	1.04439.025
Mercury(II) oxide red, for analysis EMSURE®	21908-53-2	HgO	50 g	HDPE bottle	1.04466.005
	21908-33-2	ligo	250 g	HDPE bottle	1.04466.025
Mercury(II) sulfate for analysis EMSURE <sup>®</sup> ACS	7783-35-9	HgSO₄	50 g	HDPE bottle	1.04480.005
	7703 33 3	119304	250 g	HDPE bottle	1.04480.025
			100 g	HDPE bottle	1.04481.010
Mercury(II) sulfate EMPLURA®	7783-35-9	HgSO <sub>4</sub>	250 g	HDPE bottle	1.04481.025
			1 kg	HDPE bottle	1.04481.100
Mercury(II) thiocyanate	592-85-8	Hg(SCN),	25 g	HDPE bottle	1.04484.002
for analysis EMSURE <sup>®</sup> Reag. Ph Eur	592-05-0		100 g	HDPE bottle	1.04484.010
Nickel(II) chloride hexahydrate	7701 20 0	NiCl <sub>2</sub> * 6 H <sub>2</sub> O	250 g	HDPE bottle	1.06717.025
for analysis EMSURE® ACS	7791-20-0		1 kg	HDPE bottle	1.06717.100
			100 g	HDPE bottle	1.06721.010
Nickel(II) nitrate hexahydrate for analysis EMSURE® ACS	13478-00-7	$Ni(NO_3)_2 * 6 H_2O$	250 g	HDPE bottle	1.06721.025
			1 kg	HDPE bottle	1.06721.100

# Ordering information Salts

#### Salts N-P

Product	CAS No.	Chemical formula	Content	Packaging	Ord. M
			100 g	HDPE bottle	1.06727.01
Nickel(II) sulfate hexahydrate for analysis EMSURE® ACS	10101-97-0	NiSO <sub>4</sub> * 6 H <sub>2</sub> O	250 g	HDPE bottle	1.06727.02
			1 kg	HDPE bottle	1.06727.10
Nickel(II) sulfate hexahydrate EMPLURA®	10101-97-0	NiSO <sub>4</sub> * 6 H <sub>2</sub> O	1 kg	HDPE bottle	1.06726.10
Potassium antimony(III) oxide tartrate	20200 74 5		250 g	HDPE bottle	1.08092.02
trihydrate EMPLURA®	28300-74-5	$K_2(SbO)_2C_8H_4O_{10} * 3 H_2O$	1 kg	HDPE bottle	1.08092.10
Potassium bromate for analysis			100 g	Metal can	1.04912.01
(max 0,000001% Hg) EMSURE <sup>®</sup> ACS, ISO,	7758-01-2	KBrO <sub>3</sub>	250 g	Metal can	1.04912.02
Reag. Ph Eur			25 kg	Metal drum	1.04912.90
Potassium bromide for analysis (max. 0.000001% Hg) EMSURE®ACS, Reag. Ph Eur	7758-02-3	KBr	500 g	HDPE bottle	1.04905.05
			500 g	HDPE bottle	1.04928.05
Potassium carbonate for analysis EMSURE® ACS, ISO, Reag. Ph Eur	584-08-7	K <sub>2</sub> CO <sub>3</sub>	1 kg	HDPE bottle	1.04928.10
			50 kg	Fibre carton	1.04928.90
			100 g	Metal can	1.04944.01
Potassium chlorate for analysis EMSURE®	sium chlorate for analysis EMSURE <sup>®</sup> Reag. Ph Eur NEW	500 g	Metal can	1.04944.0	
ACS, Reag. FILLUI		12 kg	PE bucket	1.04944.9	
Potassium chloride for analysis (≤ 0.005% Br)			500 g	HDPE bottle	1.04933.0
EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	7447-40-7	KCI	25 kg	Fibre carton	1.04933.9
			250 g	HDPE bottle	1.04936.0
		47-40-7 KCl	500 g	HDPE bottle	1.04936.0
			1 kg	HDPE bottle	1.04936.1
Potassium chloride for analysis EMSURE®	7447-40-7		5 kg	HDPE bottle	1.04936.5
			10 kg	Fibre carton	1.04936.9
			50 kg	Fibre carton	1.04936.9
Potassium chromate for analysis EMSURE®			250 g	HDPE bottle	1.04952.0
ACS, Reag. Ph Eur	7789-00-6	K <sub>2</sub> CrO <sub>4</sub>	1 kg	HDPE bottle	1.04952.1
			100 g	HDPE bottle	1.04967.0
Potassium cyanide for analysis EMSURE® ACS, ISO, Reag. Ph Eur	151-50-8	KCN	250 g	HDPE bottle	1.04967.02
-c3, 130, Redg. 11 Eur			1 kg	HDPE bottle	1.04967.1
Potassium cyanide EMPLURA®	151-50-8	KCN	1 kg	HDPE bottle	1.04965.1
Potassium dichromate for analysis (max. 0.000001% Hg) EMSURE® ACS, ISO	7778-50-9	$K_2Cr_2O_7$	500 g	Glass bottle	1.04865.0
Potassium dichromate for analysis EMSURE®			500 g	HDPE bottle	1.04864.0
ACS, ISO, Reag. Ph Eur	7778-50-9	$K_2Cr_2O_7$	1 kg	HDPE bottle	1.04864.10
			1 kg	HDPE bottle	1.04877.10
Potassium dihydrogen phosphate for analysis	7778-77-0	KH₂PO₄	12 kg	PE bucket	1.04877.9
$f \leq 0.005\%$ Na) EMSURE® ACS, ISO, Reag. Ph Eur				Fibre carton	1.04877.9
			250 g	HDPE bottle	1.04873.0
				HDPE bottle	1.04873.1
Potassium dihydrogen phosphate for analysis	7778-77-0	KH₂PO₄		HDPE bottle	1.04873.50
EMSURE® ISO		<u> -</u> -		Fibre carton	1.04873.90
				Fibre carton	1.04873.90

#### Salts P

Product	CAS No.	Chemical formula	Content	Packaging	Ord. M
			1 kg	HDPE bottle	1.05107.10
Potassium disulfate (potassium pyrosulfate) for analysis EMSURE <sup>®</sup> ACS	7790-62-7	$K_2S_2O_7$	5 kg	HDPE bottle	1.05107.50
			50 kg	PE drum	1.05107.90
			500 g	HDPE bottle	1.05057.05
Potassium disulfite for analysis EMSURE®	16731-55-8	$K_2S_2O_5$	1 kg	HDPE bottle	1.05057.10
			2.5 kg	HDPE bottle	1.05057.25
	7700 00 0		250 g	HDPE bottle	1.04994.02
Potassium fluoride for analysis EMSURE® ACS	7789-23-3	KF	1 kg	HDPE bottle	1.04994.10
			100 g	HDPE bottle	1.04973.01
Potassium hexacyanoferrate(III) for analysis EMSURE® ACS, Reag. Ph Eur	13746-66-2	$K_3[Fe(CN)_6]$	250 g	HDPE bottle	1.04973.02
			1 kg	HDPE bottle	1.04973.10
Potassium hexacyanoferrate(III) EMPLURA®	13746-66-2	K <sub>3</sub> [Fe(CN) <sub>6</sub> ]	1 kg	HDPE bottle	1.04971.10
			100 g	HDPE bottle	1.04984.01
Potassium hexacyanoferrate(II) trihydrate for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	14459-95-1	$K_4[Fe(CN)_6] * 3 H_2O$	500 g	HDPE bottle	1.04984.05
			50 kg	Fibre carton	1.04984.90
Dataggium havaguanoforrata(II) tribudrata EMDUUDA®	14450 05 1		1 kg	HDPE bottle	1.04982.1
Potassium hexacyanoferrate(II) trihydrate EMPLURA®	14459-95-1	$K_4[Fe(CN)_6] * 3 H_2O$	25 kg	Fibre carton	1.04982.9
Potassium hexahydroxoantimonate(V) cryst. for analysis EMSURE®	12208-13-8	K[Sb(OH) <sub>6</sub> ]	100 g	HDPE bottle	1.05110.0
Potassium hydrogen carbonate for analysis EMSURE®			500 g	HDPE bottle	1.04854.0
ACS	298-14-6	KHCO <sub>3</sub>	25 kg	Fibre carton	1.04854.9
Potassium hydrogen diiodate for analysis EMSURE®	13455-24-8	KH(IO <sub>3</sub> ) <sub>2</sub>	50 g	Glass bottle	1.04867.0
		K <sub>2</sub> HPO <sub>4</sub>	1 kg	HDPE bottle	1.05104.1
di-Potassium hydrogen phosphate anhydrous for analysis EMSURE®	7758-11-4		25 kg	Fibre carton	1.05104.9
			50 kg	Fibre carton	1.05104.9
			250 g	HDPE bottle	1.05099.0
			1 kg	HDPE bottle	1.05099.1
di-Potassium hydrogen phosphate trihydrate for analysis EMSURE®	16788-57-1	K <sub>2</sub> HO <sub>4</sub> P * 3 H <sub>2</sub> O	5 kg	HDPE bottle	1.05099.5
			25 kg	Fibre carton	1.05099.9
			50 kg	Fibre carton	1.05099.9
			250 g	HDPE bottle	1.04874.0
Potassium hydrogen phthalate for analysis EMSURE <sup>®</sup> Reag. Ph Eur	877-24-7	C <sub>8</sub> H <sub>5</sub> KO <sub>4</sub>	1 kg	HDPE bottle	1.04874.1
			12 kg PE bucket	PE bucket	1.04874.9
			500 g	HDPE bottle	1.04885.0
Potassium hydrogen sulfate for analysis EMSURE <sup>®</sup> Reag. Ph Eur	7646-93-7	KHSO₄	2.5 kg	HDPE bottle	1.04885.2
Neug. In Eur			25 kg	Fibre carton	1.04885.9
			100 g	HDPE bottle	1.05051.0
Potassium iodate for analysis EMSURE® ACS, ISO, Reag. Ph Eur	7758-05-6	KIO <sub>3</sub>	500 g	HDPE bottle	1.05051.0
reay. FIT EUI		- 2	25 ka	PE drum	1.05051.90

## Ordering information Salts

Salts P-R

Product	CAS No.	Chemical formula	Content	Packaging	Ord.
			250 g	HDPE bottle	1.05043.02
			500 g	HDPE bottle	1.05043.0
Potassium iodide for analysis EMSURE <sup>®</sup> ISO, Reag. Ph Eur	7681-11-0	KI	1 kg	HDPE bottle	1.05043.10
			2.5 kg	HDPE bottle	1.05043.2
			50 kg	Fibre carton	1.05043.90
			500 g	HDPE bottle	1.05063.0
otassium nitrate	7757 70 1	KNO	1 kg	HDPE bottle	1.05063.1
for analysis EMSURE® ISO, Reag. Ph Eur	7757-79-1	KNO <sub>3</sub>	5 kg	HDPE bottle	1.05063.5
			25 kg	Fibre carton	1.05063.9
Potassium nitrite cryst. for analysis EMSURE® ACS	7758-09-0	KNO <sub>2</sub>	250 g	HDPE bottle	1.05067.0
di-Potassium oxalate monohydrate	C 407 40 F		250 g	HDPE bottle	1.05073.0
for analysis EMSURE® ACS	6487-48-5	$K_2C_2O_4 * H_2O$	1 kg	HDPE bottle	1.05073.1
		KCIO	250 g	Metal can	1.05076.0
Potassium perchlorate for analysis EMSURE® ACS	7778-74-7	KClO₄	1 kg	Metal can	1.05076.1
Potassium permanganate for analysis (max. 0.000005% Hg) EMSURE® ACS	7722-64-7	KMnO <sub>4</sub>	1 kg	Glass bottle	1.05084.1
otassium permanganate or analysis EMSURE® ACS, Reag. Ph Eur			250 g	Glass bottle	1.05082.0
	7722-64-7	KMnO₄	1 kg	Glass bottle	1.05082.1
otassium permanganate cryst. EMPLURA®	7722-64-7	KMnO₄	1 kg	Glass bottle	1.05080.1
			5 kg	Metal can	1.05080.5
			50 kg	Steel drum	1.05080.9
Potassium peroxodisulfate for analysis (≤ 0.001% N) EMSURE® ACS, Reag. Ph Eur	7727-21-1	K <sub>2</sub> S <sub>2</sub> O <sub>8</sub>	250 g	HDPE bottle	1.05092.0
	7727-21-1	$K_2S_2O_8$	250 g	HDPE bottle	1.05091.0
Potassium peroxodisulfate for analysis EMSURE®			1 kg	HDPE bottle	1.05091.1
		C₄H₄KNaO₅ * 4 H₂O	500 g	HDPE bottle	1.08087.0
			1 kg	HDPE bottle	1.08087.1
Potassium sodium tartrate tetrahydrate for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	6381-59-5		5 kg	HDPE bottle	1.08087.5
			12 kg	PE bucket	1.08087.9
			50 kg	Fibre carton	1.08087.9
			500 g	HDPE bottle	1.05153.0
Potassium sulfate	7770 00 5	K 60	1 kg	HDPE bottle	1.05153.1
for analysis EMSURE® ACS, ISO, Reag. Ph Eur	7778-80-5	$K_2SO_4$	5 kg	HDPE bottle	1.05153.5
			25 kg	Fibre carton	1.05153.9
Potassium sulfide small lumps	20265 00 2		250 g	HDPE bottle	1.05134.0
for analysis EMSURE®	39365-88-3		1 kg	HDPE bottle	1.05134.1
			250 g	HDPE bottle	1.05125.0
Potassium thiocyanate for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	333-20-0	KSCN	1 kg	HDPE bottle	1.05125.1
Tor analysis Ensore: ACS, 150, Redy. FILEU			50 kg	Fibre carton	1.05125.9
Potassium thiocyanate EMPLURA®	333-20-0	KSCN	1 ka	HDPE bottle	1.05124.1

Co.	lte	C
Ja	цs	9

Product	CAS No.	Chemical formula	Content	Packaging	Ord.
			25 g	HDPE bottle	1.01512.0
Silver nitrate	7761 00 0		100 g	HDPE bottle	1.01512.0
for analysis EMSURE® ACS, ISO, Reag. Ph Eur	7761-88-8	AgNO <sub>3</sub>	250 g	HDPE bottle	1.01512.0
			1 kg	HDPE bottle	1.01512.1
			250 g	HDPE bottle	1.06268.0
			1 kg	HDPE bottle	1.06268.1
Sodium acetate anhydrous for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	127-09-3	CH <sub>3</sub> COONa	2.5 kg	HDPE bottle	1.06268.2
			12 kg	PE bucket	1.06268.9
			25 kg	Fibre carton	1.06268.9
			500 g	HDPE bottle	1.06267.0
			1 kg	HDPE bottle	1.06267.1
Sodium acetate trihydrate for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	6131-90-4	$CH_3COONa * 3 H_2O$	5 kg	HDPE bottle	1.06267.5
			12 kg	PE bucket	1.06267.9
			50 kg	Fibre carton	1.06267.9
Sodium ammonium hydrogen phosphate tetrahydrate for analysis EMSURE®	7783-13-3	NaNH <sub>4</sub> HPO <sub>4</sub> * 4 H <sub>2</sub> O	1 kg	HDPE bottle	1.06682.1
dium carbonate anhydrous for analysis			1 kg	HDPE bottle	1.06393.1
EMSURE® ACS, ISO, Reag. Ph Eur	497-19-8	Na <sub>2</sub> CO <sub>3</sub>	50 kg	Fibre carton	1.06393.9
	497-19-8	Na <sub>2</sub> CO <sub>3</sub>	500 g	HDPE bottle	1.06392.0
			1 kg	HDPE bottle	1.06392.1
Sodium carbonate anhydrous for analysis EMSURE <sup>®</sup> ISO			5 kg	HDPE bottle	1.06392.5
			25 kg	Fibre carton	1.06392.9
			50 kg	Fibre carton	1.06392.9
		Na <sub>2</sub> CO <sub>3</sub> * 10 H <sub>2</sub> O	1 kg	HDPE bottle	1.06391.1
Sodium carbonate decahydrate for analysis EMSURE <sup>®</sup> ISO, Reag. Ph Eur	6132-02-1		5 kg	HDPE bottle	1.06391.5
To analysis ENSORE 150, Reag. In Eur			25 kg	Fibre carton	1.06391.9
			1 kg	HDPE bottle	1.06420.1
Sodium chlorate EMPLURA®	7775-09-9	NaClO <sub>3</sub>	50 kg	PE drum	1.06420.9
			500 g	HDPE bottle	1.06404.0
			1 kg	HDPE bottle	1.06404.1
Sodium chloride			5 kg	HDPE bottle	1.06404.5
for analysis EMSURE® ACS, ISO, Reag. Ph Eur	7647-14-5	NaCl	12 kg	PE bucket	1.06404.9
			25 kg	Fibre carton	1.06404.9
			50 kg	Fibre carton	1.06404.9
			500 g	HDPE bottle	1.06448.0
tri-Sodium citrate dihydrate			1 kg	HDPE bottle	1.06448.1
for analysis EMSURE® ACS, ISO, Reag. Ph Eur	6132-04-3	$C_6H_5Na_3O_7 * 2 H_2O$	5 kg	HDPE bottle	1.06448.5
			25 kg	Fibre carton	1.06448.9
Sodium cyanide EMPLURA®	143-33-9	NaCN	1 kg	HDPE bottle	1.06437.1
Sodium dichromate dihydrate			250 g	HDPE bottle	1.06336.0
for analysis EMSURE® ACS	7789-12-0	$Na_2Cr_2O_7 * 2 H_2O$	1 ka	HDPE bottle	1.06336.1

## Ordering information Salts

Salts S

Product	CAS No.	Chemical formula	Content	Packaging	Ord. N
			250 g	HDPE bottle	1.06342.02
lium dihydrogen phosphate dihydrate			1 kg	HDPE bottle	1.06342.10
for analysis EMSURE® Reag. Ph Eur	13472-35-0	$NaH_2PO_4 * 2 H_2O$	2.5 kg	HDPE bottle	1.06342.25
			25 kg	Fibre carton	1.06342.90
			500 g	HDPE bottle	1.06346.05
			1 kg	HDPE bottle	1.06346.10
Sodium dihydrogen phosphate monohydrate for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	10049-21-5	$NaH_2PO_4 * H_2O$	12 kg	PE bucket	1.06346.90
			25 kg	Fibre carton	1.06346.90
			50 kg	Fibre carton	1.06346.90
			500 g	HDPE bottle	1.06591.05
tetra-Sodium diphosphate decahydrate for analysis EMSURE® ACS, Reag. Ph Eur	13472-36-1	$Na_4P_2O_7 * 10 H_2O$	2.5 kg	HDPE bottle	1.06591.25
			50 kg	Fibre carton	1.06591.90
			100 g	HDPE bottle	1.06528.01
			500 g	HDPE bottle	1.06528.05
Sodium disulfite (sodium metabisulfite) for analysis EMSURE® ACS, Reag. Ph Eur	7681-57-4	$Na_2S_2O_5$	1 kg	HDPE bottle	1.06528.10
			5 kg	HDPE bottle	1.06528.50
			50 kg	Fibre carton	1.06528.90
odium dithionite for analysis EMSURE®	7775-14-6	$Na_2S_2O_4$	500 g	Metal can	1.06507.05
			2.5 kg	Metal can	1.06507.25
odium dithionite EMPLURA®	7775-14-6	$Na_2S_2O_4$	1 kg	Metal can	1.06505.10
			50 kg	Steel drum	1.06505.90
			250 g	HDPE bottle	1.06449.02
Sodium fluoride for analysis EMSURE® ACS, ISO, Reag. Ph Eur	7681-49-4	NaF	1 kg	HDPE bottle	1.06449.10
ACS, 150, 100g. 111 Edi			50 kg	Fibre carton	1.06449.90
Sodium formate for analysis EMSURE®	141-53-7		500 g	HDPE bottle	1.06443.05
ACS, Reag. Ph Eur		HCOONa	50 kg	Fibre carton	1.06443.90
Sodium hexanitrocobaltate(III) [sodium cobalt(III)	12600.00.1		25 g	HDPE bottle	1.02521.00
nitrite] for analysis EMSURE® ACS, Reag. Ph Eur	13600-98-1	$Na_3[Co(NO_2)_6]$	100 g	HDPE bottle	1.02521.01
			500 g	HDPE bottle	1.06329.05
			1 kg	HDPE bottle	1.06329.10
Sodium hydrogen carbonate for analysis EMSURE®			5 kg	HDPE bottle	1.06329.50
ACS, Reag. Ph Eur	144-55-8	NaHCO <sub>3</sub>	12 kg	PE bucket	1.06329.90
			25 kg	PE drum	1.06329.90
			50 kg	Fibre carton	1.06329.90
di-Sodium hydrogen phosphate anhydrous particle		N 1120	500 g	HDPE bottle	1.06559.05
size about 0.2 - 1 mm (~18-80 mesh ASTM) EMSURE®	7558-79-4	Na <sub>2</sub> HPO <sub>4</sub>	25 kg	Fibre carton	1.06559.90
			500 g	HDPE bottle	1.06586.05
			1 kg	HDPE bottle	1.06586.10
di-Sodium hydrogen phosphate anhydrous for analysis EMSURE® ACS, Reag. Ph Eur	7558-79-4	Na <sub>2</sub> HPO <sub>4</sub>	2.5 kg	HDPE bottle	1.06586.25
Tor analysis Ensore ACS, Reay, FILEUL			12 kg	PE bucket	1.06586.90
			50 ka	Fibre carton	1.06586.90

Salts S		Chamical formula	Contout	Dockoning	
Product	CAS No.	Chemical formula		Packaging	Ord. N
di-Sodium hydrogen phosphate dihydrate			500 g	HDPE bottle	1.06580.050
				HDPE bottle	1.06580.100
for analysis EMSURE®	10028-24-7	$Na_2HPO_4 * 2 H_2O$	5 kg	HDPE bottle	1.06580.50
				Fibre carton	1.06580.90
			50 kg	Fibre carton	1.06580.90
			500 g	HDPE bottle	1.06579.05
di-Sodium hydrogen phosphate dodecahydrate	10039-32-4	Na₂HPO₄ * 12 H₂O		HDPE bottle	1.06579.10
for analysis EMSURE <sup>®</sup> ISO, Reag. Ph Eur		2 7 2	5 kg	HDPE bottle	1.06579.50
			25 kg	Fibre carton	1.06579.90
di-Sodium hydrogen phosphate heptahydrate	7782-85-6	$Na_2HPO_4 * 7 H_2O$	1 kg	HDPE bottle	1.06575.10
for analysis EMSURE <sup>®</sup> ACS			25 kg	Fibre carton	1.06575.90
Sodium hydrogen sulfate monohydrate for analysis EMSURE®	10034-88-5	NaHSO <sub>4</sub> * H <sub>2</sub> O	500 g	HDPE bottle	1.06352.05
Sodium hypochlorite solution			2.5 I	HDPE bottle	1.05614.25
(6-14% active chlorine) EMPLURA®			25 I	PE canister	1.05614.90
			100 g	Glass bottle	1.06525.01
Sodium iodate for analysis EMSURE®	7681-55-2	NaIO <sub>3</sub>	1 kg	Glass bottle	1.06525.10
			100 g	HDPE bottle	1.06523.01
Sodium iodide for analysis EMSURE®	7681-82-5	NaI	250 g	HDPE bottle	1.06523.02
ACS, Reag. Ph Eur			1 kg	HDPE bottle	1.06523.10
	7790-28-5	NaIO4	50 g	HDPE bottle	1.06597.00
Sodium metaperiodate for analysis EMSURE®			250 g	HDPE bottle	1.06597.02
ACS, Reag. Ph Eur			1 kg	HDPE bottle	1.06597.10
		$Na_2MoO_4 * 2 H_2O$	100 g	HDPE bottle	1.06521.01
Sodium molybdate dihydrate for analysis	10102-40-6		250 g	HDPE bottle	1.06521.02
EMSURE® ACS, Reag. Ph Eur			1 kg	HDPE bottle	1.06521.10
			1 kg	HDPE bottle	1.06524.10
Sodium molybdate dihydrate EMPLURA®	10102-40-6	$Na_2MoO_4 * 2 H_2O$		Fibre carton	1.06524.90
				HDPE bottle	1.06537.05
Sodium nitrate for analysis EMSURE®				HDPE bottle	1.06537.10
ACS, ISO, Reag. Ph Eur	7631-99-4	NaNO <sub>3</sub>		PE bucket	1.06537.90
				Fibre carton	1.06537.90
				HDPE bottle	1.06535.10
Sodium nitrate cryst. EMPLURA®	7631-99-4	NaNO <sub>3</sub>		Fibre carton	1.06535.90
			100 g	HDPE bottle	1.06549.01
Sodium nitrite for analysis EMSURE® ACS,	7632-00-0	NaNO <sub>2</sub>	500 g	HDPE bottle	1.06549.05
Reag. Ph Eur	7052 00 0			PE bucket	
	-			HDPE bottle	1.06549.90
di-Sodium oxalate for analysis EMSURE®	62-76-0	$Na_2C_2O_4$	250 g	HDPE bottle	1.06557.02
					1.06557.10
			100 g	Metal can	1.06564.01
Sodium perchlorate monohydrate for analysis EMSURE®	7791-07-3	NaClO <sub>4</sub> * H <sub>2</sub> O	500 g	Metal can	1.06564.05
		NE		Metal can	1.06564.25
			25 kg	Steel drum	1.06564.90

## Ordering information Salts

Salts S

Product	CAS No.	Chemical formula	Content	Packaging	Ord. M
			500 g	HDPE bottle	1.06609.05
			1 kg	HDPE bottle	1.06609.10
Sodium peroxidisulfate for analysis EMSURE®	7775-27-1	Na <sub>2</sub> S <sub>2</sub> O <sub>8</sub> NEW	5 kg	HDPE bottle	1.06609.50
			12 kg	PE bucket	1.06609.90
			25 kg	Fibre carton	1.06609.90
			1 kg	HDPE bottle	1.06578.10
			5 kg	HDPE bottle	1.06578.50
tri-Sodium phosphate dodecahydrate for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	10101-89-0	Na <sub>3</sub> PO <sub>4</sub> * 12 H <sub>2</sub> O	12 kg	PE bucket	1.06578.90
			25 kg	Fibre carton	1.06578.90
			50 kg	Fibre carton	1.06578.90
			1 kg	HDPE bottle	1.06572.10
tri-Sodium phosphate dodecahydrate for analysis EMSURE <sup>®</sup>	10101-89-0	Na <sub>3</sub> PO <sub>4</sub> * 12 H <sub>2</sub> O	5 kg	HDPE bottle	1.06572.50
INJUKE <sup>©</sup>			25 kg	Fibre carton	1.06572.90
odium polyphosphate EMPLURA® (Graham's salt)			1 kg	HDPE bottle	1.06529.10
	10361-03-2	(NaPO <sub>3</sub> ) <sub>n</sub> / n = ~ 25	5 kg	HDPE bottle	1.06529.50
			50 kg	Fibre carton	1.06529.90
	54-21-7	HOC <sub>6</sub> H <sub>4</sub> COONa	250 g	HDPE bottle	1.06601.02
Sodium salicylate for analysis EMSURE®			1 kg	HDPE bottle	1.06601.1
			2.5 kg	HDPE bottle	1.06601.2
	7757-82-6	$Na_2SO_4$	500 g	HDPE bottle	1.06637.0
Sodium sulfate anhydrous coarse granules for analysis EMSURE® ACS			1 kg	HDPE bottle	1.06637.10
			25 kg	Fibre carton	1.06637.90
			500 g	HDPE bottle	1.06649.0
	7757-82-6	Na₂SO₄ NEW	1 kg	HDPE bottle	1.06649.10
Sodium sulfate anhydrous for analysis EMSURE® ACS, ISO, Reag. Ph Eur			5 kg	HDPE bottle	1.06649.50
Ac5, 150, Ac4g. 11 Edi			12 kg	PE bucket	1.06649.9
			25 kg	Fibre carton	1.06649.90
Sodium sulfate anhydrous granulated for organic trace analysis EMSURE®	7757-82-6	$Na_2SO_4$	500 g	Glass bottle	1.06639.05
Sodium sulfate decahydrate for analysis	7707 70 0		1 kg	HDPE bottle	1.06648.10
EMSURE <sup>®</sup> ACS, Reag. Ph Eur	//2/-/3-3	$Na_2SO_4 * 10 H_2O$	25 kg	Fibre carton	1.06648.90
			500 g	HDPE bottle	1.06657.0
Sodium sulfite anhydrous for analysis EMSURE®			1 kg	HDPE bottle	1.06657.10
Reag. Ph Eur	7757-83-7	Na <sub>2</sub> SO <sub>3</sub>	5 kg	HDPE bottle	1.06657.5
			50 kg	Fibre carton	1.06657.90
			250 g	HDPE bottle	1.06663.02
di-Sodium tartrate dihydrate for analysis EMSURE®	6106-24-7	$C_4H_4Na_2O_6 * 2 H_2O$	1 kg	HDPE bottle	1.06663.10
Sodium thiocyanate EMPLURA®	540-72-7	NaSCN	2.5 kg	HDPE bottle	1.06627.2
			250 g	HDPE bottle	1.06512.02
			2.5 kg	HDPE bottle	1.06512.2
Sodium thiosulfate anhydrous EMPLURA®	7772-98-7	$Na_2O_3S_2$		Fibre carton	1.06512.90
				Fibre carton	1.06512.90

	Salts S-Z					
	Product	CAS No.	Chemical formula	Content	Packaging	Ord. No.
s			$Na_2O_3S_2 * 5 H_2O$	500 g	HDPE bottle	1.06516.0500
	Sodium thiosulfate pentahydrate for analysis			1 kg	HDPE bottle	1.06516.1000
	EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	10102-1/-/		5 kg	HDPE bottle	1.06516.5000
				25 kg	Fibre carton	1.06516.9025
				250 g	HDPE bottle	1.06673.0250
	Sodium tungstate dihydrate for analysis $EMSURE^{\otimes}$	10213-10-2	$Na_2WO_4 * 2 H_2O$	1 kg	HDPE bottle	1.06673.1000
				25 kg	Fibre carton	1.06673.9025
		10212 10 2		1 kg	HDPE bottle	1.06672.1000
	Sodium tungstate dihydrate EMPLURA®	10213-10-2	$Na_2WO_4 * 2 H_2O$	25 kg	Fibre carton	1.06672.9025
	Strontium chloride hexahydrate for analysis EMSURE® ACS	10025-70-4	SrCl <sub>2</sub> * 6 H <sub>2</sub> O	250 g	HDPE bottle	1.07865.0250
				1 kg	HDPE bottle	1.07865.1000
		10042 70 0	Sr(NO <sub>3</sub> ) <sub>2</sub>	250 g	HDPE bottle	1.07872.0250
	Strontium nitrate for analysis EMSURE®	10042-70-9		25 kg	Fibre carton	1.07872.9025
т	Tin(IV) chloride EMPLURA®	7646-78-8	SnCl₄	500 ml	Glass bottle	1.07810.0500
	Tin(II) chloride dihydrate for analysis EMSURE® ACS, ISO, Reag. Ph Eur	10025-69-1	$SnCl_2 * 2 H_2O$	100 g	Glass bottle	1.07815.0100
				250 g	Glass bottle	1.07815.0250
				1 kg	Glass bottle	1.07815.1000
				25 kg	Fibre carton	1.07815.9025
	Tin(II) chloride dihydrate for analysis	10025 60 1	$SnCl_2 * 2 H_2O$	250 g	Glass bottle	1.07814.0250
	(max. 0.000001% Hg) EMSURE®	10025-09-1		2.5 kg	Glass bottle	1.07814.2500
z	Zinc acetate dihydrate for analysis EMSURE® ACS	5970-45-6	(CH₃COO),Zn * 2 H₃O	250 g	HDPE bottle	1.08802.0250
		5970-45-0	$(C\Pi_3 COO)_2 ZII = Z \Pi_2 O$	1 kg	HDPE bottle	1.08802.1000
				250 g	HDPE bottle	1.08816.0250
	Zinc chloride for analysis EMSURE® ACS, ISO, Reag. Ph Eur	7646-85-7	ZnCl <sub>2</sub>	1 kg	HDPE bottle	1.08816.1000
				25 kg	PE drum	1.08816.9025
	Zinc iodide for analysis EMSURE®	10139-47-6	ZnI <sub>2</sub>	100 g	Glass bottle	1.08828.0100
				500 g	HDPE bottle	1.08883.0500
	Zinc sulfate heptahydrate for analysis EMSURE®	7446-20-0	ZnSO₄ * 7 H₂O	1 kg	HDPE bottle	1.08883.1000
	ACS, ISO, Reag. Ph Eur		2113U <sub>4</sub> · / Π <sub>2</sub> U	5 kg	HDPE bottle	1.08883.5000
				50 kg	Fibre carton	1.08883.9050



For more details about our packaging, please see "Packaging and Safe Handling" on page 42





### EMSURE® | EMPARTA® | EMPLURA® Solvents.

Distinguished by exceptional quality and reliability, our solvents undergo strict controls and continuous development to meet growing regulations. As your reliable, one-stop supplier, we offer a complete solution, including solvents, documentation, secure packaging and withdrawal systems.

	Premium Grade
For more information please have a look at page 22	
EMPARTA <sup>®</sup> Solvents	Standard Grade
For more information please have a look at page 32	
	Basic Grade
For more information please have a look at page 36	

## Ordering information Solvents

	Solvents A-B							
	Product	CAS No.	Purity (GC	) Evap. residu	e Water	Content	Packaging	Ord. No.
4	Acetone for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur					1	Glass bottle	1.00014.1000
						1	HDPE bottle	1.00014.1011
						2.5	Glass bottle	1.00014.2500
		67-64-1	≥ 99.8%	5 ≤ 0.0005%	≤ 0.05%	2.5	HDPE bottle	1.00014.2511
						4	Glass bottle	1.00014.4000
		0, 011	_ ,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,		_ 0.0070	5	HDPE bottle	1.00014.5000
						10	Stainless steel drum	1.00014.6010
						25 I	Stainless steel drum	1.00014.6025
						190 I	Stainless steel drum	1.00014.6190
						180 I	PE / Metal drum	1.00014.9180
	Acetone for analysis EMPARTA® ACS	67-64-1	≥ 99.5%	≤ 0.001%	≤ 0.5%	2.5	HDPE bottle	1.07021.2511
		07 04 1	2 55.570	2 0.001 /0	2 0.5 %	4	Glass bottle	1.07021.4000
	Acetone EMPLURA®	67-64-1		≤ 0.004%		1	HDPE bottle	8.22251.1000
			≥ 99.0%		≤ 0.3%	2.5	HDPE bottle	8.22251.2500
			2 99.0%		2 0.5 %	5	HDPE bottle	8.22251.5011
						25 I	Metal drum	8.22251.9025
	Acetonitrile for analysis EMSURE® ACS, Reag. Ph Eur	75-05-8	≥ 99.5%	≤ 0.001%		1	Glass bottle	1.00003.1000
						2.5	Glass bottle	1.00003.2500
					≤ 0.1%	4	Glass bottle	1.00003.4000
						10	Stainless steel drum	1.00003.6010
						25 I	Stainless steel drum	1.00003.6025
		75-05-8		≤ 0.005%		1	Glass bottle	1.15500.1000
						2.5	Glass bottle	1.15500.2500
	Acetonitrile EMPLURA®		≥ 99.0%		≤ 0.5%	4	Glass bottle	1.15500.4000
						25 I	Stainless steel drum	1.15500.6025
						190 I	Metal drum	1.15500.9190
	Acetylacetone for analysis EMSURE®	123-54-6	≥ 99.0%		≤ 0.3%	100 ml	Glass bottle	1.09600.0100
		125 54 0	2 55.070		2 0.5 %	500 ml	Glass bottle	1.09600.0500
	n-Amyl acetate EMPLURA®	628-63-7	≥ 98.0%			1	Glass bottle	8.18700.1000
	n-Amyl alcohol (Pentan-1-ol)	71-41-0	≥ 98.5%	≤ 0.005%	≤ 0.1%	1	Glass bottle	1.00975.1000
	for analysis EMSURE®	71 41 0	2 90.970	2 0.003 /0	2 0.1 /0	2.5 I	Glass bottle	1.00975.2500
	tert-Amyl alcohol EMPLURA®	75-85-4	≥ 99.0%			1	HDPE bottle	8.06193.1000
	Aniline for analysis EMSURE®	62-53-3	≥ 99.5%		≤ 0.1%	1	Glass bottle	1.01261.1000
3						1	Glass bottle	1.09626.1000
	Benzyl alcohol for analysis EMSURE®	100-51-6	≥ 99.5%		≤ 0.1%	2.5	Glass bottle	1.09626.2500
		100 51 0	2 55.570		2 0.1 /0	4	Glass bottle	1.09626.4000
						25 I	Stainless steel drum	1.09626.6025
	1-Butanol for analysis EMSURE® ACS, ISO, Reag. Ph Eur					1	Glass bottle	1.01990.1000
		71-36-3	≥ 99.5%	≤ 0.001%	≤ 0.1%	2.5 I	Glass bottle	1.01990.2500
		71-30-3				4	Glass bottle	1.01990.4000
						25 I	Stainless steel drum	1.01990.6025
	1-Butanol EMPLURA®	71-36-3	≥ 99.0%	≤ 0.004%	≤ 0.2%	2.5 l	HDPE bottle	8.22262.2500

#### Solvents B-C

	Product	CAS No.	Purity (GC	C) Evap. residu	e Water	Content	Packaging	Ord. No.
в						1	Glass bottle	1.09630.1000
	2-Butanol for analysis EMSURE®	78-92-2	≥ 99.0%	≤ 0.001%	≤ 0.2%	2.5 I	Glass bottle	1.09630.2500
						25 I	Stainless steel drum	1.09630.6025
	2-Butanol EMPLURA®	78-92-2			≤ 0.2%	2.5 I	HDPE bottle	8.22263.2500
						500 ml	Glass bottle	1.09629.0500
	tert-Butanol for analysis EMSURE <sup>®</sup> ACS	75-65-0	≥ 99.5%	≤ 0.001%	≤ 0.1%	5 1	Aluminum bottle	1.09629.5000
	ACS .					25 I	PE / Metal drum	1.09629.9025
						1	Glass bottle	8.22264.1000
	tert-Butanol EMPLURA®	75-65-0	≥ 99.0%		≤ 0.1%	5 I	Aluminum bottle	8.22264.5000
						25 I	PE canister	8.22264.9025
						1	Glass bottle	1.09652.1000
	n-Butyl acetate for analysis EMSURE®	123-86-4	≥ 99.5%	≤ 0.001%	≤ 0.1%	2.5 I	Glass bottle	1.09652.2500
						4	Glass bottle	1.09652.4000
		122.06.4				2.5 I	Glass bottle	1.01974.2500
	n-Butyl acetate EMPLURA®	123-86-4	≥ 99.0%	≤ 0.001%		25 I	Stainless steel drum	1.01974.6025
						1	Glass bottle	1.01849.1000
						2.5 l	Glass bottle	1.01849.2500
	tert-Butyl methyl ether for analysis EMSURE <sup>®</sup> ACS	1634-04-4	≥ 99.5%	≤ 0.001%	≤ 0.03%	4	Glass bottle	1.01849.4000
	LHJURE ACS					5	HDPE bottle	1.01849.5011
						190 I	Stainless steel drum	1.01849.6190
						2.5 l	Glass bottle	1.01843.2500
		1624.04.4				10 I	Metal drum	1.01843.9011
	tert-Butyl methyl ether EMPLURA®	1634-04-4	∔ ≥ 99.0%	≤ 0.005%	≤ 0.05%	25 I	Stainless steel drum	1.01843.6025
						190 I	Stainless steel drum	1.01843.6190
I						1	Glass bottle	1.03818.1000
	1-Butylpyrrolidin-2-one EMPLURA®	3470-98-2	≥ 99.8%		≤ 0.1%	2.5 I	Glass bottle	1.03818.2500
С	Carbon disulfide for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	75-15-0	≥ 99.9%	≤ 0.0010%	≤ 0.01%	1	Glass bottle	1.02214.1000
	Carbon disulfide EMPLURA®	75-15-0	≥ 99.5%	≤ 0.005%	≤ 0.02%	1	Glass bottle	1.02211.1000
						1	Glass bottle	1.02445.1000
						2.5 l	Glass bottle	1.02445.2500
	Chloroform for analysis EMSURE®		99.0 -			4	Glass bottle	1.02445.4000
	ACS, ISO, Reag. Ph Eur	67-66-3	99.4 %	≤ 0.001%	≤ 0.01%	10 I	Stainless steel drum	1.02445.6010
						25 I	Stainless steel drum	1.02445.6025
						190 I	Stainless steel drum	1.02445.6190
	Chloroform for analysis EMPARTA®		99.0 -			2.5 I	Glass bottle	1.07024.2500
	ACS	67-66-3	99.0 <i>-</i> 99.4 %	≤ 0.001%	≤ 0.01%	4	Glass bottle	1.07024.4000
						1	Glass bottle	8.22265.1000
	Chloroform EMPLURA®	67-66-3	≥ 99%	≤ 0.001%	≤ 0.1%	2.5 I	Glass bottle	8.22265.2500
	Chloroform for analysis		99.0 -			1	Glass bottle	1.02442.1000
	(for determinations with dithizone)	67-66-3	99.4%	< 0.001%	< 0.01%	2.5	Glass bottle	1.02442.2500

Solvents C-D

	Product	CAS No.	Purity (GC	) Evap. residu	e Water	Content	Packaging	Ord. No.
С						1	Glass bottle	1.09666.1000
						2.5 I	Glass bottle	1.09666.2500
						2.5 I	HDPE bottle	1.09666.2511
	Cyclohexane for analysis EMSURE®					4	Glass bottle	1.09666.4000
	ACS, ISO, Reag. Ph Eur	110-82-7	≥ 99.5%	≤ 0.001%	≤ 0.01%	5 I	HDPE bottle	1.09666.5011
						10 I	Stainless steel drum	1.09666.6010
						25 I	Stainless steel drum	1.09666.6025
						190 I	Stainless steel drum	1.09666.6191
						1	Glass bottle	1.02832.1000
		110 00 7			1.0.050/	2.5 I	Glass bottle	1.02832.2500
	Cyclohexane EMPLURA®	110-82-7	≥ 99.0%		≤ 0.05%	25 I	Stainless steel drum	1.02832.6025
						190 I	Metal drum	1.02832.9190
	Cylclohexane for denaturation	110-82-7	≥ 99.0%			190 I	Metal drum	1.02830.9190
						1	Glass bottle	1.02888.1000
						2.5 I	Glass bottle	1.02888.2500
	Cyclohexanone EMPLURA®	108-94-1	≥ 99.0%		≤ 0.2%	10 I	Stainless steel drum	1.02888.6010
						25 I	Stainless steel drum	1.02888.6025
						190 I	Metal drum	1.02888.9191
						1	Glass bottle	1.08293.1000
	Cyclopentyl methyl ether EMPLURA®	5614-37-9	≥ 99.0%		≤ 0.2%	2.5 I	Glass bottle	1.08293.2500
						4	Glass bottle	1.08293.4000
D	1,2-Dichlorobenzene for extraction	95-50-1	> 00 00/		< 0.010/	1	Glass bottle	1.02930.1000
	analysis EMSURE®	95-50-1	≥ 99.0%		≤ 0.01%	2.5 l	Glass bottle	1.02930.2500
	1.2 Disblorgethang EMDUUDA®	107-06-2	≥ 99.5%	≤ 0.002%	≤ 0.03%	1	Glass bottle	1.00955.1000
	1,2-Dichloroethane EMPLURA®	107-00-2	≥ 99.370	≤ 0.002%	\$ 0.03%	2.5 l	Glass bottle	1.00955.2500
						1	Glass bottle	1.06050.1000
			≥ 99.8%		≤ 0.01%	2.5 I	Glass bottle	1.06050.2500
	Dichloromethane for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	75-09-2		≤ 0.001%		4	Glass bottle	1.06050.4000
	5					10 I	Stainless steel drum	1.06050.6010
						25 I	Stainless steel drum	1.06050.6025
						2.5	Glass bottle	1.07020.2500
	Dichloromethane for analysis EMPARTA <sup>®</sup> ACS	75-09-2	≥ 99.5%	≤ 0.002%	≤ 0.02%	4	Glass bottle	1.07020.4000
						10 I	Stainless steel drum	1.07020.6010
						1	Glass bottle	8.22271.1000
	Dichloromethane EMPLURA®	75-09-2	≥ 99.0%	≤ 0.002%	≤ 0.1%	2.5	Glass bottle	8.22271.2500
						25 I	Metal drum	8.22271.9025
	Diethanolamine for analysis $EMSURE^{\circledast}$	111-42-2	≥ 99.5%		≤ 0.25%	1	HDPE bottle	1.16205.1000
						1	Glass bottle	1.00921.1000
						2.5 I	Glass bottle	1.00921.2500
	Diethyl ether for analysis EMSURE® ACS, ISO, Reag. Ph Eur	60-29-7	> 99 7%	< 0.0005%	≤ 0.03%	5 I	Aluminum bottle	1.00921.5000
		00237	≥ 99.7%	≤ 0.0005%	_ 0.0570	10 I	Stainless steel drum	1.00921.6010
						25 I	Stainless steel drum	1.00921.6025
						190 I	Stainless steel drum	1.00921.6190

-		_
50	lvents	D

Product	CAS No.	Purity (GC	) Evap. residu	ue Water	Content	Packaging	Ord. No
Diethyl ether for analysis EMPARTA®	co 20 7	> 00 5%	< 0.0010/	< 0.10/	2.5 l	Glass bottle	1.07026.2500
ACS	60-29-7	≥ 99.5%	≤ 0.001%	≤ 0.1%	5 I	Aluminum bottle	1.07026.5000
					1	Glass bottle	1.00923.1000
Diethyl ether EMPLURA®	60-29-7	≥ 99.0%		≤ 0.2%	5 1	Aluminum bottle	1.00923.5000
					25 I	Stainless steel drum	1.00923.6025
Diethyl ether for analysis, Ethanol	CO 20 7	> 00 00/	< 0.0010/		4	Glass bottle	1.07062.400
stabilized EMPARTA® ACS	60-29-7	≥ 98.0%	≤ 0.001%	≤ 0.5%	5 I	Aluminum bottle	1.07062.500
					1	Glass bottle	1.00867.100
Diisopropyl ether for analysis	109 20 2	> 00 00/		< 0.0E0/	2.5 I	Glass bottle	1.00867.250
EMSURE <sup>®</sup> ACS, Reag. Ph Eur	108-20-3	≥ 99.0%	≤ 0.005%	≤ 0.05% ·	4	Glass bottle	1.00867.400
					10	Stainless steel drum	1.00867.601
					1	Glass bottle	1.03053.100
					1	HDPE bottle	1.03053.101
N,N-Dimethylformamide for analysis	68-12-2 ≥ 99.8% ≤ 0.001% ≤ 0.3				2.5 I	Glass bottle	1.03053.250
EMSURE® ACS, ISO, Reag. Ph Eur		≤ 0.1%	2.5 I	HDPE bottle	1.03053.251		
					4	Glass bottle	1.03053.400
					25 I	Stainless steel drum	1.03053.602
					1	Glass bottle	1.03034.100
					1	HDPE bottle	1.03034.101
					2.5 I	Glass bottle	1.03034.250
N,N-Dimethylformamide EMPARTA®	68-12-2	≥ 99.5%	≤ 0.001%	≤ 0.1%	2.5	HDPE bottle	1.03034.251
					4	Glass bottle	1.03034.400
					25 I	Stainless steel drum	1.03034.602
		≥ 99.0%		≤ 0.1%	1	HDPE bottle	8.22275.100
N,N-Dimethylformamide EMPLURA®	68-12-2				2.5 I	HDPE bottle	8.22275.250
					25 I	Stainless steel drum	8.22275.602
					1	Glass bottle	1.02952.100
					1	HDPE bottle	1.02952.101
					2.5 I	Glass bottle	1.02952.250
Dimethyl sulfoxide for analysis					2.5 I	HDPE bottle	1.02952.251
EMSURE® ACS	67-68-5	≥ 99.9%	≤ 0.001%	≤ 0.1%	4	Glass bottle	1.02952.400
					5	HDPE bottle	1.02952.501
					25 I	PE / Metal drum	1.02952.902
					190 I	Stainless steel drum	1.02952.619
					1	Glass bottle	1.16743.100
Dimethyl sulfoxide EMPLURA®	67-68-5	≥ 99.0%		≤ 0.2%	25 I	Stainless steel drum	1.16743.602
						Glass bottle	1.09671.025
1,4-Dioxane for analysis EMSURE®					1	Glass bottle	1.09671.100
ACS, ISO	123-91-1	≥ 99.5%	≤ 0.001%	≤ 0.05%	2.5 I	Glass bottle	1.09671.250
					25	Stainless steel drum	1.09671.602
					11	Glass bottle	1.03115.100
					2.5	Glass bottle	1.03115.250
1,4-Dioxane EMPLURA®	123-91-1	≥ 99.0%		≤ 0.1%	251	Stainless steel drum	1.03115.602
					190		
					190 1	Metal drum	1.03115.919

Solvents E

	Product	CAS No.	Purity (GC	) Evap. residu	e Water	Content	Packaging	Ord.
		C 4 17 F	95.1-	< 25 mm m //		500 ml	Glass bottle	1.59010.0
	Ethanol 96% EMSURE <sup>®</sup> Reag. Ph Eur	64-17-5	96.9%	≤ 25 mg/l		2.5 I	Glass bottle	1.59010.2
						1	Glass bottle	1.00983.1
						1	HDPE bottle	1.00983.1
						2.5 I	Glass bottle	1.00983.2
						2.5 I	HDPE bottle	1.00983.2
	Ethanol absolute for analysis	64-17-5	≥ 99.9%	≤ 0.0005%	≤ 0.1%	4 I	Glass bottle	1.00983.4
	EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	04-17-5		≤ 0.0003%	≤ 0.170	5 I	HDPE bottle	1.00983.5
						10 I	Stainless steel drum	1.00983.6
						25 I	Stainless steel drum	1.00983.6
						25 I	PE / Metal drum	1.00983.9
						180 I	PE / Metal drum	1.00983.9
						2.5 I	HDPE bottle	1.07017.2
	Ethanol absolute for analysis EMPARTA <sup>®</sup> ACS	64-17-5	≥ 99.5%	≤ 0.001%	≤ 0.2%	4	Glass bottle	1.07017.4
						25 I	Metal drum	1.07017.9
		64 17 5	> 00 5%			1	HDPE bottle	8.18760.1
	Ethanol absolute EMPLURA®				< 0.20/	2.5 I	HDPE bottle	8.18760.2
		64-17-5	≥ 99.5%	≤ 0.0025%	≤ 0.2%	25 I	Metal drum	8.18760.9
						180 I	PE / Metal drum	8.18760.9
	Ethanol for analysis completely dena-					2.5 I	Glass bottle	1.03771.2
	tured with 1% Ethyl methyl ketone, 1% Isopropyl alcohol, 1 g/ 100 l		≥ 99.5%	≤ 0.005%	≤ 0.1%	5 I	HDPE bottle	1.03771.
	Denatonium benzoate EMSURE®					180 I	PE / Metal drum	1.03771.9
						1	HDPE bottle	1.00974.3
			≥ 99.5%	≤ 0.001%	≤ 0.1%	2.5 I	Glass bottle	1.00974.2
	Ethanol denatured with about 1%	64-17-5				2.5 I	HDPE bottle	1.00974.2
	Methyl ethyl ketone for analysis					4	Glass bottle	1.00974.4
	EMSURE®					25 I	Stainless steel drum	1.00974.0
						25 I	PE / Metal drum	1.00974.9
						180 I	Metal drum	1.00974.9
		4 4 4 1 2 5	5 00 F0/			1	Glass bottle	1.00845.3
	Ethanolamine for analysis EMSURE®	141-43-5	≥ 99.5%		≤ 0.2%	2.5 l	Glass bottle	1.00845.2
						1	HDPE bottle	1.09623.3
						2.5	Glass bottle	1.09623.2
						2.5 I	HDPE bottle	1.09623.2
						4	Glass bottle	1.09623.4
	Ethyl acetate for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	141-78-6	≥ 99.5%	≤ 0.001%	≤ 0.05%	5 I	HDPE bottle	1.09623.
	ACS, 150, Reag. FILLUI					10	Stainless steel drum	1.09623.0
						25 I	Stainless steel drum	1.09623.0
						25 I	PE / Metal drum	1.09623.9
						180 I	PE / Metal drum	1.09623.9
	Ethyl acetate for analysis EMPARTA® ACS	141-78-6	≥ 99.5%	≤ 0.003%	≤ 0.2%	4	Glass bottle	1.07048.4
						2.5 l	HDPE bottle	8.22277.2
	Ethyl acetate EMPLURA®	141-78-6	≥ 99.5%	≤ 0.003%	≤ 0.1%	5 I	HDPE bottle	8.22277.5

So	vents	: F-H

	Product	CAS No.	Purity (GC)	Evap. resid	ue Water	Content	Packaging	Ord. No.
Е						1	HDPE bottle	1.09621.1000
	Ethylene glycol for analysis EMSURE®					2.5 I	HDPE bottle	1.09621.2500
	Reag. Ph Eur, Reag. USP	107-21-1	≥ 99.5%		≤ 0.1%	4	Glass bottle	1.09621.4000
						25 I	PE canister	1.09621.9028
						1	HDPE bottle	1.00949.1000
	Ethylene glycol EMPLURA®	107-21-1	≥ 99.0%		≤ 0.3%	2.5 I	HDPE bottle	1.00949.2500
						25 I	PE canister	1.00949.9028
	Ethylene glycol monomethyl ether for	100.06.4				1	Glass bottle	1.00859.1000
	analysis EMSURE® ACS, Reag. Ph Eur	109-86-4	≥ 99.5%	≤ 0.003%	≤ 0.1%	2.5 I	Glass bottle	1.00859.2500
						1	Glass bottle	1.09639.1000
	Ethyl(-)-L-lactate EMPLURA®	687-47-8	≥ 99.0%		≤ 0.2%	2.5	Glass bottle	1.09639.2500
						4	Glass bottle	1.09639.4000
						1	Glass bottle	1.09708.1000
						2.5	Glass bottle	1.09708.2500
	Ethyl methyl ketone for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	78-93-3	≥ 99.5%	≤ 0.001%	≤ 0.05%	4	Glass bottle	1.09708.4000
	EMSUKE® ACS, Keag. Ph Eur					25 I	Stainless steel drum	1.09708.6025
						190 I	Stainless steel drum	1.09708.6190
	Ethyl methyl ketone for analysis EMPARTA® ACS	78-93-3	≥ 99.0%		≤ 0.2%	2.5 I	Glass bottle	1.07049.2500
						1	Glass bottle	1.06014.1000
						2.5 I	Glass bottle	1.06014.2500
	Ethyl methyl ketone (2-Butanone) EMPLURA®	78-93-3	≥ 99.0%		≤ 0.1%	10 I	Metal drum	1.06014.9011
						25 I	Stainless steel drum	1.06014.6025
						190 I	Metal drum	1.06014.9190
F						1	Glass bottle	1.01771.1000
	FAM Benzine DIN 51635	64742-49-0				5 I	Aluminum bottle	1.01771.5000
						25 I	Stainless steel drum	1.01771.6025
	Formamida for analysis EMCUDE®	75-12-7	> 00 E%		< 0.10/	1	HDPE bottle	1.09684.1000
	Formamide for analysis EMSURE <sup>®</sup>	/5-12-/	≥ 99.5%		≤ 0.1%	2.5 I	HDPE bottle	1.09684.2500
	Formamide EMPLURA®	75-12-7	≥ 99.0%		≤ 0.3%	1	HDPE bottle	1.04008.1000
		/5-12-/	≥ 99.0%		≤ 0.3%	2.5 I	HDPE bottle	1.04008.2500
						500 ml	HDPE bottle	1.04094.0500
	Glycerol 85% for analysis EMSURE®			0/	14.5 -	1	HDPE bottle	1.04094.1000
	Reag. Ph Eur		84.5 - 85.5	70	15.5%	2.5 I	HDPE bottle	1.04094.2500
						25 I	PE canister	1.04094.9026
						2.5 I	HDPE bottle	1.04057.2511
	Glycerol (vegetable origin) for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	56-81-5	≥ 99.5%		≤ 0.5%	10 I	PE canister	1.04057.9011
	anaiysis Empores ACS, Kedy. Mi EUr					25 I	PE canister	1.04057.9026
н						1	Glass bottle	1.04307.1000
	n-Heptane about 85% EMPLURA®	142-82-5	≥ 85.0%	≤ 0.005%		2.5 I	Glass bottle	1.04307.2500
						4	Glass bottle	1.04307.4000

Solvents H–I

	Product	CAS No.	Purity (GC	) Evap. residu	e Water	Content	Packaging	Ord. No.
н						1	Glass bottle	1.04379.1000
						2.5 I	Glass bottle	1.04379.2500
						2.5 l	HDPE bottle	1.04379.2511
	n-Heptane for analysis EMSURE® Reag. Ph Eur	142-82-5	≥ 99.0%	≤ 0.001%	≤ 0.01%	4	Glass bottle	1.04379.4000
	Reag. Th Eur					10 I	Stainless steel drum	1.04379.6010
						25 I	Stainless steel drum	1.04379.6025
						190 I	Stainless steel drum	1.04379.6190
						1	Glass bottle	1.04365.1000
						2.5 I	Glass bottle	1.04365.2500
		142.02.5	> 00 00/			2.5 I	HDPE bottle	1.04365.2511
	n-Heptane EMPLURA®	142-82-5	≥ 99.0%	≤ 0.005%		10	Metal drum	1.04365.9011
						25 I	Stainless steel drum	1.04365.6025
						190 I	Stainless steel drum	1.04365.6190
	Hexanes for analysis EMPARTA <sup>®</sup> ACS	110-54-3	> 09 E0/	≤ 0.01%		1	Glass bottle	1.07060.1000
	Hexanes for analysis EMPARTA® ACS	110-54-3	≥ 98.5%	≤ 0.01%		4	Glass bottle	1.07060.4000
						1	Glass bottle	1.04367.1000
						2.5 I	Glass bottle	1.04367.2500
	n-Hexane for analysis EMSURE® ACS	110-54-3	≥ 99.0%	≤ 0.001%	≤ 0.005%	2.5 I	HDPE bottle	1.04367.2511
						25 I	Stainless steel drum	1.04367.6025
						190 I	Stainless steel drum	1.04367.6190
						1	Glass bottle	1.04374.1000
						2.5 I	Glass bottle	1.04374.2500
	n-Hexane for analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	110-54-3	≥ 96.0%	≤ 0.001%	< 0.010/	2.5 l	HDPE bottle	1.04374.2511
		110-54-3	≥ 96.0%		≤ 0.01%	4	Glass bottle	1.04374.4000
						25 I	Stainless steel drum	1.04374.6025
						190 I	Stainless steel drum	1.04374.6190
		110-54-3	≥ 98.5%			2.5 l	HDPE bottle	1.07023.2511
	n-Hexane for analysis EMPARTA <sup>®</sup> ACS			≤ 0.001%	≤ 0.02%	4	Glass bottle	1.07023.4000
						25 I	Stainless steel drum	1.07023.6025
						1 I	Glass bottle	1.04368.1000
						2.5 l	Glass bottle	1.04368.2500
						2.5 l	HDPE bottle	1.04368.2511
	n-Hexane EMPLURA®	110-54-3	≥ 95.0%		≤ 0.02%	10 I	Metal drum	1.04368.9011
						25 I	Stainless steel drum	1.04368.6025
						190 I	Stainless steel drum	1.04368.6190
						190 I	Metal drum	1.04368.9190
I	Isoamyl acetate EMPLURA®	123-92-2	≥ 99.0%		≤ 0.1%	1	Glass bottle	1.01231.1000
						1	Glass bottle	1.00979.1000
	Isoamyl alcohol for analysis EMSURE®	100 51 0	> 00 00/	< 0.0020/	< 0.20/	2.5 I	Glass bottle	1.00979.2500
	ACS, Reag. Ph Eur	123-51-3	≥ 99.0%	≤ 0.002%	≤ 0.2%	4	Glass bottle	1.00979.4000
						25 I	Stainless steel drum	1.00979.6025
	Isoamyl alcohol (mixture of icomore)					1.1	HDPE bottle	9 222EE 1000
	Isoamyl alcohol (mixture of isomers)	30899-19-1			≤ 0.3%	1	HDPE Dollie	8.22255.1000

	Product	CAS No.	Purity (GC)	Evap. residu	e Water	Content	Packaging	Ord. No.
I	Isoamyl alcohol (mixture of isomers)	30899-19-5				1	Glass bottle	1.00978.1000
	for determination of fat acc. to Gerber	50055 15 5			≤ 0.3%	10	Stainless steel drum	1.00978.6010
	Isobutanol for analysis EMSURE® ACS,					1	Glass bottle	1.00984.1000
	Reag. Ph Eur	78-83-1	≥ 99.0%	≤ 0.001%	≤ 0.05%	2.5 I	Glass bottle	1.00984.2500
						2.5 I	Glass bottle	1.00985.2500
	Isobutanol (Isobutyl alcohol) EMPLURA®	78-83-1	≥ 98.5%		≤ 0.05%	25 I	Stainless steel drum	1.00985.6025
						190 I	Metal drum	1.00985.9190
						1	Glass bottle	1.06146.1000
	Isobutyl methyl ketone for extraction	108-10-1	≥ 99.0%	≤ 0.001%	≤ 0.1%	2.5 I	Glass bottle	1.06146.2500
	analysis EMSURE <sup>®</sup> ACS, Reag. Ph Eur	100-10-1	≥ 99.0%	\$ 0.001%	≤ 0.170	4	Glass bottle	1.06146.4000
						25 I	Stainless steel drum	1.06146.6025
						2.5	Glass bottle	8.20820.2500
	Isobutyl methyl ketone EMPLURA®	108-10-1	≥ 99.0%			10	Stainless steel drum	8.20820.6010
						25 I	Stainless steel drum	8.20820.6025
		92112-69-1				1	Glass bottle	1.04333.1000
	Isohexane for analysis EMSURE®		≥ 95.0%	$\leq$ 10 mg/l	≤ 0.01%	2.5 I	Glass bottle	1.04333.2500
						190 I	Stainless steel drum	1.04333.6190
	Isooctane for analysis EMSURE® ACS, Reag. Ph Eur					1	Glass bottle	1.04727.1000
						2.5 l	Glass bottle	1.04727.2500
		540-84-1	≥ 99.5%	≤ 0.001%	≤ 0.01%	4	Glass bottle	1.04727.4000
						10 I	Stainless steel drum	1.04727.6010
						25 I	Stainless steel drum	1.04727.6025
К	Kerosene EMPLURA®	64742-48-9				4	Glass bottle	1.09774.4000
М				≤ 0.0005%		1	Glass bottle	1.06009.1000
						1	HDPE bottle	1.06009.1011
						2.5	Glass bottle	1.06009.2500
						2.5	HDPE bottle	1.06009.2511
	Methanol for analysis EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	67-56-1	≥ 99.9%		≤ 0.05%	4	Glass bottle	1.06009.4000
	ACS, ISO, Reag. Ph Eur					51	HDPE bottle	1.06009.5000
						10	Stainless steel drum	1.06009.6010
						25 I	Stainless steel drum	1.06009.6025
						25	PE / Metal drum	1.06009.9025
						180	PE / Metal drum	1.06009.9180
						2.5	HDPE bottle	1.07018.2511
	Methanol for analysis EMPARTA® ACS	67-56-1	≥ 99.8%	≤ 0.001%	≤ 0.1%	4	Glass bottle	1.07018.4000
						25	Metal drum	1.07018.9026
						11	HDPE bottle	8.22283.1000
						2.5	HDPE bottle	8.22283.2500
	Methanol EMPLURA®	67-56-1	≥ 99.5%	≤ 0.001%	≤ 0.1%	51	HDPE bottle	8.22283.5000
						10	Metal drum	8.22283.9011
						25	Metal drum	8.22283.9025
						180 I	PE / Metal drum	8.22283.9180

Solvents M-P

Product	CAS No.	Purity (GC	C) Evap. residu	ue Water	Content	Packaging	Ord. No.
					1	Glass bottle	1.06012.1000
Methanol anhydrous for analysis				-	2.5 I	Glass bottle	1.06012.2500
(max. $0.003\%$ H <sub>2</sub> O)	67-56-1	≥ 99.9%	≤ 10 mg/l	≤ 0.003% -	10	Stainless steel drum	1.06012.6010
				-	25 I	Stainless steel drum	1.06012.6025
					1	Glass bottle	1.06059.1000
1ethyl benzoate EMPLURA®	93-58-3	≥ 99.0%		- ≤ 0.1%	2.5 l	Glass bottle	1.06059.2500
				-	25 I	Stainless steel drum	1.06059.6025
	107.00.0	× 00 F0/		1 0 10/	1	Glass bottle	1.16738.1000
1-Methoxy-2-propanol EMPLURA®	107-98-2	≥ 99.5%		≤ 0.1% -	25 I	Stainless steel drum	1.16738.6025
					1	HDPE bottle	8.06072.1000
	070 50 4			-	2.5 I	HDPE bottle	8.06072.2500
1-Methyl-2-pyrrolidone EMPLURA®	872-50-4	≥ 99.5%		≤ 0.1% -	10 I	Metal drum	8.06072.9011
				-	25 I	PE canister	8.06072.9025
					1	Glass bottle	1.08292.1000
2-Methyltetrahydrofuran EMPLURA®	96-47-9	≥ 99.0%		≤ 0.1%	2.5 I	Glass bottle	1.08292.2500
				-	4	Glass bottle	1.08292.4000
1-Octanol EMPLURA®					1	Glass bottle	1.00991.1000
	111-87-5	≥ 99.0%		≤ 0.1% -	25 I	Stainless steel drum	1.00991.6025
					1	Glass bottle	1.07176.1000
n-Pentane about 95% EMPLURA®	109-66-0	≥ 95.0%	≤ 0.005%	-	5	Aluminum bottle	1.07176.5000
				-	190 I	Metal drum	1.07176.9190
					1	Glass bottle	1.07177.1000
n-Pentane for analysis EMSURE®	109-66-0	≥ 99.0%	≤ 0.001%	≤ 0.01%	2.5 I	Glass bottle	1.07177.2500
,				-	4	Glass bottle	1.07177.4000
					1	Glass bottle	8.20957.1000
n-Pentane EMPLURA®	109-66-0	≥ 99.0%		-	2.5 l	Glass bottle	8.20957.2500
				-	25 I	Metal drum	8.20957.9025
					1	Glass bottle	1.09718.1000
Petroleum for analysis EMSURE®	64742-48-	9		≤ 0.01%	2.5 l	Glass bottle	1.09718.2500
				-	25 I	Stainless steel drum	1.09718.6025
Petroleum benzine boiling range		_			1	Glass bottle	1.01786.1000
30–50°C for analysis EMSURE®	64742-49-	0	≤ 0.003%	≤ 0.01% -	2.5 I	Glass bottle	1.01786.2500
					1	Glass bottle	1.00915.1000
Petroleum benzine boiling range to about 40°C EMPLURA®	64742-49-	0	≤ 0.002%	≤ 0.01%	5	Aluminum bottle	1.00915.5000
about 40 C EMPLONA				-	25 I	Stainless steel drum	1.00915.6025
					1	Glass bottle	1.01775.1000
				-	2.5 I	Glass bottle	1.01775.2500
				-	4	Glass bottle	1.01775.4000
Petroleum benzine for analysis boiling	64742-49-	0	≤ 0.001%	≤ 0.01%	5	Aluminum bottle	1.01775.5000
range 40–60°C EMSURE <sup>®</sup> ACS, ISO				-	10 I	Stainless steel drum	1.01775.6010
				-	25 I	Stainless steel drum	1.01775.6025
				-	190 I	Stainless steel drum	1.01775.6190

Р

Solvents P							
Product	CAS No.	Purity (GC	C) Evap. residu	e Water	Content		Ord. No.
Petroleum benzine boiling range					1	Glass bottle	1.01773.1000
40-80°C EMPLURA®			≤ 0.001%	≤ 0.01%	5 I	Aluminum bottle	1.01773.5000
					25 I	Stainless steel drum	1.01773.6025
Petroleum benzine boiling range					1	Glass bottle	1.00910.1000
50–70°C EMPLURA®	64742-49-0	D	≤ 0.001%	≤ 0.01%	5	Aluminum bottle	1.00910.5000
					25 I	Stainless steel drum	1.00910.6025
					1	Glass bottle	1.01774.1000
Petroleum benzine boiling range			≤ 0.001%	≤ 0.01%	2.5 I	Glass bottle	1.01774.2500
60–80°C for analysis EMSURE®			2 0.001 /0	2 0.01 /0	5	Aluminum bottle	1.01774.5000
					25 I	Stainless steel drum	1.01774.6025
Petroleum benzine boiling range 80-100°C for analysis EMSURE®	64742-49-0	)	≤ 0.001%	≤ 0.01%	1	Glass bottle	1.01777.1000
Petroleum benzine boiling range 100–120°C for analysis EMSURE <sup>®</sup> Reag. Ph Eur	64742-49-(	)	≤ 0.001%	≤ 0.01%	1	Glass bottle	1.01781.1000
Petroleum benzine boiling range					1	Glass bottle	1.01770.1000
Petroleum benzine bolling range 100–140°C (Naphta Benzine) EMPLURA®	64742-49-0	)	≤ 0.005%	≤ 0.01%	5	Aluminum bottle	1.01770.5000
					25 I	Stainless steel drum	1.01770.6025
Petroleum benzine boiling range 140-180 °C EMPLURA®	64742-82-1	1			1	Glass bottle	8.14563.1000
					1	Glass bottle	1.01769.1000
					5 I	Aluminum bottle	1.01769.5000
Petroleum ether for denaturation					10 I	Stainless steel drum	1.01769.6010
					25 I	Stainless steel drum	1.01769.6025
					190 I	Metal drum	1.01769.9190
Piperidine for analysis EMSURE®	110-89-4	≥ 99.0%	≤ 0.1%	≤ 0.3%	500 ml	Glass bottle	1.09724.0500
					1	HDPE bottle	8.22324.1000
1,2-Propanediol EMPLURA®	57-55-6	≥ 99.0%		≤ 0.2%	5	HDPE bottle	8.22324.5000
					1	Glass bottle	1.00997.1000
1-Propanol for analysis EMSURE®					2.5 I	Glass bottle	1.00997.2500
ACS, Reag. Ph Eur	71-23-8	≥ 99.5%	≤ 0.001%	≤ 0.05%	4	Glass bottle	1.00997.4000
					25 I	Stainless steel drum	1.00997.6025
					1	Glass bottle	1.00996.1000
1-Propanol EMPLURA®	71-23-8	≥ 99.0%		≤ 0.2%	2.5 I	Glass bottle	1.00996.2500
					25 I	Stainless steel drum	1.00996.6025
					1	Glass bottle	1.09634.1000
					1	HDPE bottle	1.09634.1011
					2.5	Glass bottle	1.09634.2500
					2.5	HDPE bottle	1.09634.2511
2-Propanol for analysis EMSURE®					4	Glass bottle	1.09634.4000
ACS, ISO, Reag. Ph Eur	67-63-0	≥ 99.8%	≤ 0.001%	≤ 0.05%	5 1	HDPE bottle	1.09634.5000
					10	Stainless steel drum	1.09634.6010
					25	Stainless steel drum	1.09634.6025
					190	Stainless steel drum	1.09634.6190
					190	PE / Metal drum	1.09634.9180
					1001		1.03034.9180

Solvents P-T

Product	CAS No.	Purity (GC	C) Evap. residu	e Water	Content	Packaging	Ord. No
					2.5 l	HDPE bottle	1.07022.251
2-Propanol for analysis EMPARTA® ACS	67-63-0	≥ 99.5%	≤ 0.001%	≤ 0.2%	4	Glass bottle	1.07022.400
				-	25 I	Metal drum	1.07022.902
					1	HDPE bottle	8.18766.100
	C7 C2 0			≤ 0.2%	2.5 I	HDPE bottle	8.18766.250
2-Propanol EMPLURA®	67-63-0	≥ 99.5%	≤ 0.002%		10 I	Metal drum	8.18766.901
				-	25 I	Metal drum	8.18766.902
					100 ml	Glass bottle	1.09728.010
				-	500 ml	Glass bottle	1.09728.050
				=	1	Glass bottle	1.09728.100
Pyridine for analysis EMSURE® ACS, Reag. Ph Eur	110-86-1	≥ 99.5%	≤ 0.002%	≤ 0.1%	2.5 I	Glass bottle	1.09728.250
				-	4	Glass bottle	1.09728.400
				-	25 I	Stainless steel drum	1.09728.602
				-	190 I	Stainless steel drum	1.09728.619
					0.5 I	Glass bottle	1.94601.050
Pyridine for analysis EMPARTA <sup>®</sup> ACS	110-86-1	≥ 99.0%	≤ 0.002%	≤ 0.1%	2.5 I	Glass bottle	1.94601.250
					4	Glass bottle	1.94601.400
					1	Glass bottle	1.07462.100
	110.00.1	> 00 00/	% ≤ 0.01%	-	2.5 l	Glass bottle	1.07462.250
Pyridine EMPLURA®	110-86-1	≥ 99.0%		≤ 0.1% -	25 I	Stainless steel drum	1.07462.602
				-	190 I	Metal drum	1.07462.919
			≤ 0.001%		1	Glass bottle	1.00964.100
	107 10 1	≥ 99.0%		-	2.5 I	Glass bottle	1.00964.250
Tetrachloroethylene EMPLURA®	127-18-4			≤ 0.005% -	25 I	Stainless steel drum	1.00964.602
				-	190 I	Metal drum	1.00964.919
					1	Glass bottle	1.09731.100
				-	2.5 I	Glass bottle	1.09731.250
Tetrahydrofuran for analysis	100.00.0			-	4	Glass bottle	1.09731.400
EMSURE <sup>®</sup> ACS, Reag. Ph Eur	109-99-9	≥ 99.8%	≤ 0.0005%	≤ 0.03% -	10 I	Stainless steel drum	1.09731.601
				-	25 I	Stainless steel drum	1.09731.602
				-	190 I	Stainless steel drum	1.09731.619
Tetrahydrofuran					2.5 l	Glass bottle	1.07025.250
for analysis EMPARTA® ACS	109-99-9	≥ 99.5%	≤ 0.03%	≤ 0.05% -	4	Glass bottle	1.07025.400
					1	Glass bottle	1.08114.100
				-	2.5 I	Glass bottle	1.08114.250
Tetrahydrofuran EMPLURA®	109-99-9	≥ 99.0%		≤ 0.1%	25 I	Stainless steel drum	1.08114.602
•				-	190 I	Stainless steel drum	1.08114.619
				-	190 l	Metal drum	1.08114.919

	Product	CAS No.	Purity (GC)	Evap. residu	e Water	Content	Packaging	Ord. No.
т						1	Glass bottle	1.08325.1000
					-	2.5 I	Glass bottle	1.08325.2500
						2.5 I	HDPE bottle	1.08325.2511
	Toluene for analysis EMSURE® ACS,	108-88-3	≥ 99.9%	≤ 0.0005%	≤ 0.03% -	4	Glass bottle	1.08325.4000
	ISO, Reag. Ph Eur	100-00-5	≥ 99.9%	≤ 0.0005%	≤ 0.03%	5 I	HDPE bottle	1.08325.5011
						10 I	Stainless steel drum	1.08325.6010
						25 I	Stainless steel drum	1.08325.6025
						190 I	Stainless steel drum	1.08325.6190
						2.5 I	Glass bottle	1.07019.2500
	Toluene for analysis EMPARTA® ACS	108-88-3	≥ 99.5%	$\leq 0.001\%$	≤ 0.03%	2.5 I	HDPE bottle	1.07019.2511
						4	Glass bottle	1.07019.4000
					-	1	Glass bottle	1.08323.1000
					-	2.5	Glass bottle	1.08323.2500
	Toluene EMPLURA®	108-88-3	≥ 99.0%			10 I	Metal drum	1.08323.9011
						25 I	Stainless steel drum	1.08323.6025
						190 I	Metal drum	1.08323.9190
	1,1,2-Trichlorotrifluoroethane for analysis EMSURE <sup>®</sup> Reag. Ph Eur	76-13-1	≥ 99.8%	≤ 0.0005%	≤ 0.005%	2.5 I	Glass bottle	1.08440.2500
		102 71 6			< 0.20/	5 I	PE canister	8.22341.5000
	Triethanolamine EMPLURA®	102-71-6			≤ 0.3% -	25 I	PE canister	8.22341.9026
U	n-Undecane for analysis EMSURE®	1120-21-4	≥ 99.0%		≤ 0.01%	100 ml	Glass bottle	1.09795.0100
w						4	Titripac	1.16754.4000
	Water for analysis EMSURE®	7732-18-5	≥ 99.0%	≤ 1 mg/l	≤ 0.01%	5 I	HDPE bottle	1.16754.5000
						10 I	Titripac	1.16754.9010
X						1	Glass bottle	1.08684.1000
	p-Xylene for analysis EMSURE® ISO	106-42-3	≥ 99.0%	≤ 0.001%	≤ 0.01%	2.5 I	Glass bottle	1.08684.2500
						25 I	Stainless steel drum	1.08684.6025
	Xylene (isomeric mixture) for analysis	1220 20 7	> 09 E0/		< 0.020/	2.5 I	Glass bottle	1.08297.2500
	EMSURE <sup>®</sup> ACS, ISO, Reag. Ph Eur	1330-20-7	2 98.5%	≤ 0.002%	≤ 0.03% -	4	Glass bottle	1.08297.4000
	Xylenes (isomeric mixture) for	1220 20 7	> 09 E04	< 0.0020/	< 0.050/	2.5 I	Glass bottle	1.08633.2500
	analysis EMPARTA® ACS	1330-20-7	≤ 90.3%	≤ 0.002%	≤ 0.05% ·	4	Glass bottle	1.08633.4000
	Xylenes (isomeric mixture) EMPLURA®	1330-20-7		≤ 0.002%	≤ 0.05%	2.5 I	Glass bottle	1.08634.2500





For more details about our packaging, please see "Packaging and Safe Handling" on page 42

# Essentials for daily lab routines

### Safety, simplicity and sustainability

We offer a comprehensive range of general application chemicals, which are designed to maximize safety and simplicity in daily lab work. Wherever possible, we use natural products to ensure that we both work more sustainably and achieve our environmental targets.



120

 For more information about cleaning applications see page 122

 For more information about absorption and filtration see page 134

### **Cleaning Applications** Extran<sup>®</sup> detergents for reliable, residue-free cleaning

Thorough, residue-free cleaning is essential for reliable processes. This applies to both: laboratories and production facilities. Everything that comes into contact with chemicals or biological substances must be free of impurities, both before and after use.

Put your trust in many years of Extran<sup>®</sup> experience from Merck and use our detergents for **manual cleaning** (MA) or **machine cleaning** in laboratory washing machines (AP).

#### Your advantages

Extran<sup>®</sup> is a reliable cleaning agent of consistent composition that ensures proper scientific working procedures and avoids a frequently modification of processes and applications.

- **Reliable results** by long-term detergent experience, constant product quality and composition, outstanding solubility and flowability
- Environmental protection by bio-degradable active ingredients
- **Reliable residue-free cleaning with validation support** to prove the absence of nonionic surfactants by means of a photometric test
- **Health protection** no known allergy risk or smell nuisance because Extran<sup>®</sup> is free of scent, dyestuff, oxidants, chlorine, enzymes and NTA. Extran<sup>®</sup> replaces toxic cleaning agents
- Save time and money with highly concentrated Extran<sup>®</sup> detergents and technical application support
- High flexibility and safety by a broad range of different pack sizes from 1 l to 25 l, from 2 kg to 25 kg – and specially developed withdrawal products and adapters





Pro	pert	ies	_	_	_		Applicati cleaning		ss (x - goo	od, xx - ver	y good, xxx - outs	standing)		
liquid	powder	acidic	neutral	mildly alkaline	alkaline	special properties	Food residues	Fat / wax / silicones	Organic residues	Inorganic residues	Colors/ lacquer/ pigments	Blood / cells / proteins	Extran® type	Cat. no.*
Mai	nual	clea	anir	ıg										
х					х		xx		xx	xx	xx	хх	MA 01	107555
х			х					xx	х	xx	х		MA 02	107553
x					x	phosphate-free	x	xx	x	x	xx	х	MA 05	140000
Ара	arati	ve c	lea	ning	(di	shwasher)								
	х			х			х	xx	х	xx	х	х	AP 11	107558
	x				x		xx	x	xx	xx	ххх	xx	AP 12	107563
	х				х	with detergents	xx	х	xx	х	х	xx	AP 13	107565
x					x		xx	xx		xx	xx	хх	AP 17	140006
х				х			х			xx	х	х	AP 18	140118
x		x				with phosphoric acid	x	x	xx	x			AP 21	107559
х		х				with citric acid	х	х	xx	х			AP 22	107561
	х					enzymatic	xx	xx	x	x			AP 41	107570

\*please see following pages for available pack sizes

### **Cleaning Applications** Extran<sup>®</sup> detergents for manual washing

#### Manual washing – Application

The Extran<sup>®</sup> MA types for manual washing are universally applicable concentrates for the production of water baths which work reliably and without residue.

- Water is used to prepare the cleaning solution. If slight sedimentation of the hardener occurs, more Extran<sup>®</sup> must be added. De-mineralized water boosts the cleaning effect.
- For cleaning, the items to be cleaned are simply immersed completely in the solution.
- Once cleaning is finished, they are rinsed first with tap water and then with demineralised water.
- The baths can be used for a longer time without a noticeable decrease in the cleaning effect.
- If necessary, the rinsing liquid can be supplemented with fresh Extran<sup>®</sup>.
- The length of application is less than 2 hours.
- For "difficult cases" such as plaster, blood or heavy oil, the items to be cleaned are simply left in the bath a little longer.
- Heat speeds up the cleaning process.
- Extran<sup>®</sup> is also ideally suited to ultrasound cleaning.

 x123456789
 1.07553.2500
 Supelco.

 Extran®
 MA 02

 Induid, neutral, concentrate

251



#### **Dosing aid**

For dependable and economical cleaning, the detergent must be dosed precisely: too little cleans insufficiently, too much leaves residues. To ensure accurate dosing and safe handling during manual cleaning, we offer 1 l bottles with reusable dosing aids. They can also be ordered separately if required.

Extran <sup>®</sup> MA 01 liquid, alkaline	Content	Packaging	Ord. No.
Extran <sup>®</sup> MA 01 alkaline	1	HDPE bottle	1.07555.1000
	2.5 l	HDPE bottle	1.07555.2500
	5 I	HDPE bottle	1.07555.5000
	10	PE canister	1.07555.9010
	25 I	PE canister	1.07555.9025

Extran <sup>®</sup> MA 02 liquid, neutral	Content	Packaging	Ord. No.
Extran <sup>®</sup> MA 02 neutral	2.5	HDPE bottle	1.07553.2500
	5	HDPE bottle	1.07553.5000
	10	PE canister	1.07553.9010
	25	PE canister	1.07553.9025

Extran <sup>®</sup> MA 05 liquid, alkaline, phosphate-free	Content	Packaging	Ord. No.
Extran <sup>®</sup> MA 05 alkaline, phosphate-free concentrate	2.5 I	HDPE bottle	1.40000.2500
	5	HDPE bottle	1.40000.5000
	10	PE canister	1.40000.9010
	25 I	PE canister	1.40000.9025

Accessories	Ord. No.
Dosing unit (PP) 20-28 ml for 1 l Extran <sup>®</sup> bottle	9.57571.1020
Bottle opening key for S40 and S28 screw caps	1.08801.0001

### **Cleaning Applications** Extran<sup>®</sup> detergents for automated cleaning


#### **Automated cleaning**

Extran<sup>®</sup> AP automated cleaning detergents were created and tested in cooperation with leading appliance manufacturers especially for use in laboratory washing machines. The products ensure effective cleaning, while significantly limiting foam formation and minimizing residues. The good solubility in water of all components minimizes residues on appliances which have been cleaned.

Туре	Designation	Con	tent	Packaging	Ord. No.
AP 11	powder, mildly alkaline	2	kg	HDPE bottle	1.07558.2000
		10	kg	PE drum	1.07558.9010
		25	kg	PE drum	1.07558.9025
AP 12	powder, alkaline	2	kg	HDPE bottle	1.07563.2000
		10	kg	PE drum	1.07563.9010
		25	kg	PE canister	1.07563.9025
AP 13	powder, alkaline with detergents	2	kg	HDPE bottle	1.07565.2000
		10	kg	PE drum	1.07565.9010
		25	kg	PE drum	1.07565.9025
AP 17	liquid, alkaline concentrate	2.5	I	HDPE bottle	1.40006.2500
		5	I	HDPE bottle	1.40006.5000
	NE	EW 5	I	PE canister	1.40006.5001
		10	I	PE canister	1.40006.9010
		25	I	PE canister	1.40006.9025
AP 18	liquid, mild alkaline concentrate	2.5	I	HDPE bottle	1.40118.2500
		5	I	HDPE bottle	1.40118.5000
	NE	<b>EW</b> 5	Ι	PE canister	1.40118.5001
		10	Ι	PE canister	1.40118.9010
		25	Ι	PE canister	1.40118.9025
AP 21	liquid, acidic, concentrate (contains phosphoric acid)	2.5	I	HDPE bottle	1.07559.2500
	NE	<b>EW</b> 5	Ι	PE canister	1.07559.5001
		10	Ι	PE canister	1.07559.9010
		25	Ι	PE canister	1.07559.9025
AP 22	liquid, acidic concentrate (contains citric acid)	2.5	Ι	HDPE bottle	1.07561.2500
	N	<b>EW</b> 5	Ι	PE canister	1.07561.5001
		10	Ι	PE canister	1.07561.9010
		25	Ι	PE canister	1.07561.9025
AP 41	powder, enzymatic	2	kg	HDPE bottle	1.07570.2000
		25	kg	PE drum	1.07570.9025



#### Top label with contents & essential safety information





### Your benefits

#### Safe

- no detergent contact from filling
- TOP LABEL with always visible product and safety information, additional blank space for individual documentation

#### Convenient

- direct connection
- no refill
- lightweight

#### Economical

- process automation
- reduces dishwasher repairs

#### Ecological

• non-toxic, biodegradable active ingredients

#### Extran<sup>®</sup> AP liquids in new 5 I canisters

Careful cleaning is essential in every lab. But it can pose risks and challenges, like accidental contact with harmful cleaner concentrates, frequent refilling of cleaning agents, or costly dishwasher repairs. That's why we now also offer our powerful, non-toxic, residue-free and biodegradable Extran<sup>®</sup> cleaners in new 5L canisters – making them the ideal fit for lab dishwashers. Discover quality perfected for your intended use.

> Ideal fit for lab dishwashers

### **Chemizorb® absorbents** The fast, safe and easy way to clear up chemical spills

Accidents happen in every lab at any time. With Chemizorb<sup>®</sup> absorbents, you can clear away aggressive or unpleasant spilled liquids quickly and safely. Our fast-acting absorbents consist of porous mineral or synthetic copolymers that are chemically inert, and capable of absorbing up to 400% of their own weight.

#### Your benefits:

- Easy dosing due to the wide bottle neck
- Clear process monitoring
- Bright red bottle stands out among other HDPE bottles

#### The **»all-rounders**« - quick help for multiple spillages

Chemizorb<sup>®</sup> powder and granule absorbents are insoluble in water and in all other media that are liquid at room temperature. These "all-rounders" are suitable for removing nearly all kinds of aqueous spills, such as acids, alkalis and solvents.

Chemizorb <sup>®</sup> powder	Content	Packaging	Ord. No.
	500 g	HDPE bottle	1.02051.0500
Chemizorb <sup>®</sup> powder absorbent for spilled liquids	25 kg	Fibre carton	1.02051.9025
Chemizorb <sup>®</sup> granules	Content	Packaging	Ord. No.
	1 kg	HDPE bottle	1.01568.1000
	5 kg	Bucket, plastic	1.01568.5000
Chemizorb <sup>®</sup> granules absorbent for spilled liquids	20 kg	Paper sack	1.01568.9020
	20 kg	PE drum	1.01568.9021

#### The »specialists« - make use of our experience

We offer specific absorbents for alkalis, acids, and hydrofluoric acid. Each contains special carrier materials and water-soluble neutralizers, as well as pH indicators that help you visually monitor the neutralization of the spilled chemicals. Please note that the reaction may generate heat and gas.

Chemizorb <sup>®</sup> OH <sup>-</sup>	Content	Packaging	Ord. No.
Chemizorb® OH <sup>-</sup> absorbent and neutralizer for spilled alkalis, with indicator	1 kg	HDPE bottle	1.01596.1000
Chemizorb <sup>®</sup> H <sup>+</sup>	Content	Packaging	Ord. No.
Chemizorb <sup>®</sup> H <sup>+</sup> absorbent and neutralizer for spilled	2 kg	HDPE bottle	1.03874.2000
acids, with indicator	5 kg	Bucket, plastic	1.03847.5000
Chemizorb® HF	Content	Packaging	Ord. No.
Chemizorb <sup>®</sup> HF absorbent and neutralizer for spilled hydrofluoric acid, with indicator	1 kg	HDPE bottle	1.01591.1000

#### The **»all-in-one**« set for mercury

Chemizorb<sup>®</sup> Hg kit Mercury is an all-inclusive set of reagents and auxiliaries for safe and complete removal of mercury drops and traces of elementary mercury. The reagents in the set are sufficient for decontaminating an area of roughly one square meter.

Chemizorb <sup>®</sup> Hg	Content	Packaging	Ord. No.
Chemizorb <sup>®</sup> Hg Reagents and accessories for absorbent for mercury	1 set	PE case	1.12576.0001
1 set consisting of: 500 g of reagent 1, 100 ml of reagent 2, one s	mall tub, one	e large disposal	can, protective gloves
Chemizorb <sup>®</sup> Hg reagents refill pack for Cat. No. 1.12576.0001	1 set	PE can	1.01569.0001
1 set consisting of: 500 g reagent 1 and 100 ml reagent 2			





### **Drying Agents** Optimize desiccation with absolute reliability

Our Drying agents (desiccants) are developed, produced and rigorously tested to ensure optimal drying processes, whether in the laboratory, during storage, or for transportation. Our comprehensive portfolio offers user-friendly solutions for a wide range of applications – from drying gases, liquids or solids using static or dynamic drying processes, to protecting sensitive goods and materials from moisture, mold or corrosion. Regardless of your application, you can always expect reliable, reproducible results. Because, at Merck, **consistency is our standard.**  **Safety information:** Dangers of silica gel with blue indicator According to the European Chemicals Agency (ECHA), cobalt dichloride (CoCl<sub>2</sub>) is a substance of very high concern (SVHC), which is classified as carcinogenic and toxic for reproduction\*. This hazardous inorganic compound is present in silica gel containing blue indicator. When working with the desiccant, any dust particles emitted may be easily inhaled, posing serious health hazards. To protect users from these risks, we offer a broad range of non-toxic silica gels, which are based on iron-salt instead of cobalt dichloride indicator. Explore our safe and reliable silica gels.

\*Source: ECHA "Candidate List of Substances of Very High Concern for Authorization"

#### **Your benefits**

- Safety: We strictly avoid the use of carcinogenic blue gel to **protect your health.**
- Economical: Optimal protection of goods, equipment or substances avoids replacement costs; **recoverable drying agents** can be used longer to reduce expenses.
- Reliability: **Effective moisture reduction** helps maintain your product's original condition, and ensures accurate results

### **Drying Agents** Optimize desiccation with absolute reliability



Calcium chloride [CaCl <sub>2</sub> ]	CAS No.	Content	Packaging	Ord. No.
		500 g	HDPE bottle	1.02378.0500
Calcium chloride anhydrous powder Reag. Ph Eur	10043-52-4	2.5 kg	HDPE bottle	1.02378.2500
		25 kg	Fibre carton	1.02378.9025
		1 kg	HDPE bottle	1.02379.1000
Calcium chloride anhydrous, granular $\sim 1-2$ mm	10043-52-4	5 kg	HDPE bottle	1.02379.5000
		25 kg	Fibre carton	1.02379.9025
		1 kg	HDPE bottle	1.02391.1000
Calcium chloride anhydrous, granular $\sim$ 2–6 mm	10043-52-4	5 kg	Fibre carton	1.02391.5000
		25 kg	Fibre carton	1.02391.9025
		1 kg	HDPE bottle	1.02392.1000
Calcium chloride anhydrous, granular $\sim$ 6–14 mm	10043-52-4	5 kg	Fibre carton	1.02392.5000
		25 kg	Fibre carton	1.02392.9025



Desiccant sachets [SiO <sub>2</sub> ]	Content	Packaging	Ord. No.
Desiccant sachet 10 g silica gel with humidity indicator (orange gel) sachet: 7 x 9 cm	50 units	Metal can	1.03804.0001
Desiccant sachet 100 g silica gel with humidity indicator (orange gel) sachet: 15 x 14 cm	10 units	Metal can	1.03805.0001
Desiccant sachet 250 g silica gel with humidity indicator (orange gel) sachet: 15 x 20.5 cm	10 units	Metal can	1.03806.0001
Desiccant sachet 3 g silica gel with humidity indicator (orange gel) sachet: $4 \times 7$ cm	100 units	Metal can	1.03803.0001
	1000 units	Fibre carton	1.03803.0002

Further desiccant sachets, e.g. 500 g, on request.



SICAPENT<sup>®</sup> drying agent



CAS No.	Content	Packaging	Ord. No.	
	250 g	HDPE bottle	1.05704.0250	
1318-02-1	1 kg	HDPE bottle	1.05704.1000	
	10 kg	Bucket, plastic	1.05704.9010	
	250 g	HDPE bottle	1.05734.0250	
-	1 kg	HDPE bottle	1.05734.1000	
1318-02-1	250 g	HDPE bottle	1.05741.0250	
	1 kg	HDPE bottle	1.05741.1000	
1318-02-1		250 g	Glass bottle	1.05708.0250
	1 kg	Glass bottle	1.05708.1000	
	10 kg	Bucket, plastic	1.05708.9010	
	250 g	Glass bottle	1.05739.0250	
-	1 kg	Glass bottle	1.05739.1000	
1318-02-1	1 kg	HDPE bottle	1.05743.1000	
1318-02-1	1 kg	Glass bottle	1.05703.1000	
	1318-02-1 - 1318-02-1 1318-02-1 - 1318-02-1	250 g           1318-02-1         1 kg           10 kg         250 g           -         250 g           1 kg         1 kg           1318-02-1         250 g           1318-02-1         1 kg           1318-02-1         1 kg           10 kg         10 kg           1318-02-1         1 kg           10 kg         10 kg           10 kg         10 kg           1318-02-1         1 kg	250 g         HDPE bottle           1318-02-1         1 kg         HDPE bottle           10 kg         Bucket, plastic           250 g         HDPE bottle           1 kg         HDPE bottle           -         1 kg         HDPE bottle           1318-02-1         1 kg         HDPE bottle           1318-02-1         1 kg         HDPE bottle           1318-02-1         1 kg         Glass bottle           10 kg         Bucket, plastic         250 g           318-02-1         1 kg         Glass bottle           10 kg         Bucket, plastic         250 g           318-02-1         1 kg         Glass bottle           10 kg         Bucket, plastic         250 g           318-02-1         1 kg         Glass bottle           1 kg         Glass bottle         1 kg	



1) Molecular sieves with 0.3 nm bead form (105704) and with indicator brown gel (105734) are suitable for use in Karl Fischer titrators.

Phosphorus pentoxide $[P_2O_5]$	CAS No.	Content	Packaging	Ord. No.
di-Phosphorus pentoxide extra pure	1314-56-3	1 kg	Glass bottle	1.00540.1000
		25 kg	Plastic drum	1.00540.9025
di-Phosphorus pentoxide	1314-56-3	100 g	Glass bottle	1.00570.0100
for analysis ACS, ISO, Reag. Ph Eur		500 g	Glass bottle	1.00570.0500

Silica gel [SiO₂]	CAS No.	Content	Packaging	Ord. No.
Silica gel granules, desiccant ~ 0.2–1 mm	7631-86-9	1 kg	HDPE bottle	1.01905.1000
	7(21.00.0	1 kg	HDPE bottle	1.01907.1000
Silica gel granules, desiccant ~ 2-5 mm	7631-86-9	5 kg	Plastic bottle	1.01907.5000
Silica gel with moisture indicator (brown gel) desiccant ~ 1–4 mm		1 kg	HDPE bottle	1.01972.1000
		5 kg	HDPE bottle	1.01972.5000
		25 kg	Plastic drum	1.01972.9025
		1 kg	HDPE bottle	1.01969.1000
Silica gel with indicator (orange gel), granulate ~ 1–3 mm	-	5 kg	HDPE bottle	1.01969.5000
		25 kg	Plastic drum	1.01969.9025
Silica gel beads, desiccant ~ 2-5 mm	7631-86-9	1 kg	HDPE bottle	1.07735.1000



SICAPENT <sup>®</sup> drying agent	Content	Packaging	Ord. No.
SICAPENT <sup>®</sup> drying agent with indicator (phosphorus pentoxide	500 ml	Glass bottle	1.00543.0500
for desiccators) on inert carrier material	2.8	Glass bottle	1.00543.2800

### **Absorption and Filtration** Quality materials for absorption, adsorption & filtration

Purification is one of the most important applications in analytical laboratories. To ease your daily work, we offer a complete range of absorption and adsorption reagents, as well as filtration and clarification materials – all with excellent take-up properties. Our products are suitable for a wide variety of applications, such as absorbing or binding substances, as well as for decolorization, clarification and filtration. Regardless of the purpose, they deliver quality perfected for your intended use.

#### **Your benefits**

- Reliability: All natural products used are tested for organic impurities, and various anions and cations. The products are specified and offer excellent **batch-to-batch consistency**.
- Convenience: **Comprehensive portfolio** allows successful implementation of a wide variety of purification methods.
- Sustainability: Most of our absorption, adsorption and filtration materials are natural reagents which are **not harmful to the environment.**

## Absorption and Filtration Quality materials for absorption,

adsorption & filtration

Calcium oxide	CAS No.	Content	Packaging	Ord. No.
Calcium oxide from marble small lumps ~ 3-20 mm	1305-78-8	1 kg	HDPE bottle	1.02109.1000
		25 kg	Fibre carton	1.02109.9025

Charcoal activated	CAS No.	Content	Packaging	Ord. No.
Charcoal activated for analysis	7440-44-0	250 g	Metal can	1.02186.0250
		1 kg	Metal can	1.02186.1000
		20 kg	Fibre carton	1.02186.9020
Charcoal activated granular about 1.5 mm extra pure	7440-44-0	1 kg	Plastic bag	1.02514.1000
		5 kg	Fibre carton	1.02514.5000
		25 kg	Fibre carton	1.02514.9025
Charcoal activated powder extra pure	7440-44-0	1 kg	Metal can	1.02184.1000
		5 kg	Fibre carton	1.02184.5000
		20 kg	Fibre carton	1.02184.9020
Charcoal activated pure	7440-44-0	1 kg	Plastic bag	1.02183.1000
		20 kg	Fibre carton	1.02183.9020

Charcoal activated



Glass wool	CAS No.	Content	Packaging	Ord. No.
Glass wool	65997-17-3	250 g	Metal can	1.04086.0250
		1 kg	Fibre carton	1.04086.1000

Sea sand	CAS No.	Content	Packaging	Ord. No.
Sea sand extra pure	7631-86-9	1 kg	HDPE bottle	1.07711.1000
		5 kg	HDPE bottle	1.07711.5000
		25 kg	Fibre carton	1.07711.9025
Sea sand purified by acid and calcined for analysis	7631-86-9	1 kg	HDPE bottle	1.07712.1000
		5 kg	HDPE bottle	1.07712.5000
		10 kg	HDPE bottle	1.07712.9010
		25 kg	Fibre carton	1.07712.9025

Sodalime	CAS No.	Content	Packaging	Ord. No.
Sodalime, granules ~ 1-2.5 mm	-	500 g	HDPE bottle	1.06733.0501
with indicator for analysis		2.5 kg	HDPE bottle	1.06733.2500
Sodalime pellets with indicator for analysis	-	1 kg	HDPE bottle	1.06839.1001
		5 kg	HDPE bottle	1.06839.5001
		25 kg	Fibre carton	1.06839.9025



Calcium oxid



Merck KGaA Frankfurter Strasse 250 64293 Darmstadt, Germany Phone +49 (0)6151 720

© 2020 Merck KGaA, Darmstadt, Germany and its affiliates. All Rights Reserved. Merck, the vibrant M, Chemizorb, Emparta, Emplura, Emsure, Extran, Perhydro, Sicapent and Supelco are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

34322 12/2020



For further information, please contact your local VWR organization or have a look at the VWR webpages: **vwr.com** 

